

Day-Brite CFI KEENE LIGHTOLIER

Tackle your lighting project quickly

Tight project timelines can’t hold you back, get quality lighting delivered within 5-10 shipping days. Our solutions can light the way for your next project with the Design Ready portfolio.

The selected QuickShip high performance luminaires from Genlyte Solutions brands include Lightolier, Day-Brite CFI, and Keene offerings.

Illuminate your space with ease

Genlyte Solutions provides the lighting solution for every project whether it's lighting and connecting your public spaces, giving your space an energy-saving upgrade, or working on a yet to be constructed project, we've got you covered. Our Design Ready portfolio makes it easy for you to find highly configurable lighting with modern designs within your timeline and your budget.









Table of contents

Lightolier LyteProfile 2
Lightolier ModuLyte 4
Lightolier Commercial Retrofit 6
Day-Brite CFI HCY 7
Day-Brite CFI FluxPanel 8
Day-Brite CFI Selectable Troffer (DSRT) . 10
Day-Brite CFI SofTrace 12
Day-Brite CFI FluxGrid. 14
Day-Brite CFI FCY 17
Day-Brite CFI FBY 18
Day-Brite CFI FBZ 20
Day-Brite CFI VTS Sealed Strip. 21
Day-Brite CFI SDS Selectable Strip . . 22
Day-Brite CFI V3W Vaporlume 23
Day-Brite CFI FluxSpace Strip 24
Day-Brite CFI NWL Wraparound 25
Day-Brite CFI FluxStream Strip. 26
Keene SlimFlood Dual Select 28
Keene Adjustable Slim Wall Pack 29
Keene LytePro Wall 30
Keene LytePro Area 34
Keene Garage & Canopy 35
Keene LytePro Garage & Canopy . . . 36

Click product family name to jump to catalog page!



LyteProfile

LED upgrade with ease

LyteProfile's adaptable design with AccuRender 90+ CRI technology maximizes color quality and efficacy

LyteProfile Frame

Example: 3RN


Ordering Code	Series	Aperture	Installation	Options
3RN	3	R Round	N New construction (non-IC)	
3RNLC	3	R Round	N New construction (non-IC)	LC Chicago Plenum
3RA	3	R Round	A AirSeal IC (1000lm max)	
3RAS	3	R Round	A AirSeal IC (1000lm max)	S Shallow Universal
3SN	3	S Square	N New construction (non-IC)	
3SNLC	3	S Square	N New construction (non-IC)	LC Chicago Plenum
3SA	3	S Square	A AirSeal IC (1000lm max)	
3SAS	3	S Square	A AirSeal IC (1000lm max)	S Shallow Universal
4RN	4	R Round	N New construction (non-IC)	
4RNLC	4	R Round	N New construction (non-IC)	LC Chicago Plenum
4RR	4	R Round	R Remodeler (non-IC)	
6RN	6	R Round	N New construction (non-IC)	
6RNLC	6	R Round	N New construction (non-IC)	LC Chicago Plenum
6RR	6	R Round	R Remodeler (non-IC)	

LyteProfile Engine/Trim

Example: P3RA10930NFCCE1

Ordering Code	Family	Style	Lumens	Color Temp.	Beam	Reflector	Flange	Dimming	Voltage	Plenum
P3RA10930NFCCE1	P3R	A Adjustable accent	10 1,000lm	930 3,000K (90CRI)	NF Narrow flood	CC Comfort clear	- White	E ELV	1 120V	
P3RA10930NFCCE1S	P3R	A Adjustable accent	10 1,000lm	930 3,000K (90CRI)	NF Narrow flood	CC Comfort clear	- White	E ELV	1 120V	S Shallow
P3RA10930NFCCZ10U	P3R	A Adjustable accent	10 1,000lm	930 3,000K (90CRI)	NF Narrow flood	CC Comfort clear	- White	Z10 0-10V	U 120-277V	
P3RA10930NFCCZ10US	P3R	A Adjustable accent	10 1,000lm	930 3,000K (90CRI)	NF Narrow flood	CC Comfort clear	- White	Z10 0-10V	U 120-277V	S Shallow
P3RA10935NFCCE1	P3R	A Adjustable accent	10 1,000lm	935 3,500K (90CRI)	NF Narrow flood	CC Comfort clear	- White	E ELV	1 120V	
P3RA10935NFCCE1S	P3R	A Adjustable accent	10 1,000lm	935 3,500K (90CRI)	NF Narrow flood	CC Comfort clear	- White	E ELV	1 120V	S Shallow
P3RA10935NFCCZ10US	P3R	A Adjustable accent	10 1,000lm	935 3,500K (90CRI)	NF Narrow flood	CC Comfort clear	- White	Z10 0-10V	U 120-277V	S Shallow
P3RLW10930WCCE1	P3R	LW Lensed wall wash	10 1,000lm	930 3,000K (90CRI)	W Wide	CC Comfort clear	- White	E ELV	1 120V	
P3RLW10930WCCE1S	P3R	LW Lensed wall wash	10 1,000lm	930 3,000K (90CRI)	W Wide	CC Comfort clear	- White	E ELV	1 120V	S Shallow

LIGHTOLIER



LyteProfile Engine/Trim

Example: P3RA10930NFCCE1

Ordering Code	Family	Style	Lumens	Color Temp.	Beam	Reflector	Flange	Dimming	Voltage	Plenum
P3RLW10930WCCZ10U	P3R	LW Lensed wall wash	10 1,000lm	930 3,000K (90CRI)	W Wide	CC Comfort clear	– White	Z10 0–10V	U 120–277V	
P3RLW10935WCCE1	P3R	LW Lensed wall wash	10 1,000lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	E ELV	1 120V	
P3RLW10935WCCE1S	P3R	LW Lensed wall wash	10 1,000lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	E ELV	1 120V	S Shallow
P3RLW10935WCCZ10U	P3R	LW Lensed wall wash	10 1,000lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	Z10 0–10V	U 120–277V	
P3SLW10930WCCE1	P3S	LW Lensed wall wash	10 1,000lm	930 3,000K (90CRI)	W Wide	CC Comfort clear	– White	E ELV	1 120V	
P3SLW10930WCCE1S	P3S	LW Lensed wall wash	10 1,000lm	930 3,000K (90CRI)	W Wide	CC Comfort clear	– White	E ELV	1 120V	S Shallow
P3SLW10930WCCZ10U	P3S	LW Lensed wall wash	10 1,000lm	930 3,000K (90CRI)	W Wide	CC Comfort clear	– White	Z10 0–10V	U 120–277V	
P3SLW10935WCCE1	P3S	LW Lensed wall wash	10 1,000lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	E ELV	1 120V	
P3SLW10935WCCE1S	P3S	LW Lensed wall wash	10 1,000lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	E ELV	1 120V	S Shallow
P4RDL15935WCCZ10U	P4R	D Downlight	15 1,500lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	Z10 0–10V	U 120–277V	
P4SLW15935WWHZ10U	P4R	LW Lensed wall wash	15 1,500lm	935 3,500K (90CRI)	W Wide	W White	– White	Z10 0–10V	U 120–277V	
P4RDL20935WCCZ10U	P4R	D Downlight	20 2,000lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	Z10 0–10V	U 120–277V	
P6RDL15935WCCZ10U	P6R	D Downlight	15 1,500lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	Z10 0–10V	U 120–277V	
P6RDL20935WCCZ10U	P6R	D Downlight	20 2,000lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	Z10 0–10V	U 120–277V	
P6RLW20935WCCZ10U	P6R	LW Lensed wall wash	20 2,000lm	935 3,500K (90CRI)	W Wide	CC Comfort clear	– White	Z10 0–10V	U 120–277V	
P6RDL20940WCCZ10U	P6R	D Downlight	20 2,000lm	940 4,000K (90CRI)	W Wide	CC Comfort clear	– White	Z10 0–10V	U 120–277V	



ModuLyte

Adapting to changes while keeping construction schedules

ModuLyte is a true commercial downlight in appeal and performance with a budget-friendly architecture.

ModuLyte Frame (optional)

Example: 4RNSR

Ordering Code	Size	Application	Installation	Shape
4RNSR	4 4"	R Recessed	N New construction	SR Square and round
6RNSR	6 6"	R Recessed	N New construction	SR Square and round
8RNR	8 8"	R Recessed	N New construction	R Round

4" ModuLyte Engine/Trim

Example: M4RDL259CSWCDZ10U

Ordering Code	Family	Lumens (max)	Color Temp.	Beam	Reflector	Dimming	Voltage
M4RDL259CSWCLZ10U	M4RDL	25 2500lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	W Wide	CL Clear	Z10 0-10V	U 120-277V
M4RDL259CSWCDZ10U	M4RDL	25 2500lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	W Wide	CD Clear diffuse	Z10 0-10V	U 120-277V
M4RDL259CSWWHZ10U	M4RDL	25 2500lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	W Wide	WH White	Z10 0-10V	U 120-277V

6" ModuLyte Engine/Trim

Example: M6RDL259CSWCDZ10U

Ordering Code	Family	Lumens (max)	Color Temp.	Beam	Reflector	Dimming	Voltage
M6RDL259CSWCLZ10U	M6RDL	25 2500lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	W Wide	CL Clear	Z10 0-10V	U 120-277V
M6RDL259CSWCDZ10U	M6RDL	25 2500lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	W Wide	CD Clear diffuse	Z10 0-10V	U 120-277V
M6RDL259CSWWHZ10U	M6RDL	25 2500lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	W Wide	WH White	Z10 0-10V	U 120-277V
M6RDL409CSMCLZ10U	M6RDL	40 4000lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	M Medium	CL Clear	Z10 0-10V	U 120-277V
M6RDL409CSMCDZ10U	M6RDL	40 4000lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	M Medium	CD Clear diffuse	Z10 0-10V	U 120-277V
M6RDL409CSMWHZ10U	M6RDL	40 4000lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	M Medium	WH White	Z10 0-10V	U 120-277V

8" ModuLyte Engine/Trim

Example: M8RDL259CSWCDZ10U

Ordering Code	Family	Lumens (max)	Color Temp.	Beam	Reflector	Dimming	Voltage
M8RDL259CSWCLZ10U	M8RDL	25 2500lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	W Wide	CL Clear	Z10 0-10V	U 120-277V
M8RDL259CSWCDZ10U	M8RDL	25 2500lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	W Wide	CD Clear diffuse	Z10 0-10V	U 120-277V
M8RDL259CSWWHZ10U	M8RDL	25 2500lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	W Wide	WH White	Z10 0-10V	U 120-277V
M8RDL409CSMCLZ10U	M8RDL	40 4000lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	M Medium	CL Clear	Z10 0-10V	U 120-277V
M8RDL409CSMCDZ10U	M8RDL	40 4000lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	M Medium	CD Clear diffuse	Z10 0-10V	U 120-277V
M8RDL409CSMWHZ10U	M8RDL	40 4000lm	9CS 2700K, 3000K, 3500K, 4000K, 5000K	M Medium	WH White	Z10 0-10V	U 120-277V



Accessories	
M4RLW	ML 4IN RND LENS WW OPTIC
M4MED	ML 4IN RND MED BEAM OPTIC
M4GRW	ML 4IN RND GOOF RING WH
M6RLW	ML 6IN RND LENS WW OPTIC
M6MED	ML 6IN RND MED BEAM OPTIC
M6GRW	ML 6IN RND GOOF RING WH
M8RLW	ML 8IN RND LENS WW OPTIC
M8MED	ML 8IN RND MED BEAM OPTIC
M8GRW	ML 8IN RND GOOF RING WH



Commercial Retrofit

Bright, brighter, **brightest**

Will reduce on-site time and headaches for busy installers with its adjustable lumen and color output switch.

Commercial Retrofit **Example: CR4RLMCCT**

Ordering Code	Family	Size/Lumens		Color Temperature	Voltage	Finish
CR4RLMCCT	**CR**	**4LRM**	4" Round 500-1000lm, 90CRI	**CCT** 3000K/3500K/4000K (80CRI)	– 120-347V	- White
CR6RLMCCT	**CR**	**6LRM**	6" Round 700-1500lm, 90CRI	**CCT** 3000K/3500K/4000K (80CRI)	– 120-347V	- White
CR8RLMCCT	**CR**	**8LRM**	8" Round 1000-2000lm, 90CRI	**CCT** 3000K/3500K/4000K (80CRI)	– 120-347V	- White
CR10RLMCCT	**CR**	**10LRM**	10" Round 2000-3000lm, 90CRI	**CCT** 3000K/3500K/4000K (80CRI)	– 120-347V	- White

LIGHTOLIER



HCY High Bay



Modern design and **energy savings**

A great new look with no more sacrifices and dependability you can trust.

HCY High Bay

Example: HCY1421L8CST-UN3-DIM

Ordering Code	Lumens	Color Temperature	Voltage	Driver
HCY1421L8CST-UN3-DIM	**1421L** 14,000/21,000lm	**8CST** 4,000K/5,000K (80CRI)	**UN3** 120-347V	**DIM** 0-10V
HCY2833L8CST-UN3-DIM	**2833L** 28,000/33,000lm	**8CST** 4,000K/5,000K (80CRI)	**UN3** 120-347V	**DIM** 0-10V

Accessories	
HCY2-PRSM	16" Clear polycarbonate reflector for HCY1421L
HCY2-PRLG	16" Clear polycarbonate reflector for HCY2833L
HCY-SURFACE BKT SM	Surface mount bracket for HCY1421L
HCY-SURFACE BKT LG	Surface mount bracket for HCY2833L
HCY-SENSOR	Field installed microwave sensor
HCY-REMOTE	Remote hand-held programmer for HCY-SENSOR

Day-Brite
CFI




FluxPanel

Uniform surface of light provides low glare, flicker free lighting at an affordable price.

FluxPanel **Example: 1FPZ38B835-4-DS-UNV-DIM**

Ordering Code	Width	Lumens	Color Temp.	Length	Diffuser	Voltage	Driver	Options
1FPZ38B835-4-DS-UNV-DIM	1 1'	38B 3,800lm	835 3,500K (80CRI)	4 4'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
1FPZ38B840-4-DS-UNV-DIM	1 1'	38B 3,800lm	840 4,000K (80CRI)	4 4'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ20L835-2-DS-UNV DIM	2 2'	20L 2,000lm	835 3,500K (80CRI)	2 2'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ20L840-2-DS-UNV DIM	2 2'	20L 2,000lm	840 4,000K (80CRI)	2 2'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ20L850-2-DS-UNV DIM	2 2'	20L 2,000lm	850 5,000K (80CRI)	2 2'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ30L835-2-DS-UNV DIM	2 2'	30L 3,000lm	835 3,500K (80CRI)	2 2'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ30L840-2-DS-UNV DIM	2 2'	30L 3,000lm	840 4,000K (80CRI)	2 2'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ38B835-2-DS-UNV-DIM	2 2'	38B 3,800lm	835 3,500K (80CRI)	2 2'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ38B840-2-DS-UNV-DIM	2 2'	38B 3,800lm	840 4,000K (80CRI)	2 2'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ38B850-2-DS-UNV-DIM	2 2'	38B 3,800lm	850 5,000K (80CRI)	2 2'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ42B850-2-DS-UNV-DIM	2 2'	42L 4,200lm	850 5,000K (80CRI)	2 2'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ30L835-4-DS-UNV DIM	4 4'	30L 3,000lm	835 3,500K (80CRI)	4 4'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ30L840-4-DS-UNV DIM	4 4'	30L 3,000lm	840 4,000K (80CRI)	4 4'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ30L850-4-DS-UNV DIM	4 4'	30L 3,000lm	850 5,000K (80CRI)	4 4'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ38L835-4-DS-UNV DIM	4 4'	38L 3,800lm	835 3,500K (80CRI)	4 4'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ38L840-4-DS-UNV DIM	4 4'	38L 3,800lm	840 4,000K (80CRI)	4 4'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	
2FPZ42B835-4-DS-UNV-DIM	4 4'	42B 4,200lm	835 3,500K (80CRI)	4 4'	DS Diffuse smooth	UNV 120-277V	DIM 0-10V	

Day-Brite
CFI



FluxPanel

Example: 1FPZ38B835-4-DS-UNV-DIM

Ordering Code	Width	Lumens	Color Temp.	Length	Diffuser	Voltage	Driver	Options
2FPZ42B840-4-DS-UNV-DIM	**4** 4'	**42B** 4,200lm	**840** 4,000K (80CRI)	**4** 4'	**DS** Diffuse smooth	**UNV** 120-277V	**DIM** 0-10V	
2FPZ43L835-4-DS-UNV-DIM	**4** 4'	**43L** 4,300lm	**835** 3,500K (80CRI)	**4** 4'	**DS** Diffuse smooth	**UNV** 120-277V	**DIM** 0-10V	
2FPZ43L835-4-DS-UNV-DIM-BSL10LST	**4** 4'	**43L** 4,300lm	**835** 3,500K (80CRI)	**4** 4'	**DS** Diffuse smooth	**UNV** 120-277V	**DIM** 0-10V	**BSL10LST** Factory wired Bodine integral emergency pack

Accessories	
FSF22	2'x2' surface mount field installation kit (field assembled)
FSF24	2'x4' surface mount field installation kit (field assembled)

Day-Brite
CFI



Selectable Troffer (DSRT)

Slim, sturdy, and selectable.


Selectable Troffer LED (DSRT)

Example: 1DSRT3050LCS-4-UNV-DIM

Ordering Code	Width	Lumens	Color Temp.	Length	Voltage	Driver	Options
1DSRT3050LCS-4-UNV-DIM	**1** 1'	**3050L** 3000lm, 4000lm, 5000lm	**CS** 3500K, 4000K, 5000K	**4** 4'	**UNV** 120-277V	**DIM** 0-10V	
1DSRT3050LCS-4-UNV-DIM-DAYOCC	**1** 1'	**3050L** 3000lm, 4000lm, 5000lm	**CS** 3500K, 4000K, 5000K	**4** 4'	**UNV** 120-277V	**DIM** 0-10V	**DAYOCC** Daytime Occupancy Sensor
2DSRT3050LCS-2-UNV-DIM	**2** 2'	**3050L** 3000lm, 4000lm, 5000lm	**CS** 3500K, 4000K, 5000K	**2** 2'	**UNV** 120-277V	**DIM** 0-10V	
2DSRT4060LCS-4-UNV-DIM	**2** 2'	**4060L** 4000lm, 5000lm, 6000lm	**CS** 3500K, 4000K, 5000K	**4** 4'	**UNV** 120-277V	**DIM** 0-10V	
2DSRT3050LCS-2-UNV-DIM-DAYOCC	**2** 2'	**3050L** 3000lm, 4000lm, 5000lm	**CS** 3500K, 4000K, 5000K	**2** 2'	**UNV** 120-277V	**DIM** 0-10V	**DAYOCC** Daytime Occupancy Sensor
2DSRT4060LCS-4-UNV-DIM-DAYOCC	**2** 2'	**4060L** 4000lm, 5000lm, 6000lm	**CS** 3500K, 4000K, 5000K	**4** 4'	**UNV** 120-277V	**DIM** 0-10V	**DAYOCC** Daytime Occupancy Sensor

Accessories	
1DSRT-4-SKT	1x4' Selectable Troffer Surface Kit
2DSRT-2-SKT	2x2' Selectable Troffer Surface Kit
2DSRT-4-SKT	2x4' Selectable Troffer Surface Kit
DSRT-CKT-NP	Selectable Troffer Suspension Kit with no power

Day-Brite
CFI



NEW!








SofTrace Recessed

Combines style and performance.

SofTrace Recessed **Example: 1STXG30L835-4-D-UNV-DIM**

Ordering Code	Lumens	Efficacy	CRI/CCT	Options
Common features: 1'x4', grid ceiling, diffuse ribbed, 120-277V, 0-10V				
1STXG30L835-4-D-UNV-DIM	**30L** 3000lm		**835** 80CRI, 3500K	
1STXG38B835-4-D-UNV-DIM	**38B** 3800lm		**835** 80CRI, 3500K	
1STXG38L835-4-D-UNV-DIM	**38L** 3800lm		**835** 80CRI, 3500K	
1STXG38L840-4-D-UNV-DIM	**38L** 3800lm		**840** 80CRI, 4000K	
1STXG45L835-4-D-UNV-DIM	**45L** 4500lm		**835** 80CRI, 3500K	
1STXG45L835-4-D-UNV-DIM-BSL10LST	**45L** 4500lm		**835** 80CRI, 3500K	**BSL10LST** Bodine 10W battery pack
1STXG45L840-4-D-UNV-DIM	**45L** 4500lm		**840** 80CRI, 4000K	
1STXG45LH840-4-D-UNV-DIM	**45L** 4500lm	**H** High efficacy	**840** 80CRI, 4000K	
Common features: 2'x2', grid ceiling, diffuse ribbed, 120-277V, 0-10V				
2STXG30L840-2-D-UNV-DIM	**30L** 3000lm		**840** 80CRI, 4000K	
2STXG38B835-2-D-UNV-DIM	**38B** 3800lm		**835** 80CRI, 3500K	
2STXG38B840-2-D-UNV-DIM	**38B** 3800lm		**840** 80CRI, 4000K	
2STXG38L835-2-D-UNV-DIM	**38L** 3800lm		**835** 80CRI, 3500K	
2STXG38L840-2-D-UNV-DIM	**38L** 3800lm		**840** 80CRI, 4000K	
2STXG38LH835-2-D-UNV-DIM	**38L** 3800lm	**H** High efficacy	**835** 80CRI, 3500K	
2STXG45L835-2-D-UNV-DIM	**45L** 4500lm		**835** 80CRI, 3500K	
2STXG45L835-2-D-UNV-DIM-BSL10LST	**45L** 4500lm		**835** 80CRI, 3500K	**BSL10LST** Bodine 10W battery pack
2STXG45L840-2-D-UNV-DIM	**45L** 4500lm		**840** 80CRI, 4000K	
Common features: 2'x4', grid ceiling, diffuse ribbed, 120-277V, 0-10V				
2STXG42B835-4-D-UNV-DIM	**42B** 4200lm		**835** 80CRI, 3500K	
2STXG42B840-4-D-UNV-DIM	**42B** 4200lm		**840** 80CRI, 4000K	
2STXG43L835-4-D-UNV-DIM	**43L** 4300lm		**835** 80CRI, 3500K	
2STXG43L835-4-D-UNV-DIM-BSL10LST	**43L** 4300lm		**835** 80CRI, 3500K	**BSL10LST** Bodine 10W battery pack
2STXG43L840-4-D-UNV-DIM	**43L** 4300lm		**840** 80CRI, 4000K	
2STXG43L840-4-D-UNV-DIM-BSL10LST	**43L** 4300lm		**840** 80CRI, 4000K	**BSL10LST** Bodine 10W battery pack
2STXG43LH840-4-D-UNV-DIM	**43L** 4300lm	**H** High efficacy	**840** 80CRI, 4000K	
2STXG48L835-4-D-UNV-DIM	**48L** 4800lm		**835** 80CRI, 3500K	
2STXG48L835-4-D-UNV-DIM-BSL10LST	**48L** 4800lm		**835** 80CRI, 3500K	**BSL10LST** Bodine 10W battery pack
2STXG48L840-4-D-UNV-DIM	**48L** 4800lm		**840** 80CRI, 4000K	
2STXG48LH835-4-D-UNV-DIM	**48L** 4800lm	**H** High efficacy	**835** 80CRI, 3500K	

Day-Brite
CFI



SofTrace Recessed

Example: 1STXG30L835-4-D-UNV-DIM

Ordering Code	Lumens	Efficacy	CRI/CCT	Options
2STXG48LH835-4-D-UNV-DIM-BSL10LST	**48L** 4800lm	**H** High efficacy	**835** 80CRI, 3500K	**BSL10LST** Bodine 10W battery pack
2STXG54L835-4-D-UNV-DIM	**54L** 5400lm		**835** 80CRI, 3500K	
2STXG54L840-4-D-UNV-DIM	**54L** 5400lm		**840** 80CRI, 4000K	
2STXG54L840-4-D-UNV-DIM-BSL10LST	**54L** 5400lm		**840** 80CRI, 4000K	**BSL10LST** Bodine 10W battery pack
2STXG74L835-4-D-UNV-DIM	**74L** 7400lm		**835** 80CRI, 3500K	
2STXG74L835-4-D-UNV-DIM-BSL10LST	**74L** 7400lm		**835** 80CRI, 3500K	**BSL10LST** Bodine 10W battery pack
2STXG74L840-4-D-UNV-DIM	**74L** 7400lm		**840** 80CRI, 4000K	
2STXG74L840-4-D-UNV-DIM-BSL10LST	**74L** 7400lm		**840** 80CRI, 4000K	**BSL10LST** Bodine 10W battery pack

Accessories	
FMA14	1'x4' "F" mounting frame for NEMA "F" ceiling
FMA22	2'x2' "F" mounting frame for NEMA "F" ceiling
FMA24	2'x4' "F" mounting frame for NEMA "F" ceiling



FluxGrid


A product family configurable to fit your exact needs

Ideal for commercial, educational, and hospitality applications

FluxGrid **Example: 1FGXG42B835-4-FS-UNV-DIM**

Ordering Code	Width	Ceiling Type	Air Function	Lumens	Color Temp.	Length	Diffuser	Voltage	Driver	Options
1FGXG42B835-4-FS-UNV-DIM	1 1'	G Grid		42B 4,200lm	835 3,500K (80CRI)	4 4'	FS Diffuse flat smooth	UNV 120-277V	DIM 0-10V	
1FGXG42B835-4-FS-UNV-DIM-CHIC	1 1'	G Grid		42B 4,200lm	835 3,500K (80CRI)	4 4'	FS Diffuse flat smooth	UNV 120-277V	DIM 0-10V	CHIC Chicago Plenum rated
1FGXG42B835-4-RS-UNV-DIM	1 1'	G Grid		42B 4,200lm	835 3,500K (80CRI)	4 4'	RS Diffuse round smooth	UNV 120-277V	DIM 0-10V	
1FGXG42B835-4-RS-UNV-DIM-CHIC	1 1'	G Grid		42B 4,200lm	835 3,500K (80CRI)	4 4'	RS Diffuse round smooth	UNV 120-277V	DIM 0-10V	CHIC Chicago Plenum rated
1FGXG42B840-4-FS-UNV-DIM	1 1'	G Grid		42B 4,200lm	840 4,000K (80CRI)	4 4'	FS Diffuse flat smooth	UNV 120-277V	DIM 0-10V	
1FGXG42B840-4-RS-UNV-DIM	1 1'	G Grid		42B 4,200lm	840 4,000K (80CRI)	4 4'	RS Diffuse round smooth	UNV 120-277V	DIM 0-10V	
2FGXG20L835-2-RS-UNV-DIM-SWZCS	2 2'	G Grid		20L 2,000lm	835 3,500K (80CRI)	2 2'	RS Diffuse round smooth	UNV 120-277V	DIM 0-10V	SWZCS Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG20L840-2-RS-UNV-DIM-SWZCS	2 2'	G Grid		20L 2,000lm	840 4,000K (80CRI)	2 2'	RS Diffuse round smooth	UNV 120-277V	DIM 0-10V	SWZCS Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG30L835-2-FS-UNV-DIM-SWZCS	2 2'	G Grid		30L 3,000lm	835 3,500K (80CRI)	2 2'	FS Diffuse flat smooth	UNV 120-277V	DIM 0-10V	SWZCS Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG30L835-2-RS-UNV-DIM	2 2'	G Grid		30L 3,000lm	835 3,500K (80CRI)	2 2'	RS Diffuse round smooth	UNV 120-277V	DIM 0-10V	
2FGXG30L835-2-RS-UNV-DIM-SWZCS	2 2'	G Grid		30L 3,000lm	835 3,500K (80CRI)	2 2'	RS Diffuse round smooth	UNV 120-277V	DIM 0-10V	SWZCS Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG30L840-2-FS-UNV-DIM-SWZCS	2 2'	G Grid		30L 3,000lm	840 4,000K (80CRI)	2 2'	FS Diffuse flat smooth	UNV 120-277V	DIM 0-10V	SWZCS Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG30L840-2-RS-UNV-DIM	2 2'	G Grid		30L 3,000lm	840 4,000K (80CRI)	2 2'	RS Diffuse round smooth	UNV 120-277V	DIM 0-10V	

Day-Brite
CFI



FluxGrid

Example: 1FGXG42B835-4-FS-UNV-DIM

Ordering Code	Width	Ceiling Type	Air Function	Lumens	Color Temp.	Length	Diffuser	Voltage	Driver	Options
2FGXG30L840-2-RS-UNV-DIM-SWZCS	**2** 2'	**G** Grid		**30L** 3,000lm	**840** 4,000K (80CRI)	**2** 2'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**SWZCS** Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG38B835-2-RS-UNV-DIM	**2** 2'	**G** Grid		**38B** 3,800lm	**835** 3,500K (80CRI)	**2** 2'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG38B835-2-RS-UNV-DIM-CHIC	**2** 2'	**G** Grid		**38B** 3,800lm	**835** 3,500K (80CRI)	**2** 2'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**CHIC** Chicago Plenum rated
2FGXGH38B835-2-RS-UNV-DIM-CHIC	**2** 2'	**G** Grid	**H** Air return	**38B** 3,800lm	**835** 3,500K (80CRI)	**2** 2'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**CHIC** Chicago Plenum rated
2FGXG38B840-2-RS-UNV-DIM	**2** 2'	**G** Grid		**38B** 3,800lm	**840** 4,000K (80CRI)	**2** 2'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG38L835-2-RS-UNV-DIM	**2** 2'	**G** Grid		**38L** 3,800lm	**835** 3,500K (80CRI)	**2** 2'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG38L840-2-RS-UNV-DIM	**2** 2'	**G** Grid		**38L** 3,800lm	**840** 4,000K (80CRI)	**2** 2'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG45L835-2-RS-UNV-DIM	**2** 2'	**G** Grid		**45L** 4,500lm	**835** 3,500K (80CRI)	**2** 2'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG38L835-4-RS-UNV-DIM	**2** 2'	**G** Grid		**38L** 3,800lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG38L835-4-RS-UNV-DIM-SWZCS	**2** 2'	**G** Grid		**38L** 3,800lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**SWZCS** Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG38L840-4-RS-UNV-DIM	**2** 2'	**G** Grid		**38L** 3,800lm	**840** 4,000K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG38L840-4-RS-UNV-DIM-SWZCS	**2** 2'	**G** Grid		**42B** 4,200lm	**840** 4,000K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**SWZCS** Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG42B835-4-FS-UNV-DIM	**2** 2'	**G** Grid		**42B** 4,200lm	**835** 3,500K (80CRI)	**4** 4'	**FS** Diffuse flat smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG42B835-4-RS-UNV-DIM	**2** 2'	**G** Grid		**42B** 4,200lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG42B835-4-RS-UNV-DIM-CHIC	**2** 2'	**G** Grid		**42B** 4,200lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**CHIC** Chicago Plenum rated



FluxGrid (continued)

A product family configurable to fit your exact needs

Ideal for commercial, educational, and hospitality applications

FluxGrid **Example: 1FGXG42B835-4-FS-UNV-DIM**

Ordering Code	Width	Ceiling Type	Air Function	Lumens	Color Temp.	Length	Diffuser	Voltage	Driver	Options
2FGXGH42B835-4-RS-UNV-DIM-CHIC	**2** 2'	**G** Grid	**H** Air return	**42B** 4,200lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**CHIC** Chicago Plenum rated
2FGXG42B840-4-FS-UNV-DIM	**2** 2'	**G** Grid		**42B** 4,200lm	**840** 4,000K (80CRI)	**4** 4'	**FS** Diffuse flat smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG42B840-4-RS-UNV-DIM	**2** 2'	**G** Grid		**43L** 4,300lm	**840** 4,000K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG43L835-4-RS-UNV-DIM	**2** 2'	**G** Grid		**43L** 4,300lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG43L835-4-RS-UNV-DIM-SWZCS	**2** 2'	**G** Grid		**43L** 4,300lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**SWZCS** Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG43L840-4-RS-UNV-DIM	**2** 2'	**G** Grid		**43L** 4,300lm	**840** 4,000K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG43L840-4-RS-UNV-DIM-SWZCS	**2** 2'	**G** Grid		**48L** 4,800lm	**840** 4,000K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**SWZCS** Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG48L835-4-RS-UNV-DIM	**2** 2'	**G** Grid		**48L** 4,800lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG48L835-4-RS-UNV-DIM-SWZCS	**2** 2'	**G** Grid		**48L** 4,800lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**SWZCS** Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG48L840-4-RS-UNV-DIM	**2** 2'	**G** Grid		**48L** 4,800lm	**840** 4,000K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	
2FGXG48L840-4-RS-UNV-DIM-SWZCS	**2** 2'	**G** Grid		**48L** 4,800lm	**840** 4,000K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**SWZCS** Interact Pro scalable sensor w/ integral daylight & occupancy sensing
2FGXG54L835-4-RS-UNV-DIM	**2** 2'	**G** Grid		**54L** 5,400lm	**835** 3,500K (80CRI)	**4** 4'	**RS** Diffuse round smooth	**UNV** 120-277V	**DIM** 0-10V	**BSL10LST** Factory wired Bodine integral emergency pack

Accessories	
FSF22	2'x2' surface mount field installation kit (field assembled)
FSF24	2'x4' surface mount field installation kit (field assembled)

Day-Brite CFI



FCY High Bay



Simple, easy, convenient

A value high bay with low profile and durable design, ideal for your mid to high ceiling applications

FCY High Bay **Example: FCY0815L8CST-UNV-DIM**

Ordering Code	Lumens	Color Temperature	Voltage	Driver
FCY0815L8CST-UNV-DIM	**0815L** 8,000/12,000/15,000lm	**8CST** 4,000K/5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V
FCY1524L8CST-UNV-DIM	**1524L** 15,000/18,000/24,000lm	**8CST** 4,000K/5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V
FCY2436L8CST-UNV-DIM	**2436L** 24,000/30,000/36,000lm	**8CST** 4,000K/5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V

Accessories	
FCY-PENHGR24	Pendant hanger accessory for FCY0815L and FCY1524L
FCY-PENHGR36	Pendant hanger accessory for FCY2436L
FCY-SBK24	Surface bracket accessory for FCY0815L and FCY1524L
FCY-SBK36	Surface bracket accessory for FCY2436L
FCY-WG15	Wire guard for FCY0815L
FCY-WG24	Wire guard for FCY1524L
FCY-WG36	Wire guard for FCY2436L
FCY-SENSOR	Field installed microwave sensor
FCY-REMOTE	Remote hand-held programmer for FCY-SENSOR

Day-Brite
CFI



FBY High Bay

Versatility in form and function

Reliable and cost-friendly soltution for
your big industrial or instituitonal spaces

FBY High Bay

Example: FBY12L850-UNV-LFA-SWZCSH

Ordering Code	Lumens	Color Temperature	Voltage	Options
FBY12L835-UNV	**12L** 12,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	
FBY12L835-UNV-BSL10LST	**12L** 12,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FBY12L840-UNV	**12L** 12,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	
FBY12L840-UNV-LFA	**12L** 12,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens
FBY12L850-UNV	**12L** 12,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	
FBY12L850-UNV-LFA	**12L** 12,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens
FBY12L850-UNV-LFA-SWZCSH	**12L** 12,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens **SWZCSH** Interact Pro scalable high bay sensor w/integral daylight & occupancy sensing
FBY18L840-UNV	**18L** 18,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	
FBY18L840-UNV-WC6	**18L** 18,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**WC6** Wired 6' 16/3 cord
FBY18L840-UNV-LFA	**18L** 18,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens
FBY18L840-UNV-MD360	**18L** 18,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**MD360** 360° Motion detector (ON/OFF)
FBY18L840-UNV-BSL10LST	**18L** 18,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FBY18L850-UNV	**18L** 18,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	
FBY18L850-UNV-LFA-SWZCSH	**18L** 18,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens **SWZCSH** Interact Pro scalable high bay sensor w/integral daylight & occupancy sensing
FBY24L835-UNV-WC6/5	**24L** 24,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**WC6/5** Wired 6' 18/5 cord for line voltage plus 0-10V dimming
FBY24L840-277-WP6	**24L** 24,000lm	**840** 4,000K (80CRI)	**277** 277V	**WP6** Wired 6' 16/3 cord & NEMA twist lock plug
FBY24L840-277-WP6-MD360	**24L** 24,000lm	**840** 4,000K (80CRI)	**277** 277V	**WP6** Wired 6' 16/3 cord & NEMA twist lock plug **MD360** 360° Motion detector (ON/OFF)
FBY24L840-UNV	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	
FBY24L840-UNV-WC6	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**WC6** Wired 6' 16/3 cord
FBY24L840-UNV-WC6-MD360	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**WC6** Wired 6' 16/3 cord **MD360** 360° Motion detector (ON/OFF)
FBY24L840-UNV-LFA	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens
FBY24L840-UNV-MD360	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**MD360** 360° Motion detector (ON/OFF)
FBY24L840-UNV-BSL10LST	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FBY24L850-UNV	**24L** 24,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	

Day-Brite
CFI

Clear lens



No lens



Frosted lens



FBY High Bay

Example: FBY12L850-UNV-LFA-SWZCSH

Ordering Code	Lumens	Color Temperature	Voltage	Options
FBY24L850-UNV-WC6	**24L** 24,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**WC6** Wired 6' 16/3 cord
FBY24L850-UNV-LFA	**24L** 24,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens
FBY30L840-277-WP6/4-MD360-BSL10LST	**30L** 30,000lm	**840** 4,000K (80CRI)	**277** 277V	**WP6/4** Wired 6' 16/4 cord and NEMA twist lock plug for line voltage plus unswitched hot for EMERGENCY **MD360** 360° Motion detector (ON/OFF) **BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FBY30L840-UNV	**30L** 30,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	
FBY30L840-UNV-WC6	**30L** 30,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**WC6** Wired 6' 16/3 cord
FBY30L840-UNV-WC6-LFA	**30L** 30,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**WC6** Wired 6' 16/3 cord **LFA** Frosted acrylic lens
FBY30L840-UNV-WC6-MD360	**30L** 30,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**WC6** Wired 6' 16/3 cord **MD360** 360° Motion detector (ON/OFF)
FBY30L840-UNV-LFA	**30L** 30,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens
FBY30L840-UNV-MD360	**30L** 30,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**MD360** 360° Motion detector (ON/OFF)
FBY30L840-UNV-MD360-BSL10LST	**30L** 30,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**MD360** 360° Motion detector (ON/OFF) **BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FBY30L850-UNV-WC6	**30L** 30,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**WC6** Wired 6' 16/3 cord
FBY30L850-UNV-LFA	**30L** 30,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens
FBY36L840-277-WP6-LCA-MD360	**36L** 36,000lm	**840** 4,000K (80CRI)	**277** 277V	**WP6** Wired 6' 16/3 cord & NEMA twist lock plug **LCA** Clear acrylic lens **MD360** 360° Motion detector (ON/OFF)
FBY36L840-UNV	**36L** 36,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	
FBY36L850-UNV	**36L** 36,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	
FBY48L840-UNV	**48L** 48,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	
FBY48L840-UNV-MD360	**48L** 48,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**MD360** 360° Motion detector (ON/OFF)
FBY48L840-UNV-BSL10LST	**48L** 48,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FBY60L840-UNV	**60L** 60,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	
FBY60L850-UNV	**60L** 60,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	

Accessories	
FBX-SLFA-2N	Frosted acrylic lens kit for 12000lm to 30000lm
MD360	Field installable 360° Motion detector (ON/OFF)
HNH5-VHOOK	54" Chains & V Brackets
HCH5-VHOOK	5' Cables & V Brackets
HCH10-VHOOK	10' Cables & V Brackets



FBZ High Bay



Performance and efficiency at its best

A linear high bay designed to maximize your capital investment and energy costs without sacrificing performance

FBZ High Bay

Example: FBZ48L840-UNV-N-MD360-BSL20B2

Ordering Code	Lumens	Color Temperature	Voltage	Options
FBZ24L840-UNV	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	
FBZ24L840-UNV-BSL20B2	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**BSL20B2** Factory wired 20W Philips Bodine integral emergency pack
FBZ24L840-UNV-LFA	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**LFA** Frosted acrylic lens
FBZ24L840-UNV-MD360-BSL20B2	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**MD360** 360° Motion detector (ON/OFF) **BSL20B2** Factory wired 20W Philips Bodine integral emergency pack
FBZ24L840-UNV-MD360-LCA	**24L** 24,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**MD360** 360° Motion detector (ON/OFF) **LCA** Clear acrylic lens
FBZ30L840-UNV-N-BSL20B2	**30L** 30,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**N** Narrow beam distribution **BSL20B2** Factory wired 20W Philips Bodine integral emergency pack
FBZ36L840-UNV-N-BSL20B2	**36L** 36,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**N** Narrow beam distribution **BSL20B2** Factory wired 20W Philips Bodine integral emergency pack
FBZ48L840-UNV-N-MD360-BSL20B2	**48L** 48,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**N** Narrow beam distribution **MD360** 360° Motion detector (ON/OFF) **BSL20B2** Factory wired 20W Philips Bodine integral emergency pack
FBZ48L840-UNV-N-MD360-LCA	**48L** 48,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**N** Narrow beam distribution **MD360** 360° Motion detector (ON/OFF) **LCA** Clear acrylic lens

Accessories	
FBZ-SLCA-2N	Clear acrylic lens kit for 8000lm to 30000lm
FBZ-WG2	Wire guard for 8000lm to 30000lm
MD360	Field installable 360° Motion detector (ON/OFF)
HNH5-VHOOK	54" Chains & V Brackets
HCH5-VHOOK	5' Cables & V Brackets
HCH10-VHOOK	10' Cables & V Brackets

Day-Brite
CFI



VTS Sealed Strip


Dual selectable for indoor and outdoor applications

A sealed strip luminaire offering rugged reliability, selectability, and efficacy

VTS Sealed Strip **Example: VTS22028L8CST-UN3-DIM**

Ordering Code	Length	Lumens	Color Temperature	Voltage	Driver
VTS225L840-UN3-DIM	**2** 2'	**25L** 2,500lm	**840** 4,000K (80CRI)	**UN3** 120-347V	**DIM** 0-10V
VTS22028L8CST-UN3-DIM	**2** 2'	**2028L** 2,000/2,400/2,800lm	**8CST** 3,500/4,000/5,000K (80CRI)	**UN3** 120-347V	**DIM** 0-10V
VTS450L840-UN3-DIM	**4** 4'	**50L** 5,000lm	**840** 4,000K (80CRI)	**UN3** 120-347V	**DIM** 0-10V
VTS42856L8CST-UN3-DIM	**4** 4'	**2856L** 2,800/4,200/5,600lm	**8CST** 3,500/4,000/5,000K (80CRI)	**UN3** 120-347V	**DIM** 0-10V
VTS8100L840-UN3-DIM	**8** 8'	**100L** 10,000lm	**840** 4,000K (80CRI)	**UN3** 120-347V	**DIM** 0-10V
VTS880130L8CST-UN3-DIM	**8** 8'	**80130L** 8,000/11,000/13,000lm	**8CST** 3,500/4,000/5,000K (80CRI)	**UN3** 120-347V	**DIM** 0-10V

Day-Brite
CFI



SDS Selectable Strip

Economical luminaire delivering the right light

SDS Selectable Strip

Example: SDS21224L8CST-UNV-DIM

Ordering Code	Length	Lumens	Color Temperature	Voltage	Driver
SDS21224L8CST-UNV-DIM	**2** 2'	**1224L** 1,200/1,800/2,400lm	**8CST** 3,500K/4,000K/5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V
SDS42448L8CST-UNV-DIM	**4** 4'	**2448L** 2,430/3,640/4,850lm	**8CST** 3,500K/4,000K/5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V
SDS84998L8CST-UNV-DIM	**8** 8'	**4998L** 4,900/7,350/9,800lm	**8CST** 3,500K/4,000K/5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V

Accessories	
FKR-126	54" Chains & V Brackets

Day-Brite CFI



V3W Vaporlume

Robust, yet highly efficient

A specialized wet location, IP rated product designed for use in both indoor and outdoor environments

V3W Vaporlume


Example: V3W227L840-UNV-DIM

Ordering Code	Length	Lumens	Color Temperature	Voltage	Driver	Options
V3W227L840-UNV-DIM	**2** 2'	**27L** 2,700lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
V3W435L835-UNV-DIM	**4** 4'	**35L** 3,500lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
V3W443L830-UNV-DIM	**4** 4'	**43L** 4,300lm	**830** 3000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
V3W443L835-UNV-DIM	**4** 4'	**43L** 4,300lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
V3W443L835-UNV-DIM-TR-LFA	**4** 4'	**43L** 4,300lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**TR** Torx T-10 tamper resistant stainless steel screws and latches **LFA** Smooth frosted acrylic lens
V3W443L840-UNV-DIM	**4** 4'	**43L** 4,300lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
V3W443L840-UNV-DIM-BSL10LST	**4** 4'	**43L** 4,300lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**BSL10LST** Factory wired Bodine integral emergency pack
V3W443L840-UNV-DIM-MD360WD	**4** 4'	**43L** 4,300lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**MD360WD** Wet location occupancy sensor, (ON/DIM)
V3W451L835-UNV-DIM	**4** 4'	**51L** 5,100lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
V3W451L835-UNV-DIM-IP67-LFA	**4** 4'	**51L** 5,100lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**IP67** Protection against effects of immersion **LFA** Smooth frosted acrylic lens
V3W451L840-UNV-DIM	**4** 4'	**51L** 5,100lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
V3W470L840-UNV-DIM	**4** 4'	**70L** 7,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
V3W470L840-UNV-DIM-MD360WD	**4** 4'	**70L** 7,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**MD360WD** Wet location occupancy sensor, (ON/DIM)

Accessories	
TBK	Stainless Steel Top Bracket Kit (pair of brackets)
FKR-126	54" Chains & V Brackets (must use with TBK)

Day-Brite

CFI



Flexible in **form and function**

A linear solution with a wide range of features and performance specifications making it ideal for a variety of applications

FluxSpace Strip — **Example: FLP220L840-Q-UNV-DIM-SWZCS/S**

Ordering Code	Lumens	Lens	Options
Common features: 2', 4000K, 80CRI, 120-277V, 0-10V			
FLP220L840-Q-UNV-DIM-SWZCS/S	**20L** 2,000lm	**Q** Square, frosted lens	**SWZCS/S** Interact Pro scalable sensor w/integral daylight & occupancy sensing
FLP220L840-R-UNV-DIM-SWZCS/S	**20L** 2,000lm	**R** Round, frosted lens	**SWZCS/S** Interact Pro scalable sensor w/integral daylight & occupancy sensing
FLP230L840-Q-UNV-DIM-SWZCS/S	**30L** 3,000lm	**Q** Square, frosted lens	**SWZCS/S** Interact Pro scalable sensor w/integral daylight & occupancy sensing
Common features: 4', 4000K, 80CRI, 120-277V, 0-10V			
FLP430L840-Q-UNV-DIM-SWZCS/S-BSL10LST	**30L** 3,000lm	**Q** Square, frosted lens	**SWZCS/S** Interact Pro scalable sensor (side mounted) **BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FLP430L840-Q-UNV-DIM-SWZCS/S	**30L** 3,000lm	**Q** Square, frosted lens	**SWZCS/S** Interact Pro scalable sensor w/integral daylight & occupancy sensing
FLP430L840-R-UNV-DIM-SWZCS/S-BSL10LST	**30L** 3,000lm	**R** Round, frosted lens	**BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FLP430L840-R-UNV-DIM-SWZCS/S	**30L** 3,000lm	**R** Round, frosted lens	**SWZCS/S** Interact Pro scalable sensor w/integral daylight & occupancy sensing
FLP440L840-Q-UNV-DIM-SWZCS/S	**40L** 4,000lm	**Q** Square, frosted lens	**SWZCS/S** Interact Pro scalable sensor w/integral daylight & occupancy sensing
Common features: 8', 4000K, 80CRI, 120-277V, 0-10V			
FLP860L840-Q-UNV-DIM-SWZCS/S-BSL10LST	**60L** 6,000lm	**Q** Square, frosted lens	**SWZCS/S** Interact Pro scalable sensor (side mounted) **BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FLP860L840-Q-UNV-DIM-SWZCS/S	**60L** 6,000lm	**Q** Square, frosted lens	**SWZCS/S** Interact Pro scalable sensor w/integral daylight & occupancy sensing
FLP860L840-R-UNV-DIM-SWZCS/S	**60L** 6,000lm	**R** Round, frosted lens	**SWZCS/S** Factory wired Bodine BSL310LP integral emergency pack
FLP860L840-U-UNV-DIM-SWZCS/S	**60L** 6,000lm	**U** Wide upright, frosted lens	**SWZCS/S** Interact Pro scalable sensor w/integral daylight & occupancy sensing
FLP880L840-Q-UNV-DIM-SWZCS/S-BSL10LST	**80L** 8,000lm	**Q** Square, frosted lens	**SWZCS/S** Interact Pro scalable sensor (side mounted) **BSL10LST** Factory wired 10W Philips Bodine integral emergency pack
FLP880L840-Q-UNV-DIM-SWZCS/S	**80L** 8,000lm	**Q** Square, frosted lens	**SWZCS/S** Interact Pro scalable sensor w/integral daylight & occupancy sensing
FLP880L840-R-UNV-DIM-SWZCS/S	**80L** 8,000lm	**R** Round, frosted lens	**SWZCS/S** Factory wired Bodine BSL310LP integral emergency pack

Accessories	
FKR-126	54" Chains & V Brackets
DACH48	Adjustable 48" cable hanger kit (single)
DACH48-1-SC	Adjustable 48" cable hanger kit with white straight 18/3 cord (single)
DACH48-1D-SC	Adjustable 48" cable hanger kit with white straight 18/5 cord & dim leads (single)

Day-Brite
CFI



NWL Wraparound

Simple, economical, selectable

An economical surface mount general illumination luminaire for use in commercial applications.

NWL Wraparound **Example: NWL215258CST-UNV-DIM**

Ordering Code	Length	Lumens	Color Temperature	Voltage	Driver
NWL215258CST-UNV-DIM	**2** 2'	**1525L** 1500/2000/2500lm	**8CST** 3500K/4000K/5000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V
NWL415258CST-UNV-DIM	**4** 4'	**3050L** 3000/4000/5000lm	**8CST** 3500K/4000K/5000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V
NWL815258CST-UNV-DIM	**8** 8'	**60100L** 6000/8000/10000	**8CST** 3500K/4000K/5000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V
NWL415258CST-UN3-DIM	**4** 4'	**3050L** 3000/4000/5000lm	**8CST** 3500K/4000K/5000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V
NWL815258CST-UN3-DIM	**8** 8'	**60100L** 6000/8000/10000	**8CST** 3500K/4000K/5000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V



FluxStream Strip

Real convenience for your operation's success

Tough and dependable luminaires designed
for ease of handling and flexibility

FluxStream EZ Strip

Example: FSSEZ440L840-UNV-DIM


Ordering Code	Length	Lumens	Color Temperature	Voltage	Driver	Options
FSSEZ440L840-UNV-DIM	**4** 4'	**40L** 4,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSSEZ880L840-UNV-DIM	**8** 8'	**80L** 8,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	

FluxStream Strip

Example: FSS220L835-UNV-DIM

Ordering Code	Length	Lumens	Color Temperature	Voltage	Driver	Options
FSS220L835-UNV-DIM	**2** 2'	**20L** 2,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS220L840-UNV-DIM	**2** 2'	**20L** 2,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS220L850-UNV-DIM	**2** 2'	**20L** 2,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS330L835-UNV-DIM	**3** 3'	**30L** 3,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS330L840-UNV-DIM	**3** 3'	**30L** 3,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS430L835-UNV-DIM	**4** 4'	**30L** 3,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS430L840-UNV-DIM	**4** 4'	**30L** 3,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS430L850-UNV-DIM	**4** 4'	**30L** 3,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS440L830-UNV-DIM	**4** 4'	**40L** 4,000lm	**830** 3,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS440L835-UNV-DIM	**4** 4'	**40L** 4,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS440L835-UNV-DIM-EMLED	**4** 4'	**40L** 4,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**EMLED** Factory wired Bodine BSL310LP integral emergency pack
FSS440L835-UNV-SDIM	**4** 4'	**40L** 4,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**SDIM** Step dimming to 40% input power	
FSS440L835-UNV-SDIM-EMLED	**4** 4'	**40L** 4,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**SDIM** Step dimming to 40% input power	**EMLED** Factory wired Bodine BSL310LP integral emergency pack
FSS440L840-UNV-DIM	**4** 4'	**40L** 4,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS440L840-UNV-DIM-EMLED	**4** 4'	**40L** 4,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**EMLED** Factory wired Bodine BSL310LP integral emergency pack
FSS440L840-UNV-SDIM	**4** 4'	**40L** 4,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**SDIM** Step dimming to 40% input power	
FSS440L850-UNV-DIM	**4** 4'	**40L** 4,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS455L835-UNV-DIM	**4** 4'	**55L** 5,500lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	

Day-Brite
CFI



FluxStream Strip

Example: FSS220L835-UNV-DIM

Ordering Code	Length	Lumens	Color Temperature	Voltage	Driver	Options
FSS455L840-UNV-DIM	**4** 4'	**55L** 5,500lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS455L850-UNV-DIM	**4** 4'	**55L** 5,500lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS470L835-UNV-DIM	**4** 4'	**70L** 7,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS470L840-UNV-DIM	**4** 4'	**70L** 7,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS860L840-UNV-DIM	**8** 8'	**60L** 6,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS860L850-UNV-DIM	**8** 8'	**60L** 6,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS880L835-UNV-DIM	**8** 8'	**80L** 8,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS880L835-UNV-DIM-EMLED	**8** 8'	**80L** 8,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**EMLED** Factory wired Bodine BSL310LP integral emergency pack
FSS880L840-UNV-DIM	**8** 8'	**80L** 8,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS880L840-UNV-DIM-EMLED	**8** 8'	**80L** 8,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**EMLED** Factory wired Bodine BSL310LP integral emergency pack
FSS880L850-UNV-DIM	**8** 8'	**80L** 8,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS8110L835-UNV-DIM	**8** 8'	**110L** 11,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS8110L835-UNV-DIM-EMLED	**8** 8'	**110L** 11,000lm	**835** 3,500K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**EMLED** Factory wired Bodine BSL310LP integral emergency pack
FSS8110L840-UNV-DIM	**8** 8'	**110L** 11,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	
FSS8110L840-UNV-DIM-EMLED	**8** 8'	**110L** 11,000lm	**840** 4,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	**EMLED** Factory wired Bodine BSL310LP integral emergency pack
FSS8110L850-UNV-DIM	**8** 8'	**110L** 11,000lm	**850** 5,000K (80CRI)	**UNV** 120-277V	**DIM** 0-10V	

Accessories	
FKR-126	54" Chains & V Brackets
FSTH	Sliding Hanger Bracket (set of two)
FSSWG4	Wire Guard 4' (order two for 8' models)
FSSD4L	4' Diffuse replacement lens (order two for 8' models)

Day-Brite
CFI



SlimFlood Dual Select

Fade-resistant, textured bronze finish with tempered glass lens that is heat and impact resistant

SlimFlood Dual Select

Example: SF15-SCT-K-G2-10-BZ

Ordering Code	Luminaire	Color Temperature	Mounting	Gen.	Voltage	Options	Finish
SF15-SCT-K-G2-10-BZ	**SF15** 15W	**SCT** 3000K/4000K/5000K	**K** Knuckle	**G2**	**10** 120-347V		**BZ** Bronze
SF15-SCT-Y-G2-10-BZ	**SF15** 15W	**SCT** 3000K/4000K/5000K	**Y** Yoke	**G2**	**10** 120-347V		**BZ** Bronze
SF35-SCT-K-G2-10-PCB-BZ	**SF35** 15-25-35W	**SCT** 3000K/4000K/5000K	**K** Knuckle	**G2**	**10** 120-347V	**PCB** Photocell	**BZ** Bronze
SF35-SCT-Y-G2-10-PCB-BZ	**SF35** 15-25-35W	**SCT** 3000K/4000K/5000K	**Y** Yoke	**G2**	**10** 120-347V	**PCB** Photocell	**BZ** Bronze
SF60-SCT-K-G2-10-PCB-BZ	**SF60** 15-35-60W	**SCT** 3000K/4000K/5000K	**K** Knuckle	**G2**	**10** 120-347V	**PCB** Photocell	**BZ** Bronze
SF60-SCT-Y-G2-10-PCB-BZ	**SF60** 15-35-60W	**SCT** 3000K/4000K/5000K	**Y** Yoke	**G2**	**10** 120-347V	**PCB** Photocell	**BZ** Bronze
SF100-SCT-S-G2-10-PCB-BZ	**SF100** 60-80-100W	**SCT** 3000K/4000K/5000K	**S** Slipfitter	**G2**	**10** 120-347V	**PCB** Photocell	**BZ** Bronze
SF100-SCT-T-G2-10-PCB-BZ	**SF100** 60-80-100W	**SCT** 3000K/4000K/5000K	**T** Trunnion	**G2**	**10** 120-347V	**PCB** Photocell	**BZ** Bronze
SF150-SCT-S-G2-10-PCB-BZ	**SF150** 100-120-150W	**SCT** 3000K/4000K/5000K	**S** Slipfitter	**G2**	**10** 120-347V	**PCB** Photocell	**BZ** Bronze
SF150-SCT-T-G2-10-PCB-BZ	**SF150** 100-120-150W	**SCT** 3000K/4000K/5000K	**T** Trunnion	**G2**	**10** 120-347V	**PCB** Photocell	**BZ** Bronze
SF205-SCT-S-G2-10-BZ	**SF205** 120-150-205W	**SCT** 3000K/4000K/5000K	**S** Slipfitter	**G2**	**10** 120-347V		**BZ** Bronze
SF205-SCT-T-G2-10-BZ	**SF205** 120-150-205W	**SCT** 3000K/4000K/5000K	**T** Trunnion	**G2**	**10** 120-347V		**BZ** Bronze
SF300-SCT-S-G2-10-BZ	**SF300** 205-255-300W	**SCT** 3000K/4000K/5000K	**S** Slipfitter	**G2**	**10** 120-347V		**BZ** Bronze
SF300-SCT-T-G2-10-BZ	**SF300** 205-255-300W	**SCT** 3000K/4000K/5000K	**T** Trunnion	**G2**	**10** 120-347V		**BZ** Bronze

KEENE



Adjustable Slim Wall Pack



Slim, low profile LED design

Features a discreet design that will complement any building exterior.

Adjustable Slim Wall Pack **Example: ASW25-SCT-G1-8-PCB-BW**

Ordering Code	Luminaire	Color Temperature	Voltage	Options	Finish
ASW25-SCT-G1-8-PCB-BW	**ASW25** 15-20-25W	**SCT** 3000K/4000K/5000K	**8** 120-277V	**PCB** Photocell	**BW** Brown Gray
ASW75-SCT-G1-8-PCB-BW	**ASW75** 45-60-75W	**SCT** 3000K/4000K/5000K	**8** 120-277V	**PCB** Photocell	**BW** Brown Gray



LytePro Wall

Designed for projects, built for stock

LytePro LED wall sconces feature outstanding value in compact, architectural design.

LytePro Wall

Example: LPW7-10-NW-G3-2-120-BK

Ordering Code	Family	Wattage	Color Temp./Generation	Distr.	Voltage	Photocontrol	Finish
LPW7-G3-8-BZ	LPW7		G3 Generation 3		8 120-277V		BZ Bronze
LPW7-G3-8-DGY	LPW7		G3 Generation 3		8 120-277V		DGY Dark Gray
LPW7-10-NW-G3-2-120-BK	LPW7	10 10W	NW-G3 Neutral White 4000K 70CRI Gen3	2 Type 2	120 120V		BK Black
LPW7-10-NW-G3-2-120-BZ	LPW7	10 10W	NW-G3 Neutral White 4000K 70CRI Gen3	2 Type 2	120 120V		BZ Bronze
LPW7-10-NW-G3-2-120-DGY	LPW7	10 10W	NW-G3 Neutral White 4000K 70CRI Gen3	2 Type 2	120 120V		DGY Dark Gray
LPW7-10-NW-G3-2-UNV-BK	LPW7	10 10W	NW-G3 Neutral White 4000K 70CRI Gen3	2 Type 2	UNV 120V		BK Black
LPW7-10-NW-G3-2-UNV-BZ	LPW7	10 10W	NW-G3 Neutral White 4000K 70CRI Gen3	2 Type 2	UNV 120-277V		BZ Bronze
LPW7-10-NW-G3-2-UNV-DGY	LPW7	10 10W	NW-G3 Neutral White 4000K 70CRI Gen3	2 Type 2	UNV 120-277V		DGY Dark Gray
LPW7-10-NW-G3-2-UNV-MGY	LPW7	10 10W	NW-G3 Neutral White 4000K 70CRI Gen3	2 Type 2	UNV 120-277V		MGY Med. Gray
LPW7-10-NW-G3-2-UNV-WH	LPW7	10 10W	NW-G3 Neutral White 4000K 70CRI Gen3	2 Type 2	UNV 120-277V		WH White
LPW7-10-WW-G3-2-120-BZ	LPW7	10 10W	WW-G3 Warm White 3000K 70CRI Gen3	2 Type 2	UNV 120-277V		BZ Bronze
LPW7-10-WW-G3-2-UNV-BK	LPW7	10 10W	WW-G3 Warm White 3000K 70CRI Gen3	2 Type 2	120 120V		BK Black
LPW7-10-WW-G3-2-UNV-BZ	LPW7	10 10W	WW-G3 Warm White 3000K 70CRI Gen3	2 Type 2	UNV 120-277V		BZ Bronze
LPW7-10-WW-G3-2-UNV-DGY	LPW7	10 10W	WW-G3 Warm White 3000K 70CRI Gen3	2 Type 2	UNV 120-277V		DGY Dark Gray
LPW7-10-WW-G3-2-UNV-MGY	LPW7	10 10W	WW-G3 Warm White 3000K 70CRI Gen3	2 Type 2	UNV 120-277V		MGY Med. Gray
LPW7-10-WW-G3-2-UNV-WH	LPW7	10 10W	WW-G3 Warm White 3000K 70CRI Gen3	2 Type 2	UNV 120-277V		WH White
LPW16-G3-8-BZ	LPW16		G3 Generation 3		8 120-277V		BZ Bronze
LPW16-G3-8-DGY	LPW16		G3 Generation 3		8 120-277V		DGY Dark Gray
LPW16-20-NW-G3-3-120-BK	LPW16	20 20W	SCT 3000K/4000K/5000K	3 Type 3	120 120V		BK Black
LPW16-20-NW-G3-3-120-BZ	LPW16	20 20W	SCT 3000K/4000K/5000K	3 Type 3	120 120V		BZ Bronze
LPW16-20-NW-G3-3-HVU-BZ	LPW16	20 20W	SCT 3000K/4000K/5000K	3 Type 3	HVU 347-480V		BZ Bronze
LPW16-20-NW-G3-3-UNV-BK	LPW16	20 20W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BK Black
LPW16-20-NW-G3-3-UNV-BZ	LPW16	20 20W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW16-20-NW-G3-3-UNV-DGY	LPW16	20 20W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		DGY Dark Gray
LPW16-20-NW-G3-3-UNV-MGY	LPW16	20 20W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		MGY Med. Gray
LPW16-20-NW-G3-3-UNV-WH	LPW16	20 20W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		WH White
LPW16-20-NW-G3-4-UNV-BK	LPW16	20 20W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW16-20-NW-G3-4-UNV-BZ	LPW16	20 20W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW16-20-NW-G3-4-UNV-MGY	LPW16	20 20W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		MGY Med. Gray
LPW16-20-NW-G3-4-UNV-WH	LPW16	20 20W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		WH White
LPW16-20-WW-G3-3-120-BZ	LPW16	20 20W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	120 120V		BZ Bronze
LPW16-20-WW-G3-3-277-PCB-BK	LPW16	20 20W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	277 277V	PCB Photocell	BK Black
LPW16-20-WW-G3-3-UNV-BK	LPW16	20 20W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		BK Black

KEENE



LytePro 7



LytePro 16



LytePro 32

LytePro Wall

Example: LPW7-10-NW-G3-2-120-BK

Ordering Code	Family	Wattage	Color Temp./Generation	Distr.	Voltage	Photocontrol	Finish
LPW16-20-WW-G3-3-UNV-BZ	LPW16	20 20W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW16-20-WW-G3-4-UNV-BK	LPW16	20 20W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW16-20-WW-G3-4-UNV-BZ	LPW16	20 20W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW16-20-WW-G3-4-UNV-MGY	LPW16	20 20W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		MGY Med. Gray
LPW16-30-NW-G3-3-120-BK	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	120 120V		BK Black
LPW16-30-NW-G3-3-120-BZ	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	120 120V		BZ Bronze
LPW16-30-NW-G3-3-HVU-WH	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	HVU 347-480V		WH White
LPW16-30-NW-G3-3-UNV-BK	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BK Black
LPW16-30-NW-G3-3-UNV-BZ	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW16-30-NW-G3-3-UNV-DGY	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		DGY Dark Gray
LPW16-30-NW-G3-3-UNV-MGY	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		MGY Med. Gray
LPW16-30-NW-G3-3-UNV-WH	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		WH White
LPW16-30-NW-G3-4-120-BK	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	120 120V		BK Black
LPW16-30-NW-G3-4-120-PCB-MGY	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	120 120V	PCB Photocell	MGY Med. Gray
LPW16-30-NW-G3-4-UNV-BK	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW16-30-NW-G3-4-UNV-BZ	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW16-30-NW-G3-4-UNV-DGY	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		DGY Dark Gray
LPW16-30-NW-G3-4-UNV-MGY	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		MGY Med. Gray
LPW16-30-NW-G3-4-UNV-WH	LPW16	30 30W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		WH White
LPW16-30-WW-G3-3-120-BK	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	120 120V		BK Black
LPW16-30-WW-G3-3-UNV-BK	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		BK Black
LPW16-30-WW-G3-3-UNV-BZ	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW16-30-WW-G3-3-UNV-DGY	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		DGY Dark Gray
LPW16-30-WW-G3-3-UNV-MGY	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		MGY Med. Gray
LPW16-30-WW-G3-3-UNV-WH	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		WH White
LPW16-30-WW-G3-4-120-BZ	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	120 120V		BZ Bronze
LPW16-30-WW-G3-4-UNV-BK	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW16-30-WW-G3-4-UNV-BZ	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW16-30-WW-G3-4-UNV-MGY	LPW16	30 30W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		MGY Med. Gray
LPW16-50-NW-G3-2-HVU-WH	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	2 Type 2	HVU 347-480V		WH White
LPW16-50-NW-G3-3-120-BZ	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	120 120V		BZ Bronze
LPW16-50-NW-G3-3-HVU-BZ	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	HVU 347-480V		BZ Bronze
LPW16-50-NW-G3-3-UNV-BK	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BK Black



LytePro Wall (continued)

Designed for projects, built for stock

LytePro LED wall sconces feature outstanding value in compact, architectural design.

LytePro Wall

Example: LPW7-10-NW-G3-2-120-BK

Ordering Code	Family	Wattage	Color Temp./Generation	Distr.	Voltage	Photocontrol	Finish
LPW16-50-NW-G3-3-UNV-BZ	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW16-50-NW-G3-3-UNV-DGY	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		DGY Dark Gray
LPW16-50-NW-G3-3-UNV-MGY	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		MGY Med. Gray
LPW16-50-NW-G3-3-UNV-WH	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		WH White
LPW16-50-NW-G3-4-UNV-BK	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW16-50-NW-G3-4-UNV-BZ	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW16-50-NW-G3-4-UNV-DGY	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		DGY Dark Gray
LPW16-50-NW-G3-4-UNV-MGY	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		MGY Med. Gray
LPW16-50-NW-G3-4-UNV-WH	LPW16	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		WH White
LPW16-50-WW-G3-3-UNV-BK	LPW16	50 50W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		BK Black
LPW16-50-WW-G3-3-UNV-BZ	LPW16	50 50W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW16-50-WW-G3-3-UNV-MGY	LPW16	50 50W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		MGY Med. Gray
LPW16-50-WW-G3-4-UNV-BK	LPW16	50 50W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW16-50-WW-G3-4-UNV-BZ	LPW16	50 50W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW16-50-WW-G3-4-UNV-MGY	LPW16	50 50W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		MGY Med. Gray
LPW32-G3-8-BZ	LPW32		G3 Generation 3		8 120-277V		BZ Bronze
LPW32-G3-8-DGY	LPW32		G3 Generation 3		8 120-277V		DGY Dark Gray
LPW32-50-NW-G3-3-UNV-BZ	LPW32	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW32-50-NW-G3-3-UNV-MGY	LPW32	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		MGY Med. Gray
LPW32-50-NW-G3-3-UNV-WH	LPW32	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		WH White
LPW32-50-NW-G3-4-UNV-BK	LPW32	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW32-50-NW-G3-4-UNV-BZ	LPW32	50 50W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW32-50-WW-G3-3-UNV-BZ	LPW32	50 50W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW32-50-WW-G3-4-UNV-BZ	LPW32	50 50W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW32-70-NW-G3-3-HVU-BK	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	HVU 347-480V		BK Black
LPW32-70-NW-G3-3-HVU-BZ	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	HVU 347-480V		BZ Bronze
LPW32-70-NW-G3-3-HVU-DGY	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	HVU 347-480V		DGY Dark Gray
LPW32-70-NW-G3-3-UNV-BK	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BK Black
LPW32-70-NW-G3-3-UNV-BK	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BK Black
LPW32-70-NW-G3-3-UNV-BZ	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW32-70-NW-G3-3-UNV-DGY	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		DGY Dark Gray
LPW32-70-NW-G3-3-UNV-MGY	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		MGY Med. Gray

KEENE



LytePro 7



LytePro 16



LytePro 32

LytePro Wall

Example: LPW7-10-NW-G3-2-120-BK

Ordering Code	Family	Wattage	Color Temp./Generation	Distr.	Voltage	Photocontrol	Finish
LPW32-70-NW-G3-3-UNV-WH	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		WH White
LPW32-70-NW-G3-4-HVU-BZ	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	HVU 347-480V		BZ Bronze
LPW32-70-NW-G3-4-UNV-BK	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW32-70-NW-G3-4-UNV-BZ	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW32-70-NW-G3-4-UNV-DGY	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		DGY Dark Gray
LPW32-70-NW-G3-4-UNV-MGY	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		MGY Med. Gray
LPW32-70-NW-G3-4-UNV-WH	LPW32	70 70W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		WH White
LPW32-70-WW-G3-3-UNV-BZ	LPW32	70 70W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW32-70-WW-G3-3-UNV-DGY	LPW32	70 70W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		DGY Dark Gray
LPW32-70-WW-G3-3-UNV-WH	LPW32	70 70W	WW-G3 Warm White 3000K 70CRI Gen3	3 Type 3	UNV 120-277V		WH White
LPW32-70-WW-G3-4-UNV-BK	LPW32	70 70W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW32-90-NW-G3-3-HVU-BZ	LPW32	90 90W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	HVU 347-480V		BZ Bronze
LPW32-90-NW-G3-3-UNV-BK	LPW32	90 90W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BK Black
LPW32-90-NW-G3-3-UNV-BZ	LPW32	90 90W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		BZ Bronze
LPW32-90-NW-G3-3-UNV-DGY	LPW32	90 90W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		DGY Dark Gray
LPW32-90-NW-G3-3-UNV-WH	LPW32	90 90W	NW-G3 Neutral White 4000K 70CRI Gen3	3 Type 3	UNV 120-277V		WH White
LPW32-90-NW-G3-4-UNV-BK	LPW32	90 90W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW32-90-NW-G3-4-UNV-BZ	LPW32	90 90W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		BZ Bronze
LPW32-90-NW-G3-4-UNV-MGY	LPW32	90 90W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		MGY Med. Gray
LPW32-90-NW-G3-4-UNV-WH	LPW32	90 90W	NW-G3 Neutral White 4000K 70CRI Gen3	4 Type 4	UNV 120-277V		WH White
LPW32-90-WW-G3-4-UNV-BK	LPW32	90 90W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		BK Black
LPW32-90-WW-G3-4-UNV-MGY	LPW32	90 90W	WW-G3 Warm White 3000K 70CRI Gen3	4 Type 4	UNV 120-277V		MGY Med. Gray

Accessories	
LPWCVRPLT-BK	Universal wall cover mounting plate, Black
LPWCVRPLT-BZ	Universal wall cover mounting plate, Bronze
LPWCVRPLT-DGY	Universal wall cover mounting plate, Dark Gray
LPWCVRPLT-MGY	Universal wall cover mounting plate, Medium Gray
LPWCVRPLT-WH	Universal wall cover mounting plate, White



LytePro Area

Your site lighting pro.
Delivering on value and performance.

LytePro Area

Example: LPA-A06-740-T3-UNV-FAWS-TRPC-BZ

Ordering Code	Family	Config.	CRI/CCT	Distribution	Voltage	Lighting Controls	Electrical Controls	Finish
LPA-A06-740-T3-UNV-FAWS-TRPC-BZ	**LPA**	**A06** 12,000 lumens	**740** 70 CRI, 4000K	**T3** Type 3 Medium	**UNV** 120-277V	**FAWS** Field Adjustable Wattage Selector	**TRPC** 7-Pin twist lock w/ 0-10V & On/Off Photocell (PH8)	**BZ** Bronze
LPA-A06-740-T4-UNV-FAWS-TRPC-BZ	**LPA**	**A06** 12,000 lumens	**740** 70 CRI, 4000K	**T4** Type 4 Medium	**UNV** 120-277V	**FAWS** Field Adjustable Wattage Selector	**TRPC** 7-Pin twist lock w/ 0-10V & On/Off Photocell (PH8)	**BZ** Bronze
LPA-A11-740-T3-UNV-FAWS-TRPC-BZ	**LPA**	**A11** 29,000 lumens	**740** 70 CRI, 4000K	**T3** Type 3 Medium	**UNV** 120-277V	**FAWS** Field Adjustable Wattage Selector	**TRPC** 7-Pin twist lock w/ 0-10V & On/Off Photocell (PH8)	**BZ** Bronze
LPA-A11-740-T4-UNV-FAWS-TRPC-BZ	**LPA**	**A11** 29,000 lumens	**740** 70 CRI, 4000K	**T4** Type 4 Medium	**UNV** 120-277V	**FAWS** Field Adjustable Wattage Selector	**TRPC** 7-Pin twist lock w/ 0-10V & On/Off Photocell (PH8)	**BZ** Bronze

KEENE



Garage & Canopy

Compact and efficient, **built to last**

Slim and durable with a lightweight design, this luminaire provides you with a visually appealing lighting experience.

Garage & Canopy Dual Select

Example: GC60-SCT-G2-SM-5-10-BZ

Ordering Code	Luminaire	Color Temperature	Gen.	Mounting	Distribution	Voltage	Finish
GC60-SCT-G2-SM-5-10-BZ	GC60 28-40-60W	SCT 3000K/4000K/5000K	G2	SM Surface	5 Type 5	10 120-347V	BZ Bronze
GC90-SCT-G2-SM-5-10-BZ	GC90 70-80-90W	SCT 3000K/4000K/5000K	G2	SM Surface	5 Type 5	10 120-347V	BZ Bronze
GCR60-SCT-G2-SM-5-10-BZ	GCR60 28-40-60W	SCT 3000K/4000K/5000K	G2	SM Surface	5 Type 5	10 120-347V	BZ Bronze
GCR90-SCT-G2-SM-5-10-BZ	GCR90 70-80-90W	SCT 3000K/4000K/5000K	G2	SM Surface	5 Type 5	10 120-347V	BZ Bronze

Accessory	
GC60/90-MH10	MH10 hand-held wireless remote



LytePro Garage and Canopy

Easy to specify, easy to install and easy on your budget


LytePro Garage and Canopy **Example: LPGC-A03-840-5SQ-SUR-UNV-MG**

Ordering Code	Voltage	Dimming Controls	Uplight	Finish
Common features: 6,000 lumens, 80 CRI, 4000K, type 5 square, surface mounted				
LPGC-A03-840-5SQ-SUR-UNV-MG	**UNV** 120-277V			**MG** Medium gray (opaque)
LPGC-A03-840-5SQ-SUR-UNV-WH	**UNV** 120-277V			**WH** Luminous white (translucent)
LPGC-A03-840-5SQ-SUR-UNV-UPL-WH	**UNV** 120-277V		**UPL** Uplight	**WH** Luminous white (translucent)
LPGC-A03-840-5SQ-SUR-UNV-BLFPMW-MG	**UNV** 120-277V	**BLFPMW** Bi-level set at 20% dimming, field programmable, microwave motion sensor		**MG** Medium gray (opaque)
LPGC-A03-840-5SQ-SUR-UNV-BLFPMW-WH	**UNV** 120-277V	**BLFPMW** Bi-level set at 20% dimming, field programmable, microwave motion sensor		**WH** Luminous white (translucent)
LPGC-A03-840-5SQ-SUR-UNV-BLFPMW-UPL-WH	**UNV** 120-277V	**BLFPMW** Bi-level set at 20% dimming, field programmable, microwave motion sensor	**UPL** Uplight	**WH** Luminous white (translucent)
LPGC-A03-840-5SQ-SUR-UNV-WIAPLW-MG	**UNV** 120-277V	**WIAPLW** Wireless Interact, low mounting height (7-15')		**MG** Medium gray (opaque)
LPGC-A03-840-5SQ-SUR-UNV-WIAPLW-WH	**UNV** 120-277V	**WIAPLW** Wireless Interact, low mounting height (7-15')		**WH** Luminous white (translucent)
LPGC-A03-840-5SQ-SUR-UNV-WIAPLW-UPL-WH	**UNV** 120-277V	**WIAPLW** Wireless Interact, low mounting height (7-15')	**UPL** Uplight	**WH** Luminous white (translucent)
LPGC-A03-840-5SQ-SUR-HVU-MG	**HVU** 347-480V			**MG** Medium gray (opaque)
LPGC-A03-840-5SQ-SUR-HVU-WH	**HVU** 347-480V			**WH** Luminous white (translucent)
LPGC-A03-840-5SQ-SUR-HVU-UPL-WH	**HVU** 347-480V		**UPL** Uplight	**WH** Luminous white (translucent)
Common features: 8,000 lumens, 80 CRI, 4000K, type 5 square, surface mounted				
LPGC-A04-840-5SQ-SUR-UNV-MG	**UNV** 120-277V			**MG** Medium gray (opaque)
LPGC-A04-840-5SQ-SUR-UNV-WH	**UNV** 120-277V			**WH** Luminous white (translucent)
LPGC-A04-840-5SQ-SUR-UNV-UPL-WH	**UNV** 120-277V		**UPL** Uplight	**WH** Luminous white (translucent)
LPGC-A04-840-5SQ-SUR-UNV-BLFPMW-MG	**UNV** 120-277V	**BLFPMW** Bi-level set at 20% dimming, field programmable, microwave motion sensor		**MG** Medium gray (opaque)

KEENE



Luminous white (translucent)



Medium gray (opaque)

LytePro Garage and Canopy

Example: LPGC-A03-840-5SQ-SUR-UNV-MG

Ordering Code	Voltage	Dimming Controls	Uplight	Finish
LPGC-A04-840-5SQ-SUR-UNV-BLFPMW-WH	**UNV** 120-277V	**BLFPMW** Bi-level set at 20% dimming, field programmable, microwave motion sensor		**WH** Luminous white (translucent)
LPGC-A04-840-5SQ-SUR-UNV-BLFPMW-UPL-WH	**UNV** 120-277V	**BLFPMW** Bi-level set at 20% dimming, field programmable, microwave motion sensor	**UPL** Uplight	**WH** Luminous white (translucent)
LPGC-A04-840-5SQ-SUR-UNV-WIAPLW-MG	**UNV** 120-277V	**WIAPLW** Wireless Interact, low mounting height (7-15')		**MG** Medium gray (opaque)
LPGC-A04-840-5SQ-SUR-UNV-WIAPLW-WH	**UNV** 120-277V	**WIAPLW** Wireless Interact, low mounting height (7-15')		**WH** Luminous white (translucent)
LPGC-A04-840-5SQ-SUR-UNV-WIAPLW-UPL-WH	**UNV** 120-277V	**WIAPLW** Wireless Interact, low mounting height (7-15')	**UPL** Uplight	**WH** Luminous white (translucent)
LPGC-A04-840-5SQ-SUR-HVU-MG	**HVU** 347-480V			**MG** Medium gray (opaque)
LPGC-A04-840-5SQ-SUR-HVU-WH	**HVU** 347-480V			**WH** Luminous white (translucent)
LPGC-A04-840-5SQ-SUR-HVU-UPL-WH	**HVU** 347-480V		**UPL** Uplight	**WH** Luminous white (translucent)

As the complexity of your projects skyrockets, faster delivery becomes increasingly important.

The Ledalite 10-day QuickShip program includes all of our high performance and award-winning LED linear, recessed, surface, and slot luminaire families.

Click or scan here
to view the Ledalite
Design ready brochure





Day-Brite CFI FBY High Bay (page 18)



Day-Brite CFI FluxPanel (page 8)



Day-Brite CFI FluxGrid (page 14)



Lightolier LyteProfile (page 2)



Lightolier ModuLyte (page 4)



Lightolier Commercial Retrofit Downlight (page 6)



Keene LytePro Wall (page 30)



Keene Garage & Canopy (page 35)

GENLYTE SOLUTIONS

a signify business

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone 800-555-0500

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.

SGn-2327BR-Design-Ready-catalog-en-ca 11/24