



GENLYTE
SOLUTIONS

a signify business

Office Product Guide

2025

Tackle your lighting project quickly

Tight project timelines can't hold you back; get quality lighting delivered within 5-10 shipping days. Our solutions can light the way for your next project with the Design Ready portfolio.

The selected QuickShip high performance luminaires from Genlyte Solutions brands include Lightolier, Day-Brite CFI, and Keene offerings.

Illuminate your space with ease

Genlyte Solutions provides the lighting solution for every project. Whether it's lighting and connecting your public spaces, giving your space an energy-saving upgrade, or working on a yet-to-be constructed project, we've got you covered. Our Design Ready portfolio makes it easy for you to find highly configurable lighting with modern designs within your timeline and your budget.



Design Build

Our stocking solutions are
now ready to go with your
stock and design ready needs



Stock ready

Stock and Flow
Ships in **2 days**



Design ready


Design Build
Ships in **5-10 days**

Office applications

Around the clock lighting solutions

Effective lighting design is crucial for office spaces, impacting staff morale, focus, and comfort. Well-designed lighting not only enhances concentration and productivity but also improves employees' mood, satisfaction, and well-being by minimizing eye strain and discomfort.

At **Genlyte Solutions**, our portfolio of lighting brands offers the perfect solutions to create an optimal office environment. Explore our product suggestions to elevate your workspace and foster a more productive and comfortable atmosphere for your team.



ModuLyte

Benefit from budget-friendly, commercial grade quality downlighting

Frame-optional design architecture and modular optics that can be field or factory-installed, you can be confident that ModuLyte is equipped to support a variety of project conditions.

Meet deadlines and project schedules without the stress by quickly connecting the light engine to its driver via a screw-on Communications Multipurpose Plenum (CPM) cable.

Selectable CCT and lumen output options create peace-of-mind during design and installation. Convenient switches make it easy for contractors to toggle between options to ensure lighting creates the right environment on any project.



Product Highlight

Flexibility at your fingertips

LIGHTOLIER

Product Highlight


Slim, sturdy, and selectable

Day-Brite
CFI

Selectable Troffer (DSRT)

Robust low glare luminaire designed to provide three lumen and three CCT field selectable options per size at 80CRI. Available for use in recessed, suspended, and surface mount applications with optional daylight and occupancy sensor.

DSRT is 120-277V (UNV), with 0-10V dimming, and a 3in deep housing.



Stock ready 2 day shipping

Design ready 5-10 day shipping

Lobby & Meeting Rooms



Reception Area

Day-Brite
CFI



FluxGrid Recessed

- High quality and performance for optimum energy savings
- Drivers and boards are easily accessible from below
- 3-1/8" deep low profile configuration
- Wireless control options available

Stock ready

Design ready

Day-Brite
CFI



FluxSpace Strip

- 4 different styles in a 4" housing
- State of the art smart lighting capabilities with adaptive and future proof controls
- Endless possibilities for a host of applications

Design ready

Meeting and Conference Rooms

Day-Brite
CFI




FluxGrid Recessed

- High quality and performance for optimum energy savings
- Drivers and boards are easily accessible from below
- 3-1/8" deep low profile configuration
- Wireless control options available

Stock ready

Design ready

Day-Brite
CFI



Selectable Troffer (DSRT)

- Strong and well constructed 3in deep 5VA housing
- Field selectable lumens and CCT opt.
- Polystyrene diffuser provides visual comfort, even light distribution and high efficiency illumination
- Sensor versions available

Stock ready



Kitchen & Retrofit Solutions

Kitchen

Day-Brite
CFI




FluxStream Strip

- 2', 3', 4' and 8' tandem lengths available to accommodate many field applications
- Frosted acrylic diffuser provides wide light distribution, superior glare control
- Diffuser and LED plate snap into place allowing tool-free access

Stock
ready

Design
ready

Day-Brite
CFI



SofTrace Recessed

- Ease of maintenance
- Optional occupancy and daylighting sensors
- Uniform, glare free light distribution
- Achieve energy efficiency targets and reduce energy-related costs

Design
ready

Day-Brite
CFI



SDS Selectable Strip

- Frosted glare-free lens
- Simple mounting method
- CCT & Lumen selectability
- Durable construction
- Ease of installation and maintenance

Stock
ready

Retrofit Solutions

Day-Brite
CFI



NWL Selectable Wraparound

- White polycarbonate housing
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting incl.
- Field CCT selectable for 3000K, 3500K or 4000K

Stock
ready

Day-Brite
CFI



SDS Selectable Strip

- Frosted glare-free lens
- Simple mounting method
- CCT & Lumen selectability
- Durable construction
- Ease of installation and maintenance

Stock
ready

LIGHTOLIER



Commercial Retrofit

- 4 sizes for applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock
ready

Stock ready 2 day shipping

Design ready 5-10 day shipping

Social Area & Outdoor



Social Space & Gathering Area

LIGHTOLIER



Commercial Retrofit

- 4 sizes to accommodate applications with varying ceiling heights
- Simplified installation
- 90 CRI for crisp color clarity
- 120-347V (UN3) voltage sensing driver
- 0-10V Dimming

Stock ready

LIGHTOLIER



ModuLyte

- Field interchangeable downlight (wide/medium) and lensed wall wash optics
- 59° physical cutoff provides reduced high angle glare and low UGR to optimize visual comfort
- Field selectable for 5 CCT's and up to 3 lumen levels

Stock ready

Design ready

Outdoor & Complex Parking

KEENE



LytePro Area

- Mounting to round or square pole without need for accessories
- Large bolt spacing range for easy retrofit application
- Button or twist-lock photocell, motion response, and field adjustable wattage

Stock ready

Design ready

KEENE



LytePro Garage & Canopy

- SpiroGuide light engine that reduces glare and increases uniformity
- Luminous white uplight option with a halo bezel that glows
- Dimming controls and UL924 emergency options
- Lightweight and "click!" no-screw surface mounting

Design ready

KEENE



LytePro Wall

- Low-profile design
- Replacement for incandescent, compact fluorescent and HID lamp sources up to 320W
- Optical distributions offer full cutoff performance and excellent uniformity
- Mounts to a variety of junction box types or fastens directly to wall for seamless retrofitting

Stock ready

Design ready



Day-Brite
CFI



FluxStream Strip

- 2', 3', 4' and 8' tandem lengths available to accommodate many field applications
- Frosted acrylic diffuser provides wide light distribution, superior glare control
- Diffuser and LED plate snap into place allowing tool-free access

Stock
ready

Design
ready

Day-Brite
CFI



FluxStream Industrial

- Ease of installation and maintenance
- Convenient specification
- Delivers up to 134 LPW
- Standard 0-10V dimming
- Multiple CCT and lumen options
- Multiple mounting methods

Stock
ready

Design
ready

Day-Brite
CFI



FluxStream Sealed

- Achieve energy efficiency targets and reduce energy-related costs
- Ease of maintenance
- Long lasting performance
- Reliable performance up to 122 LPW
- Optional occupancy sensors

Stock
ready

Design
ready

Day-Brite
CFI



SDS Selectable Strip

- Frosted glare-free lens
- Simple mounting method
- CCT & Lumen selectability
- Durable construction
- Ease of installation and maintenance

Stock
ready

Get started with the Design Ready catalog



Ready to create your vision?

Check out the Design Ready website and catalog for ordering information on the product families fit for bringing your Design Build project to life. Scan or click the QR code to learn more.







© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone 800-555-0500

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.