



# Find the right solution!


### Day-Brite

FluxPanel					
Catalog Number	Description	12NC	DLC	Product Image	
● 1FPZ38B835-4-DS-UNV-DIM	1x4, 3800 lumen, 80CRI, 3500K, Smooth Diffuser, UNV 120-277V, 0-10V	912401609015	PL1445PGWPJQ		
● 1FPZ38B840-4-DS-UNV-DIM	1x4, 3800 lumen, 80CRI, 4000K, Smooth Diffuser, UNV 120-277V, 0-10V	828820216595	-		
● 2FPZ38B835-2-DS-UNV-DIM	2x2, 3800 lumen, 80CRI, 3500K, Smooth Diffuser, UNV 120-277V, 0-10V	912401609018	-		
● 2FPZ38B840-2-DS-UNV-DIM	2x2, 3800 lumen, 80CRI, 4000K, Smooth Diffuser, UNV 120-277V, 0-10V	912401609019	PLNUL3YZ9JHL		
● 2FPZ42B835-4-DS-UNV-DIM	2x4, 4200 lumen, 80CRI, 3500K, Smooth Diffuser, UNV 120-277V, 0-10V	912401609021	-		
● 2FPZ42B840-4-DS-UNV-DIM	2x4, 4200 lumen, 80CRI, 4000K, Smooth Diffuser, UNV 120-277V, 0-10V	912401609022	PLCNETQY3S2C		
1FPZ38B835-4-DS-UNV-DIM-SWZCS	1x4 flat panel troffer, clean room rated, 38L, 3W, 35K, SR with Interact Pro sensor	-	-		
1FPZ38B840-4-DS-UNV-DIM-SWZCS	1x4 flat panel troffer, clean room rated, 38L, 3W, 4K, SR with Interact Pro sensor	-	-		
2FPZ38B835-2-DS-UNV-DIM-SWZCS	2x2 flat panel troffer, clean room rated, 38L, 33W, 35K, SR with Interact Pro sensor	-	-		
2FPZ38B840-2-DS-UNV-DIM-SWZCS	2x2 flat panel troffer, clean room rated, 38L, 33W, 4K, SR with Interact Pro sensor	-	-		
2FPZ42B835-4-DS-UNV-DIM-SWZCS	2x4 flat panel troffer, clean room rated, 42L, 4W, 35K, SR with Interact Pro sensor	-	-		
2FPZ42B84-4-DS-UNV-DIM-SWZCS	2x4 flat panel troffer, clean room rated, 42L, 4W, 4K, SR with Interact Pro sensor	-	-		
2FGXG38B835-2-RS-UNV-DIM	2x2, 3800 lumen, 80CRI, 3500K, round smooth lens, UNV 120-277V, 0-10V	912401607975	P5EN0ZHA		
2FGXG38B840-2-RS-UNV-DIM	2x2, 3800 lumen, 80CRI, 4000K, round smooth lens, UNV 120-277V, 0-10V	912401607978	P9G2RBR9		


● Cleanroom & NSF rated as standard

# Design Build Contractor Guide


Day-Brite

FCY LED High Bay				
Catalog Number	Description	12NC	DLC	Product Image
FCY15L8CST-UNV-DIM	15000 lm, 80CRI, Color Select 4000K/5000K, 0-10V, UNV 120-347V	912401590942	-	
FCY22L8CST-UNV-DIM	22000 lm, 80CRI, Color Select 4000K/5000K, 0-10V, UNV 120-347V	912401590943	PL45VSJUE9A	
FCY29L8CST-UNV-DIM	29000 lm, 80CRI, Color Select 4000K/5000K, 0-10V, UNV 120-347V	912401590944	PL5YOSU34LN	
FCY-PENHGR	Pendant hanger accessory (adds 2.5" to height)	912401590950	-	
FCY-SBK	Surface bracket kit (adds 2.5" to height)	912401590948	-	


Day-Brite

HCY LED High Bay				
Catalog Number	Description	12NC	DLC	Product Image
HCY1421L8CST-UN3-DIM	High bay 14,000/21,000 lm, 80CRI, color select 4000K/5000K, 0-10V UNV, 120-347V	911401874482	PLO1HSZT5F	
HCY2833L8CST-UN3-DIM	High bay 28,000/33,000 lumen, 80CRI, color select 4000K/5000K, 0-10V UNV, 120-347V	911401874582	PLJXJYXIX6N	
HCY2-PRLG	16" clear polycarbonate reflector for HCY28L and HCY33L	911401874282	-	
HCY2-PRSM	16" clear polycarbonate reflector for HCY14L and HCY21L	911401874382	-	
HCY-REMOTE	Remote programmer for sensor	911401855781	-	
HCY-SENSOR	HCY sensor accessory	911401874682	-	
HCY-SURFACE BKT LG	Surface mount bracket for HCY28L and HCY33L	911401856181	-	
HCY-SURFACE BKT SM	Surface mount bracket for HCY14L and HCY21L	911401856081	-	


Day-Brite

FBY LED High Bay				
Catalog Number	Description	12NC	DLC	Product Image
FBY18L850-UNV-LFA-SWZCSH	18,000 lm, 80CRI, 5000K, UNV 120-277V, Frosted Lens, Interact Pro	912401610448	-	
FBY18L840-UNV-LFA-SWZCSH	18,000 lm, 80CRI, 4000K, UNV 120-277V, Frosted Lens, Interact Pro	912401608906	-	


Day-Brite

FBX LED High Bay				
Catalog Number	Description	12NC	DLC	Product Image
FBX160LL40-UNV-LFA-SWZCSH	LED highbay 2x2, 16L, NOM., 11W, Frosted Lens, Interact Pro	-	-	
FBX240LL40-UNV-LFA-SWZCSH	LED highbay 2x2, 24L, NOM., 11W, Frosted Lens, Interact Pro	-	-	

Day-Brite


SDS LED Selectable Strip				
Catalog Number	Description	12NC	DLC	Product Image
SDS21224L8CST-UNV-DIM	SDS Selectable Strip, 2', 1200/1800/2400 lumen, 3500K/4000K/5000K (CRI 80), UNV, Dimmable	911401870782	PLV59H45ZE1C	
SDS42448L8CST-UNV-DIM	SDS Selectable Strip, 4', 2430/3640/4850 lumen, 3500K/4000K/5000K (CRI 80), UNV, Dimmable	911401870882	PLENTW75IZBC	
SDS84998L8CST-UNV-DIM	SDS Selectable Strip, 8', 4900/7350/9800 lumen, 3500K/4000K/5000K (CRI 80), UNV, Dimmable	911401870982	PLRQ7P8H9L	

Day-Brite


VTS LED Sealed Strip				
Catalog Number	Description	12NC	DLC	Product Image
VTS42856L8CST-UN3-DIM	VaportiteDS 4ft 28/42/56lm 3CCT 120-347V	911401825185	S-XGL7UR	
VTS880130L8CST-UN3-DIM	VaportiteDS 8ft 80/110/130lm 3CCT 120-347V	911401825385	S-EAOD4I	

# Design Build Contractor Guide


Day-Brite

FluxStream LED Wraparound				
Catalog Number	Description	12NC	DLC	Product Image
FSW440L835-UNV-DIM	FluxStream Wraparound, 4' length, 4000lm, 80CRI, 3500K, universal voltage 120-277V, 0-10V dimming	912401282849	S-7FB35E	
FSW440L840-UNV-DIM	FluxStream Wraparound, 4' length, 4000lm, 80CRI, 4000K, universal voltage 120-277V, 0-10V dimming	912401282277	S-4OIM29	
FSW440L835-UNV-DIM-SWZCS	FluxStream Wraparound, 4' length, 4000lm, 80CRI, 3500K, universal voltage 120-277V, 0-10V dim., SR with Interact Pro sensor	912401607476	-	
FSW440L840-UNV-DIM-SWZCS	FluxStream Wraparound, 4' length, 4000lm, 80CRI, 4000K, universal voltage 120-277V, 0-10V dim., SR with Interact Pro sensor	912401607477	-	
FSW880L835-UNV-DIM-SWZCS	FluxStream Wraparound, 8' length, 8000lm, 80CRI, 3500K, universal voltage 120-277V, 0-10V dim., SR with Interact Pro sensor	912401607860	-	
FSW880L840-UNV-DIM-SWZCS	FluxStream Wraparound, 8' length, 8000lm, 80CRI, 4000K, universal voltage 120-277V, 0-10V dim., SR with Interact Pro sensor	912401607861	-	
FSW430L840-UNV-DIM-SWZCS	FluxStream Wraparound, 4' length, 3000lm, 80CRI, 4000K, universal voltage 120-277V, 0-10V dim., SR with Interact Pro sensor	912401607475	-	
FSW860L840-UNV-DIM-SWZCS	FluxStream Wraparound, 8' length, 6000lm, 80CRI, 4000K, universal voltage 120-277V, 0-10V dim., SR with Interact Pro sensor	912401609167	-	

Day-Brite

FluxStream LED Strip				
Catalog Number	Description	12NC	DLC	Product Image
FSS440L835-UNV-DIM	4' Length, 4000lm, 80CRI, 3500K, UNV 120-277V, 0-10V	912401283415	PKO8S3FZ	
FSS440L840-UNV-DIM	4' Length, 4000lm, 80CRI, 4000K, UNV 120-277V, 0-10V	912401283414	PYUQ9234	
FSS440L835-UNV-DIM-SWZCS	LED strip 4', 4000lm, 3W, 3500K, SR with Interact Pro sensor	912401607470	-	
FSS440L840-UNV-DIM-SWZCS	LED strip 4', 4000lm, 3W, 4000K, SR with Interact Pro sensor	912401607471	-	
FSS880L835-UNV-DIM-SWZCS	LED strip 8', 4000lm, 6W, 3500K, SR with Interact Pro sensor	912401609547	-	
FSS880L840-UNV-DIM-SWZCS	LED strip 8', 4000lm, 6W, 400K, SR with Interact Pro sensor	912401607473	-	

Day-Brite

FluxGrid Gen 2 Recessed LED				
Catalog Number	Description	12NC	DLC	Product Image
2FGXG20L835-2-RS-UNV-DIM-SWZCS	2x2, 2000lm, 80CRI, 3500K, round smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401608349	S-EIW4T3	
2FGXG20L840-2-RS-UNV-DIM-SWZCS	2x2, 2000lm, 80CRI, 4000K, round smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401608350	S-E971I5	
2FGXG30L835-2-RS-UNV-DIM-SWZCS	2x2, 3000lm, 80CRI, 3500K, round smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401608352	S-B92WQ3	
2FGXG30L840-2-RS-UNV-DIM-SWZCS	2x2, 3000lm, 80CRI, 4000K, round smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401607971	S-RHK1D6	
2FGXG38L835-4-RS-UNV-DIM-SWZCS	2x4, 3800lm, 80CRI, 3500K, round smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401608351	S-GK12HC	
2FGXG38L840-4-RS-UNV-DIM-SWZCS	2x4, 3800lm, 80CRI, 4000K, round smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401608354	S-46MNJ	
2FGXG42B835-4-FS-UNV-DIM	2x4, 4200lm, 80CRI, 3500K, flat smooth lens, UNV 120-277V, 0-10V	912401607992	PH3XEPDS	
2FGXG42B840-4-FS-UNV-DIM	2x4, 4200lm, 80CRI, 4000K, flat smooth lens, UNV 120-277V, 0-10V	912401607994	PK90XT30	
2FGXG43L835-4-RS-UNV-DIM-SWZCS	2x4, 4300 lumen, 80CRI, 3500K, round smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401607998	S-WE9JO6	
2FGXG43L840-4-RS-UNV-DIM-SWZCS	2x4, 4300 lumen, 80CRI, 4000K, round smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401608358	S-8MQ13	
2FGXG48L835-4-RS-UNV-DIM-SWZCS	2x4, 4800 lumen, 80CRI, 3500K, round smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401608196	-	
2FGXG30L835-2-FS-UNV-DIM-SWZCS	2x2, 3000 lumen, 80CRI, 3500K, flat smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401609141	S-B92WQ3	
2FGXG30L840-2-FS-UNV-DIM-SWZCS	2x2, 3000 lumen, 80CRI, 4000K, flat smooth lens, UNV 120-277V, 0-10V, Interact Pro scalable	912401609142	S-B92WQ3	



# Design Build Contractor Guide



GeoForm				
Catalog Number	Description	12NC	DLC	Product Image
GWS-A4-84-T4M-UNV-BZ	GeoForm wedge small, 5,000lm, 80CRI, 4000K, Type 4, 120-277V, bronze	-	-	
GWM-A9-84-T4M-UNV-BZ-WIAP	GeoForm wedge medium, 6,000lm, 80CRI, 4000K, Type 4, 120-277V, bronze, wireless Interact	-	-	
GWM-A9-83-T4M-UNV-BZ-WIAP	GeoForm wedge medium, 6,000lm, 80CRI, 3000K, Type 4, 120-277V, bronze, wireless Interact	-	-	



LytePro Wall				
Catalog Number	Description	12NC	DLC	Product Image
LPW7-G3-8-BZ	LPW7, 10W, 4000K, Type 2, 120-277V, Bronze textured paint	912401477096	-	
LPW7-G3-8-DGY	LPW7, 10W, 4000K, Type 2, 120-277V, Dark gray textured paint	912401477095	-	
LPW16-G3-8-DGY	LPW16, 30W, 4000K, Type 3, 120-277V, Dark gray textured paint	912401477097	S-8ZNST4	
LPW16-G3-8-BZ	LPW16, 30W, 4000K, Type 3, 120-277V, Bronze textured paint	912401477098	S-8ZNST4	
LPW32-G3-8-BZ	LPW32, 70W, 4000K, Type 3, 120-277V, Bronze textured paint	912401477101	S-ZUC1LE	
LPW32-G3-8-DGY	LPW32, 70W, 4000K, Type 3, 120-277V, Dark gray textured paint	912401477099	S-ZUC1LE	



LytePro Area				
Catalog Number	Description	12NC	DLC	Product Image
LPA-A06-740-T3-UNV-FAWS-TRPC-BZ	80W, 70CRI, 4000K, Type 3, 120-277V, Selectable Wattage, 7-Pin Twist Lock, Bronze Finish	912300004181	S-QRTP95	
LPA-A06-740-T4-UNV-FAWS-TRPC-BZ	80W, 70CRI, 4000K, Type 4, 120-277V, Selectable Wattage, 7-Pin Twist Lock, Bronze Finish	912300004183	S-T3VBNP	
LPA-A11-740-T3-UNV-FAWS-TRPC-BZ	180W, 70CRI, 4000K, Type 3, 120-277V, Selectable Wattage, 7-Pin Twist Lock, Bronze Finish	912300004185	S-P3M1XG	
LPA-A11-740-T4-UNV-FAWS-TRPC-BZ	180W, 70CRI, 4000K, Type 4, 120-277V, Selectable Wattage, 7-Pin Twist Lock, Bronze Finish	912300004187	S-MMST34	




OptiForm				
Catalog Number	Description	12NC	DLC	Product Image
OPF-S-P6-84-T4M-AR1-UNV-WIAP-BZ	LED area light with integrated Interact Pro occ/day-light sensor, 14L, 4K, type 4, 120-277V, bronze	-	-	
OPF-S-P6-84-T5M-AR1-UNV-WIAP-BZ	LED area light with integrated Interact Pro occ/day-light sensor, 14L, 4K, type 5, 120-277V, bronze	-	-	
OPF-S-P9-84-T4M-AR1-UNV-WIAP-BZ	LED area light with integrated Interact Pro occ/day-light sensor, 22L, 4K, type 4, 120-277V, bronze	-	-	
OPF-S-P9-84-T5M-AR1-UNV-WIAP-BZ	LED area light with integrated Interact Pro occ/day-light sensor, 22L, 4K, type 5, 120-277V, bronze	-	-	




Straight Square Steel Pole				
Catalog Number	Description	12NC	DLC	Product Image
SSS-4-11-D4-BRP	4" shaft, 2' straight square steel pole, 11 ga/0.120", drilled 4-way with plugs, bronze paint	-	-	

# Design Build Contractor Guide


**LIGHTOLIER**

Calculite LED				
Catalog Number	Description	12NC	DLC	Product Image
4RN	4" Non-IC Round, New construction, UNV	912400546884	-	
6RN	6" Non-IC Round, New construction, UNV	912400546896	-	
4RN-RADIO, P4RDL1835CDU	LED downlight 4", 1L, 11W, 8 CRI, 3500K, matte diffuse with white trim, Interact Pro (RF only)	-	-	
4RN-RADIO, P4RDL184CDU	LED downlight 4", 1L, 11W, 8 CRI, 4000K, matte diffuse with white trim, Interact Pro (RF only)	-	-	


**CHLORIDE**

Compac CLU/CLX/CLC				
Catalog Number	Description	12NC	DLC	Product Image
CLU2NW	Compac LED 2 Lamp Head Emergency Unit, Nickel Metal Hydride Battery, White	912401502516	-	
CLUNW	Compac LED 2 Lamp Head Emergency Unit, Nickel Cadmium Battery, Compact White Cabinet	912401502515	-	
CLXNGW	Compac LED Exit, Nickel Metal Hydride Battery, Green Letters, White	912401502519	-	
CLXNRW	Compac LED Exit, Nickel Metal Hydride Battery, Red Letters, White	912401502518	-	
CLCNGW	Compac LED Exit/unit combo, Nickel Metal Hydride Battery, Green Letters, White	912401502522	-	
CLCNRW	Compac LED Exit/unit combo, Nickel Metal Hydride Battery, Red Letters, White	912401502521	-	

**Stonco**

Garage and Canopy				
Catalog Number	Description	12NC	DLC	Product Image
GC60/90-MH10	MH10 hand-held wireless remote	911401828182	-	
GC60-SCT-G2-SM-5-10-BZ	Selectable Wattage and CCT 28-40-60W/ 3000K-4000K-5000K, Bronze Finish	911401872181	PLVXWEOIQDC5	
GC90-SCT-G2-SM-5-10-BZ	Selectable Wattage and CCT 70-80-90W/ 3000K-4000K-5000K, Bronze Finish	911401872281	PLWNEI9VD4T5	
GCR60-SCT-G1-SM-5-10-BZ	Round, Selectable Wattage and CCT 28-40-60W/ 3000K-4000K-5000K, Bronze Finish	912401591779	PL29WA55ASGM	
GCR90-SCT-G1-SM-5-10-BZ	Round, Selectable Wattage and CCT 70-80-90W/ 3000K-4000K-5000K, Bronze Finish	912401591780	PLFS6QA93NGG	

**Stonco**

SlimFlood Dual Select				
Catalog Number	Description	12NC	DLC	Product Image
SF100-SCT-T-G2-10-PCB-BZ	SlimFlood dual select 100W max, 3CCT, UNV, trunion, PCB, bronze	911401875084	-	
SF250-300-PCB	SlimFlood, 120-150-205W PCB accessory	911401875784	-	
SF205-SCT-T-G2-10-BZ	SlimFlood dual select 205W max, 3CCT, UNV, trunion, PCB, bronze	911401875484	-	
SF300-SCT-T-G2-10-BZ	SlimFlood dual select 300W max, 3CCT, UNV, trunion, PCB, bronze	911401875684	-	
SF60-SCT-Y-G2-10-PCBBZ	SlimFlood dual select 60W max, 3CCT, UNV, yoke, bronze	911401874884	-	

# Design Build Contractor Guide



EvoKit Click				
Catalog Number	Description	12NC	DLC	Product Image
269696	1x4, EvoKit Click Selectable Color & Power, 120-277V, 0-10V, 4-pack	929002749013	S-0B7W6H	
269753	2x2, EvoKit Click Selectable Color & Power, 120-277V, 0-10V, 4-pack	929002749213	S-NEJXOV	
269829	2x4, EvoKit Click Selectable Color & Power, 120-277V, 0-10V, 4-pack	929002749413	S-M0QWEN	
267674	2x2, EvoKit Click, 3200lm, 24W, 80CRI, 3500K, 120-277V, Interact Pro Scalable, 4-pack	929002740313	PG2IVTS2	
114140	2x2, EvoKit Click, 3200lm, 24W, 80CRI, 4000K, 120-277V, Interact Pro Scalable, 4-pack	929002733913	PJHZ10F4	
523621	2x2, EvoKit Click, 3200lm, 24W, 80CRI, 3500K, 120-277V, 0-10V, 4-pack	929001777713	PBBL99UF	
523647	2x2, EvoKit Click, 3200lm, 24W, 80CRI, 4000K, 120-277V, 0-10V, 4-pack	929001777913	PCGIVN5U	
523704	2x4, EvoKit Click, 4200lm, 30W, 80CRI, 3500K, 120-277V, 0-10V, 4-pack	929001778513	P1W5T132	
523720	2x4, EvoKit Click, 4200lm, 30W, 80CRI, 4000K, 120-277V, 0-10V, 4-pack	929001778713	PD7HU98K	
267682	2x4, EvoKit Click, 4200lm, 29W, 80CRI, 3500K, 120-277V, Interact Pro Scalable, 4-pack	929002740413	PO1HXM8O	
121392	2x4, EvoKit Click, 4200lm, 29W, 80CRI, 3500K, 120-277V, Interact Pro Scalable, 4-pack	929002734213	PIJTAVRN	

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.