



	Architectural		Commercial						Specialty
Rating	Best	Best	Better	Good	Good	Better	Better	Better	Better
Product Family	Patron LED	NEW! ARC	NEW! Wet Location Emergency	VLLU	VLTU	Compac LED CLU	Compac LED CLU2/3	Compac LED CLUR3	NEW! NEMA 4X
Education	Yes	Yes	-	Yes	Yes	Yes	Yes	Yes	-
Office	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Healthcare	Yes	Yes	-	Yes	Yes	Yes	Yes	Yes	-
Retail	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Industrial	-	-	Yes	-	-	-	-	-	Yes
Residential	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	-
Size (W x H x D)	7-1/2" x 11-1/8" x 3-3/4"	6-9/100" x 9-3/25" x 3-7/20"	14-13/16" x 5-5/8" x 4-1/4"	7-5/16" x 4-1/4" x 2-3/16"	10" x 5-1/8" x 4"	7-1/8" x 4-3/4" x 2-5/8"	10-1/4" x 4-3/4" x 2-5/8"	11-1/2" x 3-3/8" x 3-1/2"	16-1/2" x 6-1/4" x 6-3/4"
Housing	Die-cast aluminum	Die-cast aluminum	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Polycarbonate
CCT	-	Color select 3000/4000/5000K 5SDCM	-	6000k	6000K	5000K	5000K	5000K	-
Max Coverage/Spacing (1fc)	62 ft (two units center to center, Indoor)	45 ft	-	16 ft, 24 ft	24 ft	40 ft center to center, 36 ft single coverage	76 ft center to center, 64 ft single coverage	85 ft center to center, 60 ft single coverage	-
Mounting	Wall	Wall	Wall	Wall, ceiling	Wall, ceiling	Wall, ceiling	Wall, ceiling	Wall, ceiling	Wall
Housing Color	Dark bronze, white	Dark bronze	Grey, black	White	White	White	White	White	White, black
Lumen Output	700 @ AC mode 500 @ EM mode	1250 lm @4000K AC mode, 400 lm @4000K emergency mode	-	150 / 250 lm	200 lm	180 lm	CLU2: 524lm CLU3: 687lm	687 lm	300 lumens per head
Self Test	Standard	Standard	-	N/A	N/A	Standard	Standard	Standard	Magnetic test switch
Self Diagnostics	Standard	Standard	Optional	N/A	N/A	Standard	Standard	Standard	Optional
Temperature Range	-20°C to 50°C (-4°F to 122°F)	-30°C to 50°C (-22°F to 122°F)	Standard: -20°C to 40°C (-4°F to 104°F) Optional: -25 C to 40 C (-13 F to 104 F)	-10°C to 40°C (50°F to 104°F)	-10°C to 40°C (50°F to 104°F)	10°C to 40°C (50°F to 104°F)	10°C to 40°C (50°F to 104°F)	10°C to 40°C (50°F to 104°F)	15W: 0° C to 50° C (32 F to 122 F) 36W 10 C to 40 C (50 F to 104 F)
Remote Capability	No	No	No	✓	✓	No	✓	✓	No
Damp Listing	No	No	No	✓	✓	✓	✓	✓	✓
Wet Listing	✓	✓	✓	No	No	No	No	No	✓
Codes and Standards	UL 924 UL 1598 NFPA 70 NFPA 101 ADA Compliant	UL/cUL 924 IP65	UL 924 NFPA 101 UL listed for wet locations	UL 924 cUL Listed NFPA 101 NFPA 70 Suitable for damp locations	UL 924 cUL Listed NFPA 101 NFPA 70 Suitable for damp locations	UL 924 NFPA 101 NFPA 70	UL 924 NFPA 101 NFPA 70	UL 924 NFPA 101 NFPA 70	UL 924 NFPA 101 NEMA 4X, IP66 and NSF rated
Battery	NiCad	LiFePO4	Sealed lead acid battery	NiCad	NiCad	NiCad	NiMH	NiMH	NiCad
Lamps	LED	LED	2 x MR16 lamp heads	2 x 1W / 2x2W	2 x 1W	2 x 1W	CLU2: 2 x 2.2W CLU3: 3 x 2.2W	3 x 2.2W	2 x MR16 lamp heads
Limited Warranty	5 years	5 years	5 years on housing and all electronics 2 years prorated on battery	5 years	3 years	5 years	5 years	5 years	5 years
Link									