



	Commercial			Specialty	
Rating	Good	Good	Better	Better	Better
Product Family	Value + VLLC	Value + VLTC	Compac CLC	NEW! Wet Location Emergency	NEW! NEMA 4X Combo
Education	Yes	Yes	Yes	Yes	-
Office	Yes	Yes	Yes	Yes	-
Healthcare	Yes	Yes	Yes	Yes	Yes
Retail	Yes	Yes	Yes	Yes	-
Industrial	-	-	-	Yes	Yes
Residential	Yes	Yes	Yes	Yes	Yes
Size (W x H x D)	11-13/16" x 9-9/16" x 1-13/16"	21" x 8-1/2" x 2-9/16"	13-3/4" x 8-11/16" x 2-1/8"	12-3/8" x 13-11/16" x 5-15/16"	14-7/8" x 14-3/16" x 6"
Housing	Thermoplastic	Thermoplastic	Thermoplastic	Polycarbonate enclosed lens	Polycarbonate enclosed lens
Max Coverage/Spacing (1/fc)	16 ft	24 ft	76 ft center to center, 56 ft single coverage	-	-
Chevrons	Field selectable	Field selectable	Field selectable	Field select chevrons	Field select chevrons
Mounting	Universal	Universal	Universal	Ceiling, end, back	Ceiling, end, back, conduit
Special Wording Available	-	-	-	-	-
Faces	Single	Single	Single	Single, double	Single, double
Font Color	Red, green	Red, green	Red, green	Red. green	Red, green
Housing Color	White	White	White, black	White, black	Black, white
Lumen Output	150 lm	200 lm	220 lm	300 lm / head	300 lm/head
Self Test	-	-	Standard	Magnetic test switch	Magnetic test switch
Self Diagnostics	-	-	Standard	Optional	Optional
Temperature Range	10°C to 40°C (50°F to 104°F)	10°C to 40°C (50°F to 104°F)	10°C to 40°C (50°F to 104°F)	0° C to 50° C (32 F to 122 F)	0°C to 50°C (32°F to 122°F)
Remote Capability	Optional	✓	Optional	Optional	Optional
Damp Listing	✓	✓	✓	✓	✓
Wet Listing	No	No	No	✓	✓
UL Listing	UL 924 cUL NFPA 101 NFPA 70	UL 924 cUL NFPA 101 NFPA 70	UL 924 NFPA 101 NFPA 70	UL 924 NFPA 101 IP66 Meets CEC title 20 regulations	UL 924 NEMA 4X, IP66 and NSF rated NFPA 101
Battery	NiCad	NiCad	NiMH	NiCad	NiCad
Lamps	2 x 1W LED	2 x 1W	2 x 2.2W	2 x 3.6W LED lamp Heads	2 x 3.3W MR16 base LED lamp Heads
Limited Warranty	3 years	3 years	5 years	5 years	5 years
Link					