









Versatility in form and function. Reliable, energy efficient and cost effective solutions for light industrial, warehouses, retail, or institutional spaces.

									
Applicability		Budget-grade	Value-grade	Value-grade	Value-grade	Value-grade	Spec-grade	Budget-grade	Value-grade
		Good	Better	Better	Better	Better	Best	Good	Better
		FCY	RBX	HRL	G Series	FBY	FBZ	HCY	APX
Applications	Big Box Retail	★	★	★	★	★	★	★	–
	Sports/Rec.	★	★	★	–	★	★	★	–
	Warehouse	★	★	–	★	★	★	★	★
	Manufacturing	★	–	–	★	★	★	★	★
	Cold Storage	★	–	–	–	★	★	★	★
	Large Indoor	★	★	★	★	★	★	★	★
	Complex Areas	★	–	–	–	★	★	★	★
Features	Light Distributions	General	General	General	General	General	General, N/M/W, & Aisle	General	General, N/M/W, & Aisle
	Modular Wiring	–	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)	Electro-Connect (see product spec sheet for details)
	Accessory	–	–	–	–	–	–	–	–
	Installation	UL Damp Location	UL Damp Location	UL Damp Location	UL Damp Location	UL Damp Location	UL Damp Location	IP65 & NEMA 4X	IP65/IP66/IP67, NEMA 4X & NSF
	DLC	Premium	Std. & Prem.	Std. & Prem.	Std. & Prem.	Std. & Prem.	Std. & Prem.	Premium	Std. & Prem.
Performance	Lumen Output	8000, 12000, 15000, 18000, 24000, 30000, & 36000	10000, 15000, & 20000	10": 8000, 14000, & 22000 12": 24000, 32000, & 37000 (field selectable)	8000, 12000, & 16000	12000, 18000, 24000, 30000, 36000, 48000, & 60000	8000, 12000, 18000, 24000, 30000, 36000, 48000, & 60000	14000, 21000, 28000, & 33000	8000, 12000, 16000, 20000, & 24000
	Color Render Index	80 CRI	80 CRI	>80 CRI	>80 CRI	>80 CRI	80 CRI	>80 CRI	>80 CRI
	Color Temperature	4000K & 5000K (color select)	2700K, 3000K, 3500K, & 4000K	3500K, 4000K, & 5000K	3500K, 4000K, & 5000K	3500K, 4000K, & 5000K	3500K, 4000K, & 5000K	4000K & 5000K	3500K, 4000K, & 5000K
	Efficacy	up to 157lm/W	up to 137lm/W	up to 150lm/W	up to 154lm/W	up to 148lm/W	up to 175lm/W	up to 149lm/W (field selectable)	up to 129lm/W
	Ambient Temp.	-40 to +50°C	-20 to +40°C	-40 to +50°C	-20 to +40°C	-20 to +45°C	-40 to +55°C (60/65)	-20 to +50°C	-20 to +40°C
	Emergency	–	Yes	Yes	Yes	Yes	Yes	No	Yes
	Voltage	120-277V	120-277V	120-277V	120-277V	120-277V	120-277V	120-277V	120-277V
Sensors/Controls	Lifespan (warranty)	5 year @ (L70) 100,000hrs	5 year @ (L70) 100,000hrs	5 year @ (L70) 50,000hrs	5 year @ (L70) 60,000hrs	5 year @ (L70) 100,000hrs	5 year @ (L70) 100,000hrs	5 year @ (L70) 50,000hrs	5 year @ (L70) 100,000hrs
	Sensor	Yes (field installed)	–	–	Yes, (field or factory installed)	Yes, (field or factory installed)	Yes	Yes (field installed)	Yes, (field or factory installed)
	SpaceWise	–	–	–	–	Yes	Yes	–	Yes
	Interact Ready	–	–	–	–	Yes	Yes	–	Yes
	Dimming	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V
Link	