



	Best	Best	Better	Better
	PureForm Post Top LED Comfort	PureForm Post Top LED Precision	Form Ten Round Post Top CPL	Form Ten Round Post Top MPL
Prefix	PPT-C	PPT-P	CPL	MPL
Lumen Output Range	1,500-16,114	2,500-17,315	5,037-21,852	5,037-21,852
Efficacy	95-147	127-186	93-113	93-113
Distribution	Type 2, 3, 4, 5	Type 2, 3, 4, 5, back light control	Type 2, 3, 4, 5	Type 2, 3, 4, 5
Color Temperature	2700, 3000, 3500, 4000, 5000	2700, 3000, 4000, 5000	3000, 4000, 5700	3000, 4000, 5700
Mounting Height Range	10'-25'	10'-25'	10'-25'	10'-25'
0 Uplight	-	✓	✓	✓
Auto Profile Dimming	-	✓	-	-
Motion Response	-	✓	-	-
Interact Controls	✓	✓	-	-
SR Drive with Zhaga Socket	✓	✓	-	-
Service Tag Standard	✓	✓	-	-
Additional Luminaire Options	-	Emergency Battery Backup (cold weather and standard), Field Adjustable Wattage Selector (FAWS)	Retrofit Kit	Retrofit Kit
Mounting	-	T3, T2	Multiple tenon sizes to fit many pole sizes - see spec sheet for details	
Finish	-	Bronze, Black, White, Medium Grey, Dark Grey	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, Black, White, Medium Grey	
IP Rating	-	IP66	Wet Location	Wet Location
Vibration	Level 2	3G	-	-
DLC Listing	-	Standard	Standard	Standard
Certifications	-	UL/cUL	UL/cUL	UL/cUL
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years			
Link	Coming soon	Coming soon		