



Outdoor

Wall Sconces

Product Selection Guide

Gardco wall sconce luminaires blend excellent performance with aesthetics. Multiple shapes are available to blend with architecture or make a statement.



Rating	Better	Better	Better	Better	Better	Better	Better	Better	Best	Best
Product	GeoForm Cylinder Small	GeoForm Block Small	GeoForm Wedge Small	GeoForm Cylinder Medium	GeoForm Block Medium	GeoForm Wedge Medium	101 LED	121 LED	PureForm Wall Sconce Comfort	PureForm Wall Sconce Precision
Prefix	GCS	GBS	GWS	GCM	GBM	GWM	101L	121	PWS-C	PWS-P
Lumen Output Range	1,700-6,500	1,700-6,500	1,700-6,500	1,700-6,500	2,900-12,700	2,900-12,700	1,429-12,045	1,391-12,421	2,000-10,000	2,000-30,000
Efficacy	130-175	130-175	130-175	130-175	140-180	140-180	98-136	93-140	95-130	130-195
Distribution	Type 2, 3, 4, Wall Wash, Spot, Pencil	Type 2, 3, 4, Wall Wash, Spot, Pencil	Type 2, 3, 4	Type 2, 3, 4, Wall Wash, Spot, Pencil	Type 2, 3, 4, Wall Wash, Spot, Pencil	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4, BLC (ETOr)
Uplight Capability (wet location)	✓	✓	-	✓	✓	-	-	-	-	-
Color Temperature	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	2700, 3000, 4000, 5000, Amber	2700, 3000, 4000, Amber	2700, 3000, 4000, 5000
Mounting Height	8-12'	8-12'	8-12'	8-12'	12-24'	12-24'	8-20'	8-20'	10-20'	10-25'
0 Uplight	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Emergency Battery Backup (0°C to 40°C)	✓	✓	✓	-	-	-	-	-	✓	-
Emergency Cold Pack (-20°C to 40°C)	-	-	-	✓	✓	✓	✓	✓	✓	✓
Field Adjustable Wattage Selector (FAWS)	✓	✓	✓	✓	✓	✓	-	✓	✓	✓
Dual Circuit Control (DCC)	-	-	-	-	✓	✓	✓	✓	-	✓
Auto Profile Dimming	-	-	-	✓	✓	✓	✓	✓	✓	✓
Motion Response	-	-	-	-	✓	✓	✓	✓	✓	✓
Interact Compatible	-	-	-	-	-	-	-	✓	✓	✓
Photocell	Button	Button	Button	Button	Button	Button	Button, TLRD5, TLRD7, TLRPC	Button	Button	Button
Additional Options	Emergency Battery Backup	Diffusing lens, Emergency Battery Backup	Diffusing lens	Emergency Battery Backup	Emergency Battery Backup	Emergency Battery Backup	-	-	Emergency Battery Backup	Emergency Battery Backup
Finish	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray	Bronze, Black, White, Medium Gray, Dark Gray
IP Rating	IP65	IP65	IP65	IP65	IP65	IP65	IP66 LED Light Engine	IP66 LED Light Engine	IP65	IP65 housing/IP66 LED Light Engine
DLC Listing	Premium	Premium	Premium	Premium	Premium	Premium	Standard	Premium, Standard	Premium	Premium
Certifications	cULus	cULus	cULus	cULus	cULus	cULus	Title 24, cULus	Title 24, cULus	UL/cUL	UL/cUL
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Link										