

AccuRender technology helps ensure colors are rendered more accurately and consistently, while doing so as efficiently as 80 CRI products.



★	High
★	Medium
★	Low
—	NA

	Budget-grade	Value-grade	Performance-grade	Specification-grade	
	Good	Better	Better	Best	
	LyteCaster LED	ModuLyte LED	LyteProfile LED	Calculte LED	
Applications	Retail	★	★	★	
	Hospitality	★	★	★	
	Office	★	★	★	
	Education	★	★	★	
	Residential	★	★	★	
Features	Sizes	3", 4", 5", 6"	4", 6", 8"	3", 4", 6"	2", 3", 4", 6", 7"
	Shapes	Round & Square	Round	Round & Square	Round & Square
	Styles	Downlight, Baffle, Adj. Accent, Gimbal, Pinhole, Wall Wash, & Shower Light	Downlight & Wall Wash	Downlight, Adj. Accent, Shower Light, & Lensed Wall Wash	Downlight, Adj. Accent, Wall Wash, Shower Light
	Reflector	Chrome, Diffuse, & White	White & Black (matte) Specular Clear & Comfort Diffuse	White & Black (matte), Specular Clear, Comfort Clear, & Comfort Clear Diffuse	White (matte), Black (anodized), Specular Clear, Comfort Clear, Comfort Clear Diffuse, & Champagne Bronze
	Flange	White (matte)	White & Black (matte), Polished (matches aperture)	White & Black (matte), Polished (matches aperture) & Flangeless	White (matte), Black (anodized), Polished (matches aperture) & Flangeless
	Trim Direct & Reflected Cutoff	70° / 70° & 30° Adj. Accent	59° / 59°	60° / 60° & 40° Adj. Accent	45° / 50° & 45° Adj. Accent
	Retrofit ready	Yes (frames available)	Yes (frames available)	Yes (frames available), Flex available	Yes (frames available), Flex available
	Lumen Range	3" 800lm 4" 650/1000lm 5" 1000/1500lm 6" 1500/2000lm	4" 500-4000lm 6" 500-5000lm 8" 500-5000lm	3" 500-1500lm 4" 500-4000lm 6" 1000-5000lm	2" 600-1500lm 3" 500-1500lm 4" 500-3000lm 6" & 7" 1000-6000lm
	Color Render Index	90 CRI  Accurender	90 CRI  Accurender	90 CRI  Accurender	90 CRI  Accurender
	Color Temperature	2700K, 3000K, 3500K, & 4000K	2700K, 3000K, 3500K, 4000K, 5000K selectable	2700K, 3000K, 3500K, & 4000K	2700K, 3000K, 3500K, 4000K, & 5000K
Efficacy	up to 100lm/W	up to 115lm/W	up to 100lm/W	up to 120lm/W	
SDCM	3	3 (@2700K & 5000K)	2	2	
Emergency	—	Yes (accessories available)	Yes (accessories available)	Yes (accessories available)	
Voltage	120V (ELV/Triac) 120/277V (0-10V)	120V/277V, & 347V	120V (ELV/Triac), 120/277V, & 347V	120V (ELV/Triac), 120/277V, & 347V	
Life	L70 @ 50,000hrs	L80 @ 72,000hrs	L80 @ 60,000hrs	L90 @ 60,000hrs	
Controls	Tunable White	3" : Crisp White, Premium White, & Premium Color	—	4" Round : Dim-to-warm & Tunable 6" Round : Dim-to-warm & Tunable	4" Round : Dim-to-warm & Tunable 6" Round : Dim-to-warm & Tunable
	Interact ready	—	Yes	Yes	Yes
	Dimming	ELV/Triac & 0-10V	0-10V	ELV/Triac, 0-10V, Lutron, & Phase-cut	ELV/Triac, 0-10V, Lutron, DALI, DMX, Phase-cut
	Link				

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.