

Easy to install solutions for existing construction and LED upgrade opportunities.



★	High
★	Medium
★	Low
—	NA

		Budget-grade	Budget-grade	Budget-grade	Budget-grade	Value-grade	Value-grade
		Good	Good	Good	Good	Better	Best
		Flat Downlight LED with dual select	Downlight LED with dual select	Gimbal LED with dual select	Residential Retrofit Downlight LED with CCT select	Commercial Retrofit Downlight LED with dual select	ModuLyte LED with dual select
Applications	Retail	★	★	★	★	★	★
	Hospitality	★	★	★	★	★	★
	Office	★	★	★	★	★	★
	Education	★	★	★	★	★	★
	Residential	★	★	★	★	★	★
Features	Sizes	3", 4", 5", 6", 8"	3", 4", 6"	3", 4", 6"	4", 6"	4", 6", 8", 10"	4", 6", 8"
	Shapes	Round & Square	Round	Round	Round	Round	Round
	Finishes	White or Black	White	White	White	White	Downlight & Wall Wash
	Trim Direct & Reflected Cutoff	Lambertian	Lambertian	Lambertian	Better	Better	Best
Performance	Lumen Range (standard)	3" 400lm 4" 700lm 5" 900lm 6" 1100lm 8" 1300lm	3" 400lm 4" 700lm 6" 1100lm	3" 400lm 4" 700lm 6" 1100lm	4" 700lm 6" 900lm	—	—
	Lumen Range (Field Selectable)	3" 370/500lm 4" 540/700lm 5" 900/1100lm 6" 900/1100lm 8" 1100/1300lm	3" 370-500lm 4" 540-700lm 6" 900-1100lm	3" 370-500lm 4" 540-700lm 6" 900-1100lm	—	4" 500/700/1000lm 6" 700/1000/1500lm 8" 1000/1500/2000lm 10" 2000/2500/3000lm	4" 500-4000lm 6" 500-5000lm 8" 500-5000lm
	Color Render Index	90 CRI	90 CRI	90 CRI	90 CRI	90 CRI	90 CRI Accrender
	Correlated Color Temperature	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)	Field Selectable 3CCT (3000K, 3500K, & 4000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)
	Efficacy	up to 82lm/W	up to 74lm/W	up to 74lm/W	up to 96lm/W	up to 94lm/W	up to 120lm/W
	SDCM	3	3	3	3	3	3 (@2700K & 5000K)
	Emergency	—	—	—	—	—	Yes
	Voltage	120V (standard) 120/277V (field select)	120V (standard) 120/277V (field select)	120V (standard) 120/277V (field select)	120V	120/347V (field select)	120-277V 347V
	Life	50,000hrs	50,000hrs	50,000hrs	50,000hrs	50,000hrs	L80 @ 72,000hrs
	Tunable White	—	—	—	—	—	—
Controls	Dimming	ELV/Triac (standard) 0-10V (field select)	ELV/Triac (standard) 0-10V (field select)	ELV/Triac (standard) 0-10V (field select)	ELV/TRIAC	0-10V dim	0-10v (1%)
	Link						