

Powerful indoor portfolio of all-in-one field selectable lumen & CCT luminaires that will impress your most discerning customers.



★	High
★	Medium
★	Low
—	NA

		Budget-grade	Budget-grade	Budget-grade	Budget-grade	Value-grade	Value-grade	Value-grade
		Good	Good	Good	Good	Better	Better	Best
		Downlight & Gimbal LED with dual select	Surface Mount Downlight LED	Flat Downlight LED with dual select	Residential Retrofit Downlight LED with CCT select	Commercial Retrofit Downlight LED with dual select	SlimSurface LED	ModuLyte LED with dual select
Applications	Retail	★	★	★	★	★	★	★
	Hospitality	★	★	★	★	★	★	★
	Office	★	★	★	★	★	★	★
	Education	★	★	★	★	★	★	★
	Residential	★	★	★	★	★	★	★
Features	Sizes	3", 4", 6"	5", 7", 9" 11", 14"	3", 4", 5", 6", 8"	4", 6"	4", 6", 8", 10"	4", 6" square 5", 7", 10" round	4", 6", 8"
	Shapes	Round	Round	Round & Square	Round	Round	Round & Square	Round
	Finishes	White	White	White or Black	White	White	White, Black, & Aluminum	Downlight & Lensed Wall Wash
	Glare	Lambertian	Lambertian	Lambertian	Better	Better	Better	Best
Performance	Lumen Range (standard)	3" 400lm 4" 700lm 6" 1100lm	5" 700lm 7" 1000lm 9" 1200lm 11" 1500lm 14" 1650lm	3" 400lm 4" 700lm 5" 900lm 6" 1100lm 8" 1300lm	4" 700lm 6" 900lm	—	■ 4" 650lm ■ 6" 1000lm ● 5" 650lm ● 7" 1000lm ● 10" 2200lm	—
	Lumen Range (Field Selectable)	3" 370-500lm 4" 540-700lm 6" 900-1100lm	5" 540/700lm 7" 800/1000lm 9" 900/1200lm 11" 1200/1500lm 14" 1600/2000lm	3" 370/500lm 4" 540/700lm 5" 900/1100lm 6" 900/1100lm 8" 1100/1300lm	—	4" 500/700/1000lm 6" 700/1000/1500lm 8" 1000/1500/2000lm 10" 2000/2500/3000lm	—	4" 500/4000lm 6" 500/5000lm 8" 500/5000lm
	Color Render Index	90 CRI	90 CRI	90 CRI	90 CRI	90 CRI	80 CRI & 90 CRI	90 CRI
	Correlated Color Temperature	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)	Field Selectable 3CCT (3000K, 3500K, & 4000K)	2700K, 3000K, 3500K, & 4000K	Field Selectable 5CCT (2700K, 3000K, 3500K, 4000K, & 5000K)
	Efficacy	up to 74lm/W	up to 84lm/W	up to 82lm/W	up to 96lm/W	up to 94lm/W	up to 94lm/W	up to 120lm/W
	SDCM	3	3	3	3	3	3	3 (@2700K & 5000K)
	Emergency	—	—	—	—	—	—	Yes
	Voltage	120V (standard) 120/277V (field select)	120V (standard) 120/277V (field select)	120V (standard) 120/277V (field select)	120V	120/347V (field select)	120V (ELV/Triac) 120/277V (0-10V)	120-277V 347V
	Life	50,000hrs	50,000hrs	50,000hrs	50,000hrs	50,000hrs	50,000hrs	L90 @ 60,000hrs
	Controls	Tunable White	—	—	—	—	—	—
Dimming		ELV/Triac (standard) 0-10v (field select)	ELV/Triac (standard) 0-10v (field select)	ELV/Triac (standard) 0-10v (field select)	ELV/TRIAC	0-10v	ELV/Triac & 0-10v	0-10v (1%)
Link								

© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.