



	Better	Better	Better	Best	Best
Category	Modern	Modern	Modern	Multiple	Multiple
Style	Contemporary	Contemporary	Contemporary	Contemporary, Transitional, Historical	Contemporary, Transitional, Historical
Product	<b>Leonis</b>	<b>SoleCity Small</b>	<b>SoleCity Medium</b>	<b>OmniScope</b>	<b>OmniScope</b>
Prefix	LEN4, LEN5, LEN6	ULS100	ULM100	S-OSA	S-OSA-C
Light Engine	-	-	-	LEDgine	ComfortEdge™
Lumen Output Range	Up to 13,211	Up to 15,776	Up to 31,718	Up to 21,681	Up to 18,724
Efficacy	Up to 141 LPW	Up to 128 LPW	Up to 128 LPW	Up to 199 LPW	Up to 152 LPW
Distribution	Type II, III, IV, V	Type III, IV, V	Type III, IV, V	2, 2B, 3, 32, 4, 5	2, 3, 4, 5
Color Temperature	3000K, 4000K	3000K, 4000K	3000K, 4000K	2700K, 3000K, 4000K(70/80 CRI)	2700K, 3000K, 4000K(70/80 CRI)
Mounting Height Range	20' - 30'	15' - 30'	15' - 35'	15' - 25'	15' - 25'
DALI	✓	✓	✓	✓	✓
Sensor Ready Driver	✓	-	-	✓	✓
Photocell	✓	✓	✓	✓	✓
Receptacle	✓	✓	✓	✓	✓
Shielding	HS	HS	HS	HS	Consult Factory
Additional Surge Protection	✓	✓	✓	✓	✓
Finish	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)	Blue, Sandstone, Black, Green, Grey, Burgundy, Scarlet, White; (Textured)
IP Rating	IP66	IP66	IP66	IP66	IP66
Vibration	1.5G	1.5G	1.5G	3G	3G
DLC Listing	-	✓	✓	Premium	Premium
Certifications	cULus	cULus	cULus	cUL/Dark Skies	cUL/Dark Skies
Lifetime Per TM21	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 60,000 hours	L70 > 84,000 hours	L70 > 84,000 hours
Limited Warranty	5 years	5 years	5 years	5 Years	5 Years
Link					