


PHILIPS

LED lamps

Field Selectable

Field selectable lamps

April 2025





With the unique convenience of adjustable color temperatures and/or lumen outputs, our new field selectable product line makes it easy to always have the right product for the job.



**Contractor-grade
InstantFit Circline LED Lamps**
with selectable CCT



**Flex Fit (Hor/Ver adj.)
PLED lamps**
with selectable CCT



**Consumer LED
A19 bulbs & PARs**
with selectable CCT



**Flex Fit
TLED lamps**
with selectable CCT



**CorePro MainsFit
TLED lamps**
with selectable CCT, Lumen & base



**CorePro MainsFit
PLED lamps**
with selectable CCT



**MasterClass
LED corn cob lamps**
with selectable CCT & Wattage



**MasterClass high wattage
LED corn cob lamps**
with selectable CCT

Field Selectable products give you the added benefit of carrying one SKU versus multiple SKUs, keeping your inventory low and turns high. These field selectable products are priced right and are all part of our Ready to go offering!

Learn more about additional Ready to go offerings at:
www.philips.com/LEDlamps



FlexFit (Type A+B) TLED and PLED lamps

with selectable CCT

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	CRI - CCT (min) (K)	Life ¹ (hrs)	Price
588624	929003794504	7.5T8/COR/24-5CCT/FF11/G/DIM 25/1	7.5	1100	82CRI - 3000/3500/4000/5000/6500	50,000	
588632	929003794604	10.5T8/COR/36-5CCT/FF15/G/DIM 25/1	10.5	1500	82CRI - 3000/3500/4000/5000/6500	50,000	
588640	929003794704	12T8/COR/48-5CCT/FF18/G/DIM 25/1	12	1800	82CRI - 3000/3500/4000/5000/6500	50,000	
589788	929003807304	16PL-C/T/COR/42HV-5CCT/FF18/4P 50/1	16	1850	82CRI - 2700/3000/3500/4000/5000	50,000	
606150	929004257834	15T8-1U/COR/24-5CCT/FF22/G 10/1 *	15	1800/2000/2200	80CRI - 3000/3500/4000/5000/6500	50,000	
606582	929004236104	15T8-6U/COR/24-5CCT/FF22/G 10/1 *	15	1800/2000/2200	80CRI - 3000/3500/4000/5000/6500	50,000	



MainsFit CorePro (UL Type-B) TLED lamps

with selectable CCT (120-277V) 240° beam angle

Product No. (6nc)	Model No. (12nc)	Description	Wts (W)	Lumens (lm)	CRI - CCT (min) (K)	Life ¹ (hrs)	Price
589804	929003815504	43T8/COR/96-5CCT/MF52LS/G/FA8-R17D 10/1	43	3400/4300/5200	82CRI - 3000/3500/4000/5000/6500	50,000	
592766	929004235004	4.5T5HE/COR/12-5CCT/MF5/G 25/1 *	4.5	500	82CRI - 3000/3500/4000/5000/6500	50,000	
592774	929004235104	9T5HE/COR/22-5CCT/MF12/G 25/1 *	9	1200	82CRI - 3000/3500/4000/5000/6500	50,000	
592782	929004235204	12T5HE/COR/34-5CCT/MF16/G 25/1	12	1600	82CRI - 3000/3500/4000/5000/6500	50,000	
592790	929004235304	13T5HE/COR/46-5CCT/MF18/G 25/1	13	1800	82CRI - 3000/3500/4000/5000/6500	50,000	



InstantFit Contractor-grade Circline LED lamps

with selectable CCT (120-277V) 120° beam angle

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	CRI - CCT (min) (K)	Lifetime ¹ (hrs)	Price
588095	929003740604	11CIR/CNG/8-4CCT/IF12/P/G10q 6/1	11	1200	82CRI - 3000K/3500K/4000K/5000K	50,000	
588103	929003740704	16CIR/CNG/12-4CCT/IF17/P/G10q 6/1	16	1700	82CRI - 3000K/3500K/4000K/5000K	50,000	
605010	929004236004	22CIR/CNG/16-4CCT/IF26/P/G10q 6/1	22	2600	82CRI - 3000K/3500K/4000K/5000K	50,000	



MainsFit CorePro PLED lamps

with selectable CCT (120-277V) 120° beam angle

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	CRI - CCT (min) (K)	Lifetime ¹ (hrs)	Price
607127	929004602404	8PL-L/COR/18-5CCT/MF9/G/4P 10/1 *	8	900	80CRI - 2700/3000/3500/4000/5000	50,000	
607135	929004602504	10PL-L/COR/24-5CCT/MF11/G/4P 10/1 *	10	1100	80CRI - 2700/3000/3500/4000/5000	50,000	
607143	929004602604	16PL-L/COR/36-5CCT/MF20/G/4P 10/1 *	16	2000	80CRI - 2700/3000/3500/4000/5000	50,000	
607150	929004602704	18PL-L/COR/55-5CCT/MF28/G/4P 10/1 *	18	2800	80CRI - 2700/3000/3500/4000/5000	50,000	
606566	929004582904	5PL-S/COR/9H-5CCT/MF5/P/2P 20/1 *	5	500	80CRI - 2700/3000/3500/4000/5000	50,000	
606574	929004583004	6PL-S/COR/13H-5CCT/MF6/P/2P 20/1 *	6	600	80CRI - 2700/3000/3500/4000/5000	50,000	

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture. MasterClass corn cob LED HID replacement lamps are damp location rated and suitable for enclosed fixtures.

* Launched in May of 2025



MasterClass LED corn cob HID replacement lamps

with selectable CCT & Lumens

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI - CCT (min) (K)	Life ¹ (hrs)	Price
606250	929004257904	18-12-9CC/LED/3PW/3CCT/E26 BB 6/1	18/12/9	50MH	5000K: 2400/1600/1200 3000K: 2200/1450/1100	80CRI - 3000/4000/5000	50,000	
606269	929004258004	27-18-12CC/LED/3PW/3CCT/E26 BB 6/1	27/18/12	70MH/50HPS	5000K: 3800/2500/1600 3000K: 3600/2400/1500	80CRI - 3000/4000/5000	50,000	
606228	929004258104	36-27-18CC/LED/3PW/3CCT/E26 BB 6/1	36/27/18	100MH/70HPS	5000K: 5000/3800/2500 3000K: 4800/3600/2400	80CRI - 3000/4000/5000	50,000	
606236	929004258204	36-27-18CC/LED/3PW/3CCT/Ex39 BB 3/1	36/27/18	100MH/70HPS	5000K: 5000/3800/2500 3000K: 4800/3600/2400	80CRI - 3000/4000/5000	50,000	
606244	929004258304	54-45-36CC/LED/3PW/3CCT/Ex39 BB 3/1	50/45/36	175MH/100HPS	5000K: 7500/6200/5000 3000K: 7000/5850/4700	80CRI - 3000/4000/5000	50,000	



MasterClass high wattage LED corn cob lamps

with selectable CCT

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	Price
583682	929003631404	80CC/LED/3CCT/LS EX39 BB 3/1	80	250	11500/12000/12000	80	3000/4000/5000	50,000	
583690	929003631504	115CC/LED/3CCT/LS EX39 BB 3/1	115	320	15800/17000/17000	80	3000/4000/5000	50,000	
583708	929003631604	145CC/LED/3CCT/LS EX39 BB 3/1	145	400	20500/22000/22000	80	3000/4000/5000	50,000	



Consumer LED lamps

with selectable CCT (120-277V)

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lms (lm)	CRI - CCT (min) (K)	Life ¹ (hrs)	Price
583161	929003620203	7.2BR30/DipS/5CCT/P/E26/DIM/T20 2/3CT	7	65	650	90CRI - 2700/3000/3500/4000/5000	15,000	
586875	929003620333	8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT	8	60	800	90CRI - 2700/3000/3500/4000/5000	15,000	
586883	929003620433	14A19/DipS/5CCT/FR/P/E26/DIM/T20 2/2PF	14	100	1500	90CRI - 2700/3000/3500/4000/5000	15,000	
586479	929003741003	10PAR38/90W/DipS/5CCT/40D/D/P/E26/T20	10	90	900	90CRI - 2700/3000/3500/4000/5000	15,000	

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture. MasterClass corn cob LED HID replacement lamps are damp location rated and suitable for enclosed fixtures.





© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLt-2158BR 05/25 philips.com/LEDlamps

Signify North America Corp.
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.