PHILIPS

SM378B S P13 927 PSU-E MB D100 G-TT PRO

911401532946

GreenSpace Flex Luna, 13.5 W, 1510 lm, 2700 K, Structured optic, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

General Information

Driver included	Yes
Light source engine type	LED
Value ladder	Performance

Light Technical

Luminous Flux	1,510 lm
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	112 lm/W
Color rendering index (CRI)	92
Light source color	927 warm white
Unified glare rating CEN	16

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	13.5 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Number of products on MCB of 16 A type B	66
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	-
Control interface	-

Mechanical and Housing

Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Structured optic
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Lens
Net Weight (Piece)	0.558 kg

Dimensional drawing



Approval and Application

CE mark	Yes
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Application Conditions

Lumen Maintenance	50000hrs

Product Data

Order product name	SM378B S P13 927 PSU-E MB D100 G-TT PRO
Full product name	SM378B S P13 927 PSU-E MB D100 G-TT PRO
Order code	911401532946
Material Nr. (12NC)	911401532946
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36

Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	INI-SM378BPRO.pdf	Download

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.