CorePro LED PLC 2P

LED PLC 8.5W 840 2P G24d-3

LED, PL-C, EM, 147.5 mm, 220-240 V, 8.5 W, 26W PL-C, 4000 K, 1000 lm, 30000 hour(s)

CorePro LED PLC 2P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

Product data

General Information	
Cap-Base	G24d-3
Nominal lifetime	30,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED

Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	1,000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	117.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8.5 W
Lamp Current (Max)	43 mA
Lamp Current (Min)	33 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	26W PL-C
Ballast Compatibility	EM

Temperature	
T-Case Maximum (Nom)	75 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	147.5 mm

CorePro LED PLC 2P

Bulb Shape	PL-C
Net Weight (Piece)	0.090 kg

Full product name	LED PLC 8.5W 840 2P G24d-3
Full product code	871869667001900
Order code	929001201308
Material Nr. (12NC)	929001201308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696670019
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696670026

Approval and Application

Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	11 kWh
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 35 °C

Product Data

Order product name	LED PLC 8.5W 840 2P G24d-3

Dimensional drawing



Product	D1	D	A1	A2	A3
LED PLC 8.5W 840 2P G24d-3	34 mm	34 mm	129 mm	148 mm	171 mm

Photometric data



General uniform lighting - LED PLC 8.5W 840 2P G24d-3



Spectral Power Distribution Colour - LED PLC 8.5W 840 2P G24d-3

CorePro LED PLC 2P

Photometric data



Light Distribution Diagram - LED PLC 8.5W 840 2P G24d-3

Lifetime



LEDtube PLC 100mm 9W G24D-3 830 950lm



LEDtube PLC 100mm 9W G24D-3 830 950lm



LEDtube PLC 100mm 9W G24D-3 830 950lm



Lumen Maintenance Diagram - LED PLC 8.5W 840 2P G24d-3

CorePro LED PLC 2P

Lifetime



Lumen Maintenance Diagram - LED PLC 8.5W 840 2P G24d-3

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.