Specialty Lamps

4A19/PER/GREEN/G/E26/ND 4/1PF

LEDbulb, A19, 40 W, E26, 15000 hour(s), Glass

LEDbulb, A19, 40 W, E26, 15000 hour(s), Glass

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LEDbulb

Light Technical	
Color Code	Green
Beam Angle (Nom)	330 degree(s)
Color Designation	Green
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	4 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.40
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	125 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Green
Bulb Material	Glass
Overall length	106 mm
Overall width	60 mm
Overall height	106 mm
Dimensions (Height x Width x Depth)	106 x 60 x 106 mm
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.030 kg

Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	N/A

Specialty Lamps

LED Innovations	EyeComfort
Ambient temperature range	-20 °C to 45 °C

Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data

Order product name	4A19/PER/GREEN/G/E26/ND 4/1PF
Full product name	4A19/PER/GREEN/G/E26/ND 4/1PF
Order code	929001937453
Material Nr. (12NC)	929001937453
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568870
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677568875

Dimensional drawing



Product	D	C
4A19/PER/GREEN/G/E26/ND 4/1PF	60 mm	106 mm

Photometric data



Light Distribution Diagram - 4A19/PER/GREEN/G/E26/ND 4/1PF



General uniform lighting - 4A19/PER/GREEN/G/E26/ND 4/1PF

Specialty Lamps

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 4A19/PER/GREEN/G/E26/ND 4/1PF

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.