PHILIPS

Lighting



# UniStrip G4 – Best in Class Linear LED Surface Mounted Luminaire for Exterior Fixed and Dynamic Architectural Lighting Applications

## UniStrip G4

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

**Benefits**

- High and Low Power LEDs versions available
- Various spread lenses that fit all applications
- Adjustable brackets and through wiring for end-to-end connection

# UniStrip G4

## Features

- Six sub-families with power ranges from 3W to 120W
- DC and AC powered versions
- Narrow, medium, wide and asymmetric beams available
- Optional glare shields for more visual comfort

## Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

## Warnings and Safety

- For outdoor use only

## Dimensional drawing













## Dimensional drawing







## Product details

UniStrip G4 Detail Photo



UniStrip G4 Detail Photo




UniStrip G4 Detail Photo



UniStrip G4 Detail Photo

## Product details

UniStrip G4 Detail Photo



159A3710 Detail Photo



UniStrip G4 Detail Photo



159A3691 Detail Photo




UniStrip G4 Detail Photo




UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



159A3731 Detail Photo



# UniStrip G4

| General Information | |
|---|---|
| **Driver included** | No |

| Mechanical and Housing | |
|---|---|
| **Housing Color** | Dark gray |

| Approval and Application | |
|---|---|
| **CE mark** | CE mark |
| **Mech. impact protection code** | IK06 |
| **Ingress protection code** | IP66 |

## General Information

| Order Code | Full Product Name | Light source replaceable |
|---|---|---|
| 911401779982 | BCP386 12LED 27K 24V 60 L30 | - |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | - |
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | - |
| 911401780102 | BCP386 12LED RGBNW 24V 45 L30 DMX | - |
| 911401780122 | BCP386 12LED RGBNW 24V A11 L30 DMX | - |
| 911401780192 | BCP386 30LED 30K 24V 45 L50 | - |
| 911401780232 | BCP386 30LED 27K 24V 60 L50 | - |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | - |
| 911401780312 | BCP386 30LED 30K 24V A11 L50 | - |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | - |
| 911401780352 | BCP386 30LED RGBNW 24V 45 L50 DMX | - |
| 911401780362 | BCP386 30LED RGBWW 24V A11 L50 DMX | - |
| 911401780372 | BCP386 30LED RGBNW 24V A11 L50 DMX | - |
| 911401780482 | BCP386 60LED 27K 24V 60 L100 | - |
| 911401780502 | BCP386 60LED 30K 24V 60 L100 | - |
| 911401780522 | BCP386 60LED 40K 24V 60 L100 | - |
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | - |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | - |
| 911401780592 | BCP386 60LED RGBWW 24V 45 L100 DMX | - |
| 911401780602 | BCP386 60LED RGBNW 24V 45 L100 DMX | - |
| 911401780612 | BCP386 60LED RGBWW 24V A11 L100 DMX | - |
| 911401780622 | BCP386 60LED RGBNW 24V A11 L100 DMX | - |
| 911401780632 | BCP386 60LED RGB 24V 30 L100 DMX | - |
| 911401780642 | BCP386 60LED RGB 24V 45 L100 DMX | - |
| 911401780652 | BCP386 60LED RGB 24V A3 L100 DMX | - |
| 911401738662 | BCP381 12LED 30K 24V 40 L50 | No |
| 911401738782 | BCP381 24LED 27K 24V 40 L100 | No |
| 911401738822 | BCP381 24LED 30K 24V 40 L100 | No |
| 911401738982 | BCP381 6LED 30K 24V 40 L30 | No |

| Order Code | Full Product Name | Light source replaceable |
|---|---|---|
| 911401739162 | BCP382 18LED 27K 24V 40 L50 | No |
| 911401739222 | BCP382 18LED 30K 24V 40 L50 | No |
| 911401739382 | BCP382 36LED 27K 24V 40 L100 | No |
| 911401739422 | BCP382 36LED 30K 24V 17 L100 | No |
| 911401739442 | BCP382 36LED 30K 24V 40 L100 | No |
| 911401739602 | BCP382 9LED 27K 24V 40 L30 | No |
| 911401739642 | BCP382 9LED 30K 24V 17 L30 | No |
| 911401739662 | BCP382 9LED 30K 24V 40 L30 | No |
| 911401739182 | BCP382 18LED 30K 24V A2 L50 | No |
| 911401739342 | BCP382 36LED 27K 24V A2 L100 | No |
| 911401739402 | BCP382 36LED 30K 24V A2 L100 | No |
| 911401739622 | BCP382 9LED 30K 24V A2 L30 | No |
| 911401738602 | BCP381 12LED 27K 24V A2 L50 | No |
| 911401738642 | BCP381 12LED 30K 24V A2 L50 | No |
| 911401738802 | BCP381 24LED 30K 24V A2 L100 | No |
| 911401738962 | BCP381 6LED 30K 24V A2 L30 | No |
| 911401738702 | BCP381 12LED 40K 24V 40 L50 | No |
| 911401738862 | BCP381 24LED 40K 24V 40 L100 | No |
| 911401739022 | BCP381 6LED 40K 24V 40 L30 | No |
| 911401739242 | BCP382 18LED 40K 24V A2 L50 | No |
| 911401739262 | BCP382 18LED 40K 24V 17 L50 | No |
| 911401739462 | BCP382 36LED 40K 24V A2 L100 | No |
| 911401739482 | BCP382 36LED 40K 24V 17 L100 | No |
| 911401739502 | BCP382 36LED 40K 24V 40 L100 | No |
| 911401739702 | BCP382 9LED 40K 24V 17 L30 | No |
| 911401738682 | BCP381 12LED 40K 24V A2 L50 | No |
| 911401738842 | BCP381 24LED 40K 24V A2 L100 | No |
| 911401739002 | BCP381 6LED 40K 24V A2 L30 | No |

## Light Technical

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color Temperature (Nom) | Optical cover type | Color rendering index (CRI) | Luminous Flux |
|---|---|---|---|---|---|---|---|
| 911401779982 | BCP386 12LED 27K 24V 60 L30 | - | Warm white | 2700 K | Clear glass | 80 | 200 lm |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | - | Warm white | 3000 K | Clear glass | 80 | 195 lm |
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | - | Neutral white | 4000 K | Clear glass | 80 | 205 lm |

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color Temperature (Nom) | Optical cover type | Color rendering index (CRI) | Luminous Flux |
|---|---|---|---|---|---|---|---|
| 911401780102 | BCP386 12LED RGBNW 24V 45 L30 DMX | - | Red, green, blue and white | - | Clear glass | - | 150 lm |
| 911401780122 | BCP386 12LED RGBNW 24V A11 L30 DMX | - | Red, green, blue and white | - | Clear glass | - | 145 lm |
| 911401780192 | BCP386 30LED 30K 24V 45 L50 | - | Warm white | 3000 K | Clear glass | 80 | 490 lm |
| 911401780232 | BCP386 30LED 27K 24V 60 L50 | - | Warm white | 2700 K | Clear glass | 80 | 495 lm |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | - | Warm white | 2700 K | Clear glass | 80 | 485 lm |
| 911401780312 | BCP386 30LED 30K 24V A11 L50 | - | Warm white | 3000 K | Clear glass | 80 | 485 lm |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | - | Neutral white | 4000 K | Clear glass | 80 | 515 lm |
| 911401780352 | BCP386 30LED RGBNW 24V 45 L50 DMX | - | Red, green, blue and white | - | Clear glass | - | 390 lm |
| 911401780362 | BCP386 30LED RGBWW 24V A11 L50 DMX | - | Red, green, blue and white | - | Clear glass | - | 360 lm |
| 911401780372 | BCP386 30LED RGBNW 24V A11 L50 DMX | - | Red, green, blue and white | - | Clear glass | - | 375 lm |
| 911401780482 | BCP386 60LED 27K 24V 60 L100 | - | Warm white | 2700 K | Clear glass | 80 | 985 lm |
| 911401780502 | BCP386 60LED 30K 24V 60 L100 | - | Warm white | 3000 K | Clear glass | 80 | 985 lm |
| 911401780522 | BCP386 60LED 40K 24V 60 L100 | - | Neutral white | 4000 K | Clear glass | 80 | 1,045 lm |
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | - | Warm white | 3000 K | Clear glass | 80 | 960 lm |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | - | Neutral white | 4000 K | Clear glass | 80 | 1,020 lm |
| 911401780592 | BCP386 60LED RGBWW 24V 45 L100 DMX | - | Red, green, blue and white | - | Clear glass | - | 720 lm |
| 911401780602 | BCP386 60LED RGBNW 24V 45 L100 DMX | - | Red, green, blue and white | - | Clear glass | - | 750 lm |
| 911401780612 | BCP386 60LED RGBWW 24V A11 L100 DMX | - | Red, green, blue and white | - | Clear glass | - | 695 lm |
| 911401780622 | BCP386 60LED RGBNW 24V A11 L100 DMX | - | Red, green, blue and white | - | Clear glass | - | 730 lm |
| 911401780632 | BCP386 60LED RGB 24V 30 L100 DMX | - | Red, green and blue | - | Clear glass | - | 375 lm |
| 911401780642 | BCP386 60LED RGB 24V 45 L100 DMX | - | Red, green and blue | - | Clear glass | - | 375 lm |
| 911401780652 | BCP386 60LED RGB 24V A3 L100 DMX | - | Red, green and blue | - | Clear glass | - | 345 lm |
| 911401738662 | BCP381 12LED 30K 24V 40 L50 | 40° x 40° | Warm white | 3000 K | Clear flat | 80 | 842 lm |
| 911401738782 | BCP381 24LED 27K 24V 40 L100 | 40° x 40° | Warm white | 2700 K | Clear flat | 80 | 1,651 lm |
| 911401738822 | BCP381 24LED 30K 24V 40 L100 | 40° x 40° | Warm white | 3000 K | Clear flat | 80 | 1,651 lm |
| 911401738982 | BCP381 6LED 30K 24V 40 L30 | 40° x 40° | Warm white | 3000 K | Clear flat | 80 | 430 lm |
| 911401739162 | BCP382 18LED 27K 24V 40 L50 | 40° x 40° | Warm white | 2700 K | Clear flat | 80 | 1,208 lm |
| 911401739222 | BCP382 18LED 30K 24V 40 L50 | 40° x 40° | Warm white | 3000 K | Clear flat | 80 | 1,208 lm |
| 911401739382 | BCP382 36LED 27K 24V 40 L100 | 40° x 40° | Warm white | 2700 K | Clear flat | 80 | 2,367 lm |
| 911401739422 | BCP382 36LED 30K 24V 17 L100 | 17° x 17° | Warm white | 3000 K | Clear flat | 80 | 2,345 lm |
| 911401739442 | BCP382 36LED 30K 24V 40 L100 | 40° x 40° | Warm white | 3000 K | Clear flat | 80 | 2,367 lm |
| 911401739602 | BCP382 9LED 27K 24V 40 L30 | 40° x 40° | Warm white | 2700 K | Clear flat | 80 | 619 lm |
| 911401739642 | BCP382 9LED 30K 24V 17 L30 | 17° x 17° | Warm white | 3000 K | Clear flat | 80 | 610 lm |
| 911401739662 | BCP382 9LED 30K 24V 40 L30 | 40° x 40° | Warm white | 3000 K | Clear flat | 80 | 619 lm |
| 911401739182 | BCP382 18LED 30K 24V A2 L50 | 16° x 35° | Warm white | 3000 K | Clear flat | 80 | 1,221 lm |
| 911401739342 | BCP382 36LED 27K 24V A2 L100 | 16° x 35° | Warm white | 2700 K | Clear flat | 80 | 2,393 lm |
| 911401739402 | BCP382 36LED 30K 24V A2 L100 | 16° x 35° | Warm white | 3000 K | Clear flat | 80 | 2,393 lm |
| 911401739622 | BCP382 9LED 30K 24V A2 L30 | 16° x 35° | Warm white | 3000 K | Clear flat | 80 | 623 lm |
| 911401738602 | BCP381 12LED 27K 24V A2 L50 | 16° x 35° | Warm white | 2700 K | Clear flat | 80 | 848 lm |
| 911401738642 | BCP381 12LED 30K 24V A2 L50 | 16° x 35° | Warm white | 3000 K | Clear flat | 80 | 848 lm |
| 911401738802 | BCP381 24LED 30K 24V A2 L100 | 16° x 35° | Warm white | 3000 K | Clear flat | 80 | 1,663 lm |

| Order Code | Full Product Name | Luminaire light beam spread | Light source color | Correlated Color Temperature (Nom) | Optical cover type | Color rendering index (CRI) | Luminous Flux |
|---|---|---|---|---|---|---|---|
| 911401738962 | BCP381 6LED 30K 24V A2 L30 | 16° x 35° | Warm white | 3000 K | Clear flat | 80 | 432 lm |
| 911401738702 | BCP381 12LED 40K 24V 40 L50 | 40° x 40° | Neutral white | 4000 K | Clear flat | 80 | 910 lm |
| 911401738862 | BCP381 24LED 40K 24V 40 L100 | 40° x 40° | Neutral white | 4000 K | Clear flat | 80 | 1,783 lm |
| 911401739022 | BCP381 6LED 40K 24V 40 L30 | 40° x 40° | Neutral white | 4000 K | Clear flat | 80 | 464 lm |
| 911401739242 | BCP382 18LED 40K 24V A2 L50 | 16° x 35° | Neutral white | 4000 K | Clear flat | 80 | 1,318 lm |
| 911401739262 | BCP382 18LED 40K 24V 17 L50 | 17° x 17° | Neutral white | 4000 K | Clear flat | 80 | 1,292 lm |
| 911401739462 | BCP382 36LED 40K 24V A2 L100 | 16° x 35° | Neutral white | 4000 K | Clear flat | 80 | 2,584 lm |
| 911401739482 | BCP382 36LED 40K 24V 17 L100 | 17° x 17° | Neutral white | 4000 K | Clear flat | 80 | 2,533 lm |
| 911401739502 | BCP382 36LED 40K 24V 40 L100 | 40° x 40° | Neutral white | 4000 K | Clear flat | 80 | 2,557 lm |
| 911401739702 | BCP382 9LED 40K 24V 17 L30 | 17° x 17° | Neutral white | 4000 K | Clear flat | 80 | 659 lm |
| 911401738682 | BCP381 12LED 40K 24V A2 L50 | 16° x 35° | Neutral white | 4000 K | Clear flat | 80 | 916 lm |
| 911401738842 | BCP381 24LED 40K 24V A2 L100 | 16° x 35° | Neutral white | 4000 K | Clear flat | 80 | 1,796 lm |
| 911401739002 | BCP381 6LED 40K 24V A2 L30 | 16° x 35° | Neutral white | 4000 K | Clear flat | 80 | 467 lm |

## Operating and Electrical

| Order Code | Full Product Name | Power Consumption |
|---|---|---|
| 911401779982 | BCP386 12LED 27K 24V 60 L30 | 3 W |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | 3 W |
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | 3 W |
| 911401780102 | BCP386 12LED RGBNW 24V 45 L30 DMX | 3 W |
| 911401780122 | BCP386 12LED RGBNW 24V A11 L30 DMX | 3 W |
| 911401780192 | BCP386 30LED 30K 24V 45 L50 | 7.5 W |
| 911401780232 | BCP386 30LED 27K 24V 60 L50 | 7.5 W |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | 7.5 W |
| 911401780312 | BCP386 30LED 30K 24V A11 L50 | 7.5 W |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | 7.5 W |
| 911401780352 | BCP386 30LED RGBNW 24V 45 L50 DMX | 8 W |
| 911401780362 | BCP386 30LED RGBWW 24V A11 L50 DMX | 8 W |
| 911401780372 | BCP386 30LED RGBNW 24V A11 L50 DMX | 8 W |
| 911401780482 | BCP386 60LED 27K 24V 60 L100 | 15 W |
| 911401780502 | BCP386 60LED 30K 24V 60 L100 | 15 W |
| 911401780522 | BCP386 60LED 40K 24V 60 L100 | 15 W |
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | 15 W |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | 15 W |
| 911401780592 | BCP386 60LED RGBWW 24V 45 L100 DMX | 15 W |
| 911401780602 | BCP386 60LED RGBNW 24V 45 L100 DMX | 15 W |
| 911401780612 | BCP386 60LED RGBWW 24V A11 L100 DMX | 15 W |
| 911401780622 | BCP386 60LED RGBNW 24V A11 L100 DMX | 15 W |
| 911401780632 | BCP386 60LED RGB 24V 30 L100 DMX | 15 W |
| 911401780642 | BCP386 60LED RGB 24V 45 L100 DMX | 15 W |
| 911401780652 | BCP386 60LED RGB 24V A3 L100 DMX | 15 W |
| 911401738662 | BCP381 12LED 30K 24V 40 L50 | 12 W |
| 911401738782 | BCP381 24LED 27K 24V 40 L100 | 24 W |
| 911401738822 | BCP381 24LED 30K 24V 40 L100 | 24 W |
| 911401738982 | BCP381 6LED 30K 24V 40 L30 | 6 W |

| Order Code | Full Product Name | Power Consumption |
|---|---|---|
| 911401739162 | BCP382 18LED 27K 24V 40 L50 | 18 W |
| 911401739222 | BCP382 18LED 30K 24V 40 L50 | 18 W |
| 911401739382 | BCP382 36LED 27K 24V 40 L100 | 36 W |
| 911401739422 | BCP382 36LED 30K 24V 17 L100 | 36 W |
| 911401739442 | BCP382 36LED 30K 24V 40 L100 | 36 W |
| 911401739602 | BCP382 9LED 27K 24V 40 L30 | 9 W |
| 911401739642 | BCP382 9LED 30K 24V 17 L30 | 9 W |
| 911401739662 | BCP382 9LED 30K 24V 40 L30 | 9 W |
| 911401739182 | BCP382 18LED 30K 24V A2 L50 | 18 W |
| 911401739342 | BCP382 36LED 27K 24V A2 L100 | 36 W |
| 911401739402 | BCP382 36LED 30K 24V A2 L100 | 36 W |
| 911401739622 | BCP382 9LED 30K 24V A2 L30 | 9 W |
| 911401738602 | BCP381 12LED 27K 24V A2 L50 | 12 W |
| 911401738642 | BCP381 12LED 30K 24V A2 L50 | 12 W |
| 911401738802 | BCP381 24LED 30K 24V A2 L100 | 24 W |
| 911401738962 | BCP381 6LED 30K 24V A2 L30 | 6 W |
| 911401738702 | BCP381 12LED 40K 24V 40 L50 | 12 W |
| 911401738862 | BCP381 24LED 40K 24V 40 L100 | 24 W |
| 911401739022 | BCP381 6LED 40K 24V 40 L30 | 6 W |
| 911401739242 | BCP382 18LED 40K 24V A2 L50 | 18 W |
| 911401739262 | BCP382 18LED 40K 24V 17 L50 | 18 W |
| 911401739462 | BCP382 36LED 40K 24V A2 L100 | 36 W |
| 911401739482 | BCP382 36LED 40K 24V 17 L100 | 36 W |
| 911401739502 | BCP382 36LED 40K 24V 40 L100 | 36 W |
| 911401739702 | BCP382 9LED 40K 24V 17 L30 | 9 W |
| 911401738682 | BCP381 12LED 40K 24V A2 L50 | 12 W |
| 911401738842 | BCP381 24LED 40K 24V A2 L100 | 24 W |
| 911401739002 | BCP381 6LED 40K 24V A2 L30 | 6 W |

## Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|---|---|---|
| 911401779982 | BCP386 12LED 27K 24V 60 L30 | No |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | No |
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | No |
| 911401780102 | BCP386 12LED RGBNW 24V 45 L30 DMX | Yes |
| 911401780122 | BCP386 12LED RGBNW 24V A11 L30 DMX | Yes |
| 911401780192 | BCP386 30LED 30K 24V 45 L50 | No |
| 911401780232 | BCP386 30LED 27K 24V 60 L50 | No |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | No |
| 911401780312 | BCP386 30LED 30K 24V A11 L50 | No |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | No |
| 911401780352 | BCP386 30LED RGBNW 24V 45 L50 DMX | Yes |
| 911401780362 | BCP386 30LED RGBWW 24V A11 L50 DMX | Yes |
| 911401780372 | BCP386 30LED RGBNW 24V A11 L50 DMX | Yes |
| 911401780482 | BCP386 60LED 27K 24V 60 L100 | No |
| 911401780502 | BCP386 60LED 30K 24V 60 L100 | No |
| 911401780522 | BCP386 60LED 40K 24V 60 L100 | No |
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | No |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | No |
| 911401780592 | BCP386 60LED RGBWW 24V 45 L100 DMX | Yes |
| 911401780602 | BCP386 60LED RGBNW 24V 45 L100 DMX | Yes |
| 911401780612 | BCP386 60LED RGBWW 24V A11 L100 DMX | Yes |
| 911401780622 | BCP386 60LED RGBNW 24V A11 L100 DMX | Yes |
| 911401780632 | BCP386 60LED RGB 24V 30 L100 DMX | Yes |
| 911401780642 | BCP386 60LED RGB 24V 45 L100 DMX | Yes |
| 911401780652 | BCP386 60LED RGB 24V A3 L100 DMX | Yes |
| 911401738662 | BCP381 12LED 30K 24V 40 L50 | No |
| 911401738782 | BCP381 24LED 27K 24V 40 L100 | No |
| 911401738822 | BCP381 24LED 30K 24V 40 L100 | No |
| 911401738982 | BCP381 6LED 30K 24V 40 L30 | No |

| Order Code | Full Product Name | Dimmable |
|---|---|---|
| 911401739162 | BCP382 18LED 27K 24V 40 L50 | No |
| 911401739222 | BCP382 18LED 30K 24V 40 L50 | No |
| 911401739382 | BCP382 36LED 27K 24V 40 L100 | No |
| 911401739422 | BCP382 36LED 30K 24V 17 L100 | No |
| 911401739442 | BCP382 36LED 30K 24V 40 L100 | No |
| 911401739602 | BCP382 9LED 27K 24V 40 L30 | No |
| 911401739642 | BCP382 9LED 30K 24V 17 L30 | No |
| 911401739662 | BCP382 9LED 30K 24V 40 L30 | No |
| 911401739182 | BCP382 18LED 30K 24V A2 L50 | No |
| 911401739342 | BCP382 36LED 27K 24V A2 L100 | No |
| 911401739402 | BCP382 36LED 30K 24V A2 L100 | No |
| 911401739622 | BCP382 9LED 30K 24V A2 L30 | No |
| 911401738602 | BCP381 12LED 27K 24V A2 L50 | No |
| 911401738642 | BCP381 12LED 30K 24V A2 L50 | No |
| 911401738802 | BCP381 24LED 30K 24V A2 L100 | No |
| 911401738962 | BCP381 6LED 30K 24V A2 L30 | No |
| 911401738702 | BCP381 12LED 40K 24V 40 L50 | No |
| 911401738862 | BCP381 24LED 40K 24V 40 L100 | No |
| 911401739022 | BCP381 6LED 40K 24V 40 L30 | No |
| 911401739242 | BCP382 18LED 40K 24V A2 L50 | No |
| 911401739262 | BCP382 18LED 40K 24V 17 L50 | No |
| 911401739462 | BCP382 36LED 40K 24V A2 L100 | No |
| 911401739482 | BCP382 36LED 40K 24V 17 L100 | No |
| 911401739502 | BCP382 36LED 40K 24V 40 L100 | No |
| 911401739702 | BCP382 9LED 40K 24V 17 L30 | No |
| 911401738682 | BCP381 12LED 40K 24V A2 L50 | No |
| 911401738842 | BCP381 24LED 40K 24V A2 L100 | No |
| 911401739002 | BCP381 6LED 40K 24V A2 L30 | No |

## Approval and Application

| Order Code | Full Product Name | Flammability mark |
|---|---|---|
| 911401779982 | BCP386 12LED 27K 24V 60 L30 | - |
| 911401780062 | BCP386 12LED 30K 24V A11 L30 | - |
| 911401780082 | BCP386 12LED 40K 24V A11 L30 | - |
| 911401780102 | BCP386 12LED RGBNW 24V 45 L30 DMX | - |
| 911401780122 | BCP386 12LED RGBNW 24V A11 L30 DMX | - |
| 911401780192 | BCP386 30LED 30K 24V 45 L50 | - |
| 911401780232 | BCP386 30LED 27K 24V 60 L50 | - |
| 911401780292 | BCP386 30LED 27K 24V A11 L50 | - |
| 911401780312 | BCP386 30LED 30K 24V A11 L50 | - |
| 911401780332 | BCP386 30LED 40K 24V A11 L50 | - |
| 911401780352 | BCP386 30LED RGBNW 24V 45 L50 DMX | - |
| 911401780362 | BCP386 30LED RGBWW 24V A11 L50 DMX | - |
| 911401780372 | BCP386 30LED RGBNW 24V A11 L50 DMX | - |
| 911401780482 | BCP386 60LED 27K 24V 60 L100 | - |

| Order Code | Full Product Name | Flammability mark |
|---|---|---|
| 911401780502 | BCP386 60LED 30K 24V 60 L100 | - |
| 911401780522 | BCP386 60LED 40K 24V 60 L100 | - |
| 911401780562 | BCP386 60LED 30K 24V A11 L100 | - |
| 911401780582 | BCP386 60LED 40K 24V A11 L100 | - |
| 911401780592 | BCP386 60LED RGBWW 24V 45 L100 DMX | - |
| 911401780602 | BCP386 60LED RGBNW 24V 45 L100 DMX | - |
| 911401780612 | BCP386 60LED RGBWW 24V A11 L100 DMX | - |
| 911401780622 | BCP386 60LED RGBNW 24V A11 L100 DMX | - |
| 911401780632 | BCP386 60LED RGB 24V 30 L100 DMX | - |
| 911401780642 | BCP386 60LED RGB 24V 45 L100 DMX | - |
| 911401780652 | BCP386 60LED RGB 24V A3 L100 DMX | - |
| 911401738662 | BCP381 12LED 30K 24V 40 L50 | For mounting on normally flammable surfaces |
| 911401738782 | BCP381 24LED 27K 24V 40 L100 | For mounting on normally flammable surfaces |

# UniStrip G4

| Order Code | Full Product Name | Flammability mark |
|---|---|---|
| 911401738822 | BCP381 24LED 30K 24V 40 L100 | For mounting on normally flammable surfaces |
| 911401738982 | BCP381 6LED 30K 24V 40 L30 | For mounting on normally flammable surfaces |
| 911401739162 | BCP382 18LED 27K 24V 40 L50 | For mounting on normally flammable surfaces |
| 911401739222 | BCP382 18LED 30K 24V 40 L50 | For mounting on normally flammable surfaces |
| 911401739382 | BCP382 36LED 27K 24V 40 L100 | For mounting on normally flammable surfaces |
| 911401739422 | BCP382 36LED 30K 24V 17 L100 | For mounting on normally flammable surfaces |
| 911401739442 | BCP382 36LED 30K 24V 40 L100 | For mounting on normally flammable surfaces |
| 911401739602 | BCP382 9LED 27K 24V 40 L30 | For mounting on normally flammable surfaces |
| 911401739642 | BCP382 9LED 30K 24V 17 L30 | For mounting on normally flammable surfaces |
| 911401739662 | BCP382 9LED 30K 24V 40 L30 | For mounting on normally flammable surfaces |
| 911401739182 | BCP382 18LED 30K 24V A2 L50 | For mounting on normally flammable surfaces |
| 911401739342 | BCP382 36LED 27K 24V A2 L100 | For mounting on normally flammable surfaces |
| 911401739402 | BCP382 36LED 30K 24V A2 L100 | For mounting on normally flammable surfaces |
| 911401739622 | BCP382 9LED 30K 24V A2 L30 | For mounting on normally flammable surfaces |
| 911401738602 | BCP381 12LED 27K 24V A2 L50 | For mounting on normally flammable surfaces |

| Order Code | Full Product Name | Flammability mark |
|---|---|---|
| 911401738642 | BCP381 12LED 30K 24V A2 L50 | For mounting on normally flammable surfaces |
| 911401738802 | BCP381 24LED 30K 24V A2 L100 | For mounting on normally flammable surfaces |
| 911401738962 | BCP381 6LED 30K 24V A2 L30 | For mounting on normally flammable surfaces |
| 911401738702 | BCP381 12LED 40K 24V 40 L50 | For mounting on normally flammable surfaces |
| 911401738862 | BCP381 24LED 40K 24V 40 L100 | For mounting on normally flammable surfaces |
| 911401739022 | BCP381 6LED 40K 24V 40 L30 | For mounting on normally flammable surfaces |
| 911401739242 | BCP382 18LED 40K 24V A2 L50 | For mounting on normally flammable surfaces |
| 911401739262 | BCP382 18LED 40K 24V 17 L50 | For mounting on normally flammable surfaces |
| 911401739462 | BCP382 36LED 40K 24V A2 L100 | For mounting on normally flammable surfaces |
| 911401739482 | BCP382 36LED 40K 24V 17 L100 | For mounting on normally flammable surfaces |
| 911401739502 | BCP382 36LED 40K 24V 40 L100 | For mounting on normally flammable surfaces |
| 911401739702 | BCP382 9LED 40K 24V 17 L30 | For mounting on normally flammable surfaces |
| 911401738682 | BCP381 12LED 40K 24V A2 L50 | For mounting on normally flammable surfaces |
| 911401738842 | BCP381 24LED 40K 24V A2 L100 | For mounting on normally flammable surfaces |
| 911401739002 | BCP381 6LED 40K 24V A2 L30 | For mounting on normally flammable surfaces |

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.