


**PHILIPS
LUMEC**

Urban

Domus



Bring balance to your environment

The Philips Lumec Domus family of LED pendant and post top luminaires – Domus, Domus 55, and Domus Small – are all designed to complement each other and bring balance to any environment. Their charm is undeniable. Simplicity, refinement, and elegance, all fuse together to create harmonious beauty through designed equilibrium.

Features and benefits

- Versatile luminaires with classic shape to fit in any area or project
- Constructed from top-quality materials to maintain excellent performance in the most demanding environments
- Multiple lumen packages with output of up to 17,483 lumens
- Type 2, 3, 4, and 5 optics available
- 4000K and 3000K color temperatures available
- Dimming driver standard
- Multiple driver options and programmed dimming options available



DMS50

Domus LED large pendant

The Domus 50 is one of the most versatile luminaires offered by Philips Lumec. This classic shape was one of the first in a line of pioneering Philips Lumec designs. Domus offers a subtly refined design that balances shape, dimension and proportion.

Lumen range: 3,895 - 17,483

Wattage range: 35 - 180

Efficacy range: 95 - 118



DMS55

Domus LED large pendant

The Domus' timeless design has proven to be one of the most adaptable shapes we offer and with the Domus 55 you will get even more versatility. Designed with a higher profile than it's counterparts, the Domus 55 offers flexible mounting options such as the side arm mount.

Lumen range: 3,895 - 17,483

Wattage range: 35 - 180

Efficacy range: 95 - 118



DMS60

Domus LED large post top

Wherever it is installed, the Domus LED post top creates harmony. Whether you are paring it with the rest of the Domus family or using it on its own in your projects, the Domus 60 becomes an integral part of the landscape design.

Lumen range: 3,370-7,309

Wattage range: 37-80

Efficacy range: 84-96



DOS

Domus LED small post top

The Domus small is the perfect complement to the rest of the Domus family. For example, you could install the Domus in a parking lot, and the Domus small along the paths leading from the parking lot to the building.

Lumen range: 2,333-5,149

Wattage range: 29-54

Efficacy range: 81-99

Unbeatable charm for your projects

See how Philips Lumec Domus LED luminaires can help you to achieve consistency across your project scope with refined design and ingenious craftsmanship.

Visit philips.com/luminaires for more information.

Prior to ordering, consult specification sheets. Please visit www.philips.com/luminaires for the most current information, notes, and exclusions.



© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd.
Markham, ON,
Canada L6C 2S3
Tel. 800-668-9008