



© 2018 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLu-1801BN 02/18 [philips.com/luminaires](https://philips.com/luminaires)

Philips Lighting  
North America Corporation  
200 Franklin Square Drive  
Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd,  
Markham, ON,  
Canada L6C 2S3  
Tel. 800-668-9008

**PHILIPS  
LUMEC**

Urban

Candela

CAND1 / CAND2 / CAND3



Traditional evolution  
**giving you options**

# Candela

## LED luminaires

Attention to detail is perhaps the most important aspect of the Philips Lumec Candela LED post top and pendant luminaires. From the European inspired nautical design to the wide range of options available, to the wide assortment of complementary products that harmonize with this luminaire, no stone has been left unturned to give decision makers unprecedented flexibility and design options. Whatever the project, be it town or country, the presence of Candela luminaires will bring architectural and landscaped developments to new heights. Powered by the Philips EcoSwap LED light engine, Candela provides longevity and energy savings.



### Benefits


- Wide selection of options and styles for greater design freedom.
- Post top and pendant versions available to suit a wide range of applications.
- Powered by the Philips EcoSwap LED light engine providing longevity and energy savings.
- Lumen packages with output of up to 8,111 lumens.
- Available in wall mount versions.
- Type 3 & 5 optics available.
- Color temperatures 4000K and 3000K are available.



### Pendant



### Dimensions



**CAND1:**  
EPA: 1.85 sq. ft.  
Weight: 58 lbs (26.4 kg)

**CAND3:**  
EPA: 2.36 sq. ft.  
Weight: 55 lbs (25.85 kg)

**Lumen range:** 4823 – 8111

**Wattage range:** 50, 70

**Efficacy range:** 100-117





**Lumen range:** 2649–5960


**Wattage range:** 50, 70

**Efficacy range:** 53–87

### Post top



### Dimensions



**CAND2:**

EPA: 1.85 sq. ft.

Weight: 44 lbs (20 kg)

## Enhance your projects

See how the **Philips Lumec Candela LED post top and pendant luminaires** are a sure choice for a harmonious integration of any architectural site or urban setting.

Visit **[philips.com/luminaires](http://philips.com/luminaires)** for more information.

*Prior to ordering, consult specification sheets for the most current information, notes, and exclusions.*

