

by (s) ignify

Site & Area

**PureForm** 





# Creativity and continuity can coexist

The **PureForm** family consists of medium and large area luminaires, a wall sconce, a bollard, and a post top. These luminaires were designed to complement each other, yet each product fulfills its own unique purpose in style. This ensures that the luminaires bring a cohesive feeling to your project, while also enhancing your creative vision. At a glance, they are obviously all part of one family, but each product also makes a strong individual aesthetic statement.

# Make a distinctive again and again



# Large area, precision optics P34

- Precision optics designed to maximize spacing with exceptional uniformity
- Type 2, 3, 4, 5, 5W, AFR, and BLC optical distributions
- · Back light control capability
- Up to 50,000 lumens
- Up to 133 lumens per watt
- Retrofit arm, wall mount, adjustable slipfitter



# Medium area, precision optics P26

- Precision optics designed to maximize spacing with exceptional uniformity
- Type 2, 3, 4, 5, 5W, AFR, and BLC optical distributions
- Back light control capability
- Up to 28,900 lumens
- Up to 150 lumens per watt
- Retrofit arm, wall mount, adjustable slipfitter



# Medium area, comfort optics P26

- Comfort optics designed to enhance visual comfort by reducing glare
- Suitable for mounting height up to 25'
- Type 2, 3, and 5 optical distributions
- · Up to 9,100 lumens
- · Retrofit arm, wall mount, adjustable slipfitter

# statement

## **PureForm family benefits**

- Sleek, low profile designs blend with architecture.
- Multiple product types accommodate different application areas throughout a building exterior, while maintaining a unified aesthetic.
- Comfort optics are available in the post top, wall sconce, and medium area, designed to enhance visual comfort by reducing glare.
- Medium area and wall sconce feature both comfort optics and precision optics, making them suitable for a range of mounting heights and lumen outputs.
- Seamless integration with the latest controls solutions across the entire family makes management easy, further enhancing value.





# Wall sconce, precision optics PWS

- Precision optics designed to maximize spacing with exceptional uniformity
- Higher lumen output and excellent performance allow for a reduction in pole count
- Type 2, 3, and 4 optical distributions
- Up to 21,800 lumens
- Up to 137 lumens per watt
- Emergency battery backup option



# Wall sconce, comfort optics PWS

- Comfort optics designed to enhance visual comfort by reducing glare
- Type 2, 3, and 4 optical distributions
- · Up to 9,600 lumens
- · Integral motion sensor option
- $\cdot$  Emergency battery backup option



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873

Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008