


# Unlock your connectivity with Interact

## Make the leap from smart lighting to super smart lighting

Connectivity is the future and key to unlocking your smart building potential. Interact is a connected system with wireless luminaire level controls and integral occupancy & daylight sensing.

## Start simple and lay the foundation

- Smart lighting with luminaire integrated occupancy and daylight sensor.
- Save up to **80%** on installation and material cost compared with more complex systems.<sup>1</sup>



## Features

- ✓ Motion, daylight sensing and grouping can be done right out of the box.
- ✓ A gateway can be added at any time for additional features, such as scheduling and remote management.
- ✓ Set up is simple and can be done from your smart phone.
- ✓ Interact delivers a consistent experience between indoor and outdoor lighting control.
- ✓ Interact is the only system that offers wireless connectivity and control for lamps, luminaires, and retrofit kits.



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

All trademarks are owned by Signify Holding or their respective owners.

PGC-2306PM 03/23

[www.gardcolighting.com](http://www.gardcolighting.com)

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008



by Signify

Outdoor

OptiForm

Site and Area



# Bring innovation to your site

# OptiForm site and area luminaires



## OptiForm small OPF-S

- 25,000-22,000 lumens
- Up to 183 LPW
- 11 lbs



## OptiForm medium OPF-M

- 13,500-34,000 lumens
- Up to 190 LPW
- 13 lbs



## OptiForm large OPF-L

- 34,000-67,000 lumens
- Up to 190 LPW
- 26 lbs

# Installation designed with you in mind

- ✓ Retrofit-ready standard arm mounts to existing drill patterns

- ✓ Mounts to round or square pole standard



- ✓ Two-piece housing allows for mounting to be installed first, and luminaire second




Learn more about OptiForm  
Visit [gardcolighting.com/optiform](http://gardcolighting.com/optiform)


# Illumination your way

- ✓ Three sizes with output ranging from 2,500 to 67,000 lumens
- ✓ Leading efficacy up to 192 lumens per watt
- ✓ Two light engines in the small size
- ✓ 11 optical distributions


Type 2 Medium




Type 3 Medium



Type 4 Medium



Type 4 Wide



Type 5 Medium




Type 5 Narrow



Type 5 Wide



Autofront Row



Back Light Control



LEED Corner Left



LEED Corner Right

