LIGHTOLIER

by (signify

Designed with simplicit in mind

CorePro LED

Track Heads with AccuRender technology



CorePro

Track Heads

Lightolier is a global market leader widely recognized for its innovative LED lighting solutions with an unmatched commitment to technology leadership, reliability, visual appeal and high performance. Track and recessed multiple cylinder utilize the same LED and optical architecture. They are designed to meet the most demanding accent lighting applications allowing for lighting and aesthetic consistency within any space.



AccuRender Technology (CRI 90+)

The right light brings colors to life. Our new AccuRender technology helps ensure colors are rendered more accurately and consistently, while doing so as efficiently as CRI 80 products.



Standard CRI 80 Good color rendering and high efficacy



Standard CRI 90 Better color rendering and low efficacy

AccuRender Best color rendering, color preference and high efficacy

Enjoy design flexibility

- Full range of products and options:
- Available soon across Lightolier portfolio for application flexibility
- Multiple color temperatures (CCTs) and lumen packages are offered

Promote savings

High efficacy, with no penalty:

- Energy efficacy compares well to conventional 80 CRI
- Up to 25% more energy savings vs competitor 90 CRI¹
- Helps meet Title 24 requirements

Show your true colors

High color rendering:

- True to life colors to help energize your environment and render better flesh tones critical for healthcare hospitality and retail applications.
- $\begin{array}{ll} R_{a} \text{ up to 94 CRI} & \cdot & R_{f} \text{ up to 92 TM-30} \\ R_{9} \text{ up to 67 CRI} & & R_{f,h1} \text{ up to 91 TM-30} \\ G_{a} \text{ up to 99 CRI} & & R_{9} \text{ up to 100 TM-30} \\ C_{9} \text{ up to 94 CRI} & & R_{cs,h1} \text{ up to -5\% TM-30} \end{array}$

Achieve color balance

Best in class color consistency:

 Promote aesthetic harmony in your space with ≤ 2 SDCM

Crisp White

Dial-up the drama of your display. Highlight the variances in white tones, add contrast to blacks and create a real pleasing sparkle effect while retaining warm skin tones.

Premium White

The new benchmark for retail fashion. Delivering stronger and brighter whites via the best lighting technology on the market with minimal compromise to energy savings.


Premium Color


Enhance the contrast between colors and whites to achieve new depths of color rendering for a vibrant saturated fashionforward visual experience that won't affect the atmosphere and will have a positive effect on energy efficiency.

Standard Color

Standard CRI 90

LED Color Recipes (90CRI/3000K)





LED upgrade with ease

CorePro LED track heads combine classic, small form design with the benefits of LED technology. Now available with AccuRender 90+ CRI technology for the highest color quality at the highest efficacy. A completely integrated LED luminaire. By combining the optics, light source, thermal management system and driver into a single housing, this luminaire provides a sleek look suitable for lower mounting heights and smaller spaces. This small, sleek luminaire design offers efficacy of up to 125lm/w.

Benefits

- An affordable solution to convert from traditional technologies to an integrated LED fixture.
- No need to replace halogen lamps and bi-pin sockets.
- Provides the efficiency, output and lifetime only an integrated LED solution can offer.
- Consumes 82% less energy than a 50W MR16.
- Higher flux than available LED MR16 lamps.
- No compatibility concerns with electronic transformers.

LT CorePro LED

Track Heads (1000lm)

Features

- Efficacy: up to 125 lm/w
- Lumens: 1000 lm
- Watts: 9 W (max)
- CRI: 90+
- CCT: 2700 4000 K
- Volts: 120/277V (50/60Hz)
- Lifetime: 100,000 hrs (L80)
- Adapters: Lightolier, Halo, Juno
- Beams: Narrow Flood, Wide Flood





Fixture


example: LTL08RNF927ALVA

| Series | Adapters | Lumens | Beams | CRI/CCT | Finishes | Version VA |
|------------------------------------|----------------------------------|------------------|--|---|---|---------------|
| LT CorePro LED Mini Track Heads | L Lightolier H Halo J Juno | 08 10001m | RNF Narrow Flood 21° RWF Wide Flood 38° | 927 90CRI / 2700K 930 90CRI / 3000K 935 90CRI / 3500K 940 90CRI / 4000K LED Color Recipes CW30 CW30 90CRI / 3000K Crisp White PW30 90CRI / 3000K Premium White PC30 90CRI / 3000K Premium Color | AL Aluminum BK Matte Black WH Matte White | VA Version A |

Assembly









cULus Listed. 5 year warranty. ENERGY STAR[®] certified (excluding Crisp White, Premium White, and Premium Color configurations). Accessories are not Energy Star qualified.

(s)ignify

© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.