

LIGHTOLIER

by  Signify

Downlighting

Calculite
with IntelliHue Powercore technology

4" & 6" Downlight & Wall Wash



The marriage you've been waiting for



Lightolier Calculite LED downlights combined with IntelliHue Powercore technology by Color Kinetics provides the ultimate in flexibility for your downlighting projects.


Calculite LED generation 3 downlight features industry leading visual comfort, excellent uniform illumination over time, and patented installation flexibility. IntelliHue Powercore technology from Color Kinetics provides millions of combinations of precise white and color to maximize potential of architectural appeal in a variety of applications. Calculite LED downlights with IntelliHue Powercore technology from Color Kinetics greatly expands product flexibility in addition to providing peace of mind with precision quality.

For further details and availability, please contact your authorized representative.


© 2021 Signify Holding. All rights reserved.

C4 & C6 Calculite 4" & 6"

Round Downlight & Wall Wash with IntelliHue Powercore technology



Calculite LED 4"



Calculite LED 6"

Features

- **Lumens:** 1500
- **CRI:** 80-90 (white spectrum)
- **CCT:** 2700K - 6500K
- **Shape:** Round
- **Interface:** CK Data Enabler Pro (DMX or Ethernet)
- **Voltage:** 120/277V
- **Trims:** Standard Calculite Downlight & Wall Wash
- **Installation:** Standard Uniframe Non-IC

Frame

example: 6RN

Series	Installation	Voltage / Options
4R 4" Non-IC Round	N New construction	- Universal 120V/277V
6R 6" Non-IC Round	R Remodeler	- Universal 120V/277V

Engine

example: C6L15CKMDMXU

Series	Lumens	Color Kinetics	Beam	Dimming	Voltage
<input type="checkbox"/>					
C4L Calculite LED 4"	15 1500lm	CK IntelliHue by Color Kinetics	M Medium (56°)	DMX Digital Multiplexing	U Universal 120V/277V/347V
C6L Calculite LED 6"			W Wide (76°)		

Trim

example: C6RDLCPP

Series	Aperture	Style	Finish	Flange
<input type="checkbox"/>				
C4 Calculite LED 4"	R Round	DL Downlight	BK Black (anodized)	- White (matte)
C6 Calculite LED 6"		WW Wall Wash ¹	CL Specular clear CC Comfort clear CD Comfort clear diffuse CZ Champagne bronze	P Polished (matches aperture) F Flangeless (CA4RFT/CA6RFT required)
			WH White (matte)	- White (matte) F Flangeless (CA4RFT/CA6RFT required)

Accessories

CA4RFT or CA6RFT	Mud-in ring for use in flangeless trim installations (ordered with a flangeless trim)
C4RVPWH or C6RVPWH	IP65 Rated vandal proof matte white accessory (mounts onto flangeless trims & new construction frame only)

1. Specify wide (W) beam light engine only for wall wash trim option.



Visit [Signify.com/warranties](https://www.signify.com/warranties) for more information on Signify's standard 5-year limited warranty.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.