



Alkco's LED Graphic Wall Illuminators, are an integral part of our MRI product family. Designed to enhance and optimize the illumination of various graphic images. The contemporary look and feel is supported by its thin profile allowing it to meet ADA standards. Furthermore, its unique side hinge enables ease of graphic changes. This product helps foster a relaxing environment with its uniform light appearance, supporting patient ease and relaxation during procedures.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Wall Illuminator ordering guide

example: RVGW024024-42-B

Model Number ¹	LED Color Temp.	Finish ²
—	42 —	
RVGW024024 24x24 nominal RVGW024048 24x48 nominal RVGW048048 48x48 nominal RVGW048060 48x60 nominal	42 4200K	B Black S Silver CC Custom Color

Footnotes:

¹ See page 2 for details. Custom sizes are available upon request.

² Customer to provide color chip to match.



RVGW Relaxview Graphic Wall Illuminator

4200K


Features

- Easy installation and requires minimal maintenance.
- Long life LED source.
- Available in neutral white, black and custom color options.
- Dimmers option to support the whole MRI product family.
- Designed for wall mounting.
- Agion® antimicrobial finish.
- Class 1 low voltage installation.
- Dimming option available on RelaxView Power Distribution Module PDM.
- On/Off and 5 level dimming control available with addition of RelaxView Intelligent Wall Dimmer IWD.

Specifications

- **Construction:** Non-ferrous construction, allowing for no interference with other medical equipment.
- **Finish:** The housing has a polyester powder-coat paint finish with an Agion® antimicrobial finish.
- **Light Source:** LED source densely populated for lower power consumption and uniformity, attached to heat-sink for maximum performance and reliability.
The LED source is available in 4200K white.
- **Electrical:** RelaxView is powered by remote Class 1 low voltage power distribution module(s) (sold separately). Dimming is available. The RelaxView panels do not include a DC power supply. Remote modular Power Distribution Module PDM needed with or without dimmer.
- **Installation:** Easy installation into standard grid or hard ceilings.
- **Listing:** Components are CE or ETL listed and RoHS compliant.
- **Warranty:** Fixture warranted against defects for 5 years from original date of purchase. <https://www.signify.com/en-us/support/warranties>

Dimensions (see chart below for details)



Model No.	Nominal Size (LxW) ¹	Visual Opening (in inches)		Graphic Size (in inches)		Light Box Dimensions (O.D. in inches)			Number of LEDs	Power (W) @24VDC	Current (A) @120VAC	Lum. Flux lm	Illum. Area Sq. In.
		Vert.	Horiz.	Vert.	Horiz.	Vert.	Horiz.	Depth					
RVGW024024	24x24	24.00	24.00	25.00	25.00	25.50	25.50	2.00	576	46.08	0.38	2304	576
RVGW024048	24x48	24.00	48.00	25.00	49.00	25.50	49.50	2.00	1152	92.16	0.77	4608	1152
RVGW048048	48x48	48.00	48.00	49.00	49.00	49.50	49.50	2.00	2304	184.32	1.54	9216	2304
RVGW048060	48x60	48.00	60.00	49.00	61.00	49.50	61.50	2.00	2880	230.40	1.92	11520	2880


Footnotes:

¹ Other sizes are available. Contact factory for pricing.

RVGW Relaxview Graphic Wall Illuminator

4200K

Scene choices



Wall Scene ordering guide

example: GDH2027-BCA

Scene Number ¹	Graphic Protection
—	<input type="checkbox"/> BCA —
GDH2027 Clouds FDL3098 Tropical FDL3139 Desert FDL3798 Garden FDL3015 Landscape FDL3022 Miscellaneous XXXXXX TBD	BCA Back, clear acrylic

Footnotes:

¹ Other scenes available upon request.

Buy American Act of 1933 (BAA):

This product is manufactured in one of our US factories and, as of the date of this document, this product was considered a commercially available off-the-shelf (COTS) item meeting the requirements of the BAA. This BAA designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Prior to ordering, please visit www.signify.com/baa to view a current list of BAA-compliant products to confirm this product's current compliance.



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
 400 Crossing Blvd, Suite 600
 Bridgewater, NJ 08807
 Telephone 800-555-0050

Signify Canada Ltd.
 281 Hillmount Road,
 Markham, ON, Canada L6C 2S3
 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.