



ZBP333 CFRM L470 W470
WH

910925865291



ZBP333 | MINI 300 LED GEN3 ACC.

Mini 300 LED gen3 luminaires, perfect product design and latest LED technology combination for highly efficient light outputs can turn your petrol station into a branded landmark and help visitors to approach safely in visual comfort. Mini 300 LED gen3, the state-of-the-art LED luminaires with light on demand intelligent motion sensing control system takes energy saving to new levels with dimming, but at the same time, ensuring sufficient lighting for orientation and safety. The light scenarios can be tailored to your preference at the first installation or during the lifespan of the products. The optional Master-Slave combination with a built-in presence and light sensor there's no need for an external sensor and one Master Mini 300 LED gen3 can control up to 6 basic luminaires. Not only will this have a positive impact on your investment, it can also lead to additional energy saving. Mini 300 LED gen3 luminaire is so light that it can be installed effortlessly by one person. Luminaire settings can even be changed from ground level using a smart phone or tablet as a remote control,

eliminating the need to work at height. With the free Mini 300 LED App, even the status of the luminaire can be read while standing on the floor. The Mini 300 LED gen3 luminaires in recessed mounted, surface mounted and floodlight versions, which are suitable for undercanopy lighting, is a breakthrough, retrofit solution reduces installation costs.

General Information

Service tag	Yes
Value ladder	Specification

Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Mechanical and Housing

Overall length	520 mm
Overall width	520 mm
Overall height	92 mm
Overall diameter	0 mm
Dimensions (Height x Width x Depth)	92 x 520 x 520 mm
Material	Steel
Ingress protection code	-
Mech. impact protection code	IK08 [5 J vandal-protected]
Accessory color	White
Angle	0°
Net Weight (Piece)	4.900 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	ZBP333 CFRM L470 W470 WH
Full product name	ZBP333 CFRM L470 W470 WH
Full product code	871869699769700
Order code	910925865291
Material Nr. (12NC)	910925865291
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696997697
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696997697
Product family code	ZBP333 [MINI 300 LED GEN3 ACC.]

Dimensional drawing

