

SP340Z SMTE-5 L1500 SI

910925867358



- V, Silver

Philips FlexBlend is an attractive family of surface-mounted and suspended luminaires, next to FlexBlend recessed. The luminaire range is enabling building owners to advance their lighting operations, by offering office-compliant lighting with a return on investment of less than three to four years. FlexBlend provides the required flexibility through an adaptable design. This gives the possibility to install the luminaires easily in the field, at any moment. Even when the luminaire is suspended today, tomorrow it can be adapted to a surface-mounted installation on site. And vice versa. . The suspended and surface-mounted luminaire range fits many different office spaces like open plan offices, corridors, reception areas or meeting rooms. FlexBlend is offered in both lines and as standalone, using the same lighting module. This gives users the option to use FlexBlend as standalone today, and tomorrow, as a line. The controller is integrated in the luminaire. As technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations that can help optimise operations further. For this reason, FlexBlend has all connectivity and future-ready options available. As a System Ready luminaire, it can be paired with lighting management systems such as the Philips SpaceWise, and to software-based lighting systems

such as Interact Office wired (PoE) and Interact Office wireless and/or existing and upcoming sensor innovations. The luminaire range is therefore future-ready and can be delivered without any system component, and in a next phase, in the field to be upgraded. An attractive opportunity for new installations and renovations.

Warnings and Safety

- The product is IP20 & as such is not protected against water ingress and as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not followed and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe use and the product warranty will become void

General Information

Service Tag	Yes
Value ladder	Performance

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Product Data

Order product name	SP340Z SMTE-5 L1500 SI
Full product name	SP340Z SMTE-5 L1500 SI
Full EOC	871951410617800
Order code	910925867358
Material no. (12 NC)	910925867358
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8719514106178
Numerator – packs per outer box	1
EAN/UPC - Case	8719514106178
Product family code	SP340Z [FLEXBLEND S&S ACCESSORIES]

Mechanical and Housing

Overall length	1,500 mm
Material	Stainless steel
Ingress protection code	-
Mech. impact protection code	-
Accessory colour	Silver
Angle	-
Net Weight (Piece)	0.350 kg

Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_910925867358_en_GB.txt	Download 

