PHILIPS

Lighting

GreenSpace Flex Luna

RS378B P8 930 PSU-E WB M43 WP PRO

GreenSpace Flex Luna, 8 W, 930 warm white, IP20/54 | Finger-protected; dust accumulation-protected, splash-proof

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	705 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color rendering index (CRI)	92
Light source color	930 warm white
Unified glare rating CEN	16

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	8 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	75
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	-
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Structured optic
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Lens
Net Weight (Piece)	0.160 kg

GreenSpace Flex Luna

Approval and Application	
CE mark	Yes
Ambient temperature range	-20 to +45 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	RS378B P8 930 PSU-E WB M43 WP PRO

Full product name	RS378B P8 930 PSU-E WB M43 WP PRO
Order code	911401500546
Material Nr. (12NC)	911401500546
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

Dimensional drawing



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.