



GreenSpace Flex Luna

RS378B P17 940 PSU-E WB M70 PRO

GreenSpace Flex Luna, 17.5 W, 940 neutral white, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

| General Information | |
|--|-------------------|
| Light source engine type | LED |
| Value ladder | Performance |
| Light Technical | |
| Luminous Flux | 2,390 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 137 lm/W |
| Color rendering index (CRI) | 92 |
| Light source color | 940 neutral white |
| Unified glare rating CEN | 16 |
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Power Consumption | 17.5 W |
| Power Factor (Fraction) | 0.9 |
| Number of products on MCB of 16 A type B | 52 |

| Protection class IEC | Safety class II |
|------------------------------|--------------------------|
| Controls and Dimming | |
| Dimmable | - |
| Control interface | - |
| Mechanical and Housing | |
| Housing Material | Aluminum Alloy |
| Optical cover material | Polycarbonate |
| Housing Color | Black |
| Optical cover finish | Structured optic |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.35 J reinforced] |
| Optical cover type | Lens |
| Net Weight (Piece) | 0.440 kg |
| Approval and Application | |
| CE mark | Yes |

GreenSpace Flex Luna

| | |
|---------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
|---------------------------|---------------|

Initial Performance (IEC Compliant)

| | |
|-----------------------------|-------------|
| Luminous flux tolerance | -10% / +10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|---------------------------------|
| Order product name | RS378B P17 940 PSU-E WB M70 PRO |
|--------------------|---------------------------------|

| | |
|---------------------------------|---------------------------------|
| Full product name | RS378B P17 940 PSU-E WB M70 PRO |
| Order code | 911401511846 |
| Material Nr. (12NC) | 911401511846 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 18 |

Dimensional drawing

