



GreenSpace Grid

GD309B 3*P33 940 PSU-E WB

GreenUp Grid, 108.9 W, 89.1 W, 940 neutral white, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Grid product family offers a complete range of options with comprehensive control availability, optical solutions and powerful lumen outputs, meanwhile ensures the product reliability and quality within compact luminaire body.

Product data

| General Information | | Protection class IEC | |
|--|-------------------|------------------------------|-------------------------|
| Light source engine type | LED | Safety class II | |
| Value ladder | Performance | Controls and Dimming | |
| Light Technical | | Dimmable | No |
| Luminous Flux | 9,700 lm | Control interface | - |
| Correlated Color Temperature (Nom) | 4000 K | Mechanical and Housing | |
| Luminous Efficacy (rated) (Nom) | 98 lm/W | Housing Material | Aluminum Alloy |
| Color rendering index (CRI) | >90 | Optical cover material | Acrylate |
| Light source color | 940 neutral white | Housing Color | White |
| Operating and Electrical | | Optical cover finish | Frosted |
| Input Voltage | 200 to 240 V | Ingress protection code | IP20 [Finger-protected] |
| Line Frequency | 50 to 60 Hz | Mech. impact protection code | IK03 [0.3 J] |
| Power Consumption | 108.9 89.1 W | Optical cover type | Acrylate |
| Power Factor (Fraction) | 0.9 | Net Weight (Piece) | 2.030 kg |
| Number of products on MCB of 16 A type B | - | | |

GreenSpace Grid

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | No |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|---------------------------|
| Order product name | GD309B 3*P33 940 PSU-E WB |
|--------------------|---------------------------|

| | |
|---------------------------------|---------------------------|
| Full product name | GD309B 3*P33 940 PSU-E WB |
| Full product code | 872016952717199 |
| Order code | 911401560212 |
| Material Nr. (12NC) | 911401560212 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169527171 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8720169538665 |

Dimensional drawing

