



GreenSpace Surface Mount

SM303C P9S 927 PSU NB

GreenSpace Surface Mount, 8.1 W, 9.9 W, 650 lm, 2700 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

| General Information | | Power Factor (Fraction) | | 0.5 |
|------------------------------------|----------------|--|-------------------------|-----------------|
| Light source engine type | LED | Number of products on MCB of 16 A type B | | - |
| Value ladder | Performance | Protection class IEC | | Safety class II |
| Light Technical | | Controls and Dimming | | |
| Luminous Flux | 650 lm | Dimmable | No | |
| Correlated Color Temperature (Nom) | 2700 K | Control interface | - | |
| Luminous Efficacy (rated) (Nom) | 72 lm/W | Mechanical and Housing | | |
| Color rendering index (CRI) | >90 | Housing Material | Aluminum Alloy | |
| Light source color | 927 warm white | Optical cover material | Acrylate | |
| Operating and Electrical | | Housing Color | White | |
| Input Voltage | 200 to 240 V | Optical cover finish | Frosted | |
| Line Frequency | 50 to 60 Hz | Ingress protection code | IP20 [Finger-protected] | |
| Power Consumption | 8.1 9.9 W | Mech. impact protection code | IK03 [0.3 J] | |

GreenSpace Surface Mount

| | |
|--------------------|----------|
| Optical cover type | Acrylate |
| Net Weight (Piece) | 0.391 kg |

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | No |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|-----------------------|
| Order product name | SM303C P9S 927 PSU NB |
|--------------------|-----------------------|

| | |
|---------------------------------|-----------------------|
| Full product name | SM303C P9S 927 PSU NB |
| Full product code | 872016952873499 |
| Order code | 911401586812 |
| Material Nr. (12NC) | 911401586812 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169528734 |
| Numerator - Packs per outer box | 24 |
| EAN/UPC - Case | 8720169540224 |

Dimensional drawing

