



GreenSpace Surface Mount

SP303P P6 940 PSU NB

GreenSpace Surface Mount, 80 lm/W, 940 neutral white

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

| General Information | | |
|--|-------------------------|-----------------|
| Light source engine type | LED | |
| Value ladder | Performance | |
| Number of products on MCB of 16 A type B | | - |
| Protection class IEC | | Safety class II |
| Light Technical | | |
| Luminous Flux | 480 lm | |
| Correlated Color Temperature (Nom) | 4000 K | |
| Luminous Efficacy (rated) (Nom) | 80 lm/W | |
| Color rendering index (CRI) | >90 | |
| Light source color | 940 neutral white | |
| Operating and Electrical | | |
| Input Voltage | 200 to 240 V | |
| Line Frequency | 50 to 60 Hz | |
| Power Consumption | 5.4 6.6 W | |
| Power Factor (Fraction) | 0.5 | |
| Controls and Dimming | | |
| Dimmable | No | |
| Control interface | - | |
| Mechanical and Housing | | |
| Housing Material | Aluminum Alloy | |
| Optical cover material | Acrylate | |
| Housing Color | White | |
| Optical cover finish | Frosted | |
| Ingress protection code | IP20 [Finger-protected] | |
| Mech. impact protection code | IK03 [0.3 J] | |
| Optical cover type | Acrylate | |

GreenSpace Surface Mount

| | |
|--|---------------|
| Net Weight (Piece) | 0.805 kg |
| Approval and Application | |
| CE mark | No |
| Ambient temperature range | -20 to +40 °C |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|----------------------|
| Order product name | SP303P P6 940 PSU NB |
|--------------------|----------------------|

| | |
|---------------------------------|----------------------|
| Full product name | SP303P P6 940 PSU NB |
| Full product code | 872016952546799 |
| Order code | 911401592012 |
| Material Nr. (12NC) | 911401592012 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169525467 |
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 8720169536951 |

Dimensional drawing

