



Surface Mounted Accessory

RC159Z SMB W62L62

Accessory, White

Surface Mounted Brackets provide a robust and efficient solution for installing recessed luminaires directly onto solid ceilings where suspended or modular ceiling systems are not available. Designed to support a wide range of recessed luminaires, the brackets enable clean and professional surface installations without compromising system quality or visual integration. Their precise mechanical interface ensures secure attachment and sufficient internal space for wiring, allowing installers to achieve a neat and seamless result. Compatible with multiple luminaire families—including SlimBlend, CoreLine Panel Gen6, CoreLine Recessed, and Ledinaire Panel Gen5—the brackets offer a flexible approach to project design by enabling the use of recessed luminaires in environments where ceiling integration is not possible. This reduces the need for additional luminaire variants and helps minimise stock complexity. Engineered for installer convenience, the brackets feature a straightforward mounting process that supports fast installation while ensuring reliable long term performance. By enabling simple conversion from recessed to surface mounted application, Surface Mounted Brackets increase design versatility for specifiers and installers alike. Always refer to the installation instructions of the relevant luminaire family to confirm compatibility before installation.

Warnings and Safety

- Always consult the installation instructions of both the accessory and the selected luminaire before installation.
- Ensure the ceiling surface is capable of supporting the weight and fastening requirements of the mounted luminaire.
- Installation must be performed by qualified personnel in accordance with local safety regulations and building standards.

Product data

Surface Mounted Accessory

Mechanical and Housing

Overall length	640.5 mm
Overall width	640.5 mm
Overall height	78.5 mm
Dimensions (Height x Width x Depth)	79 x 641 x 641 mm
Material	Aluminum
Ingress protection code	-
Mech. impact protection code	-
Accessory color	White
Net Weight (Piece)	1.020 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
--	--

Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

Product Data

Order product name	RC159Z SMB W62L62
Full product name	RC159Z SMB W62L62
Full product code	872016975215399
Order code	75215399
Material Nr. (12NC)	911401807887
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169752153
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169752221

Dimensional drawing

