



SmartBright LED Waterproof WT065C

WT065C LED22S/865 1-10V L600 LA

SmartBright LED Waterproof WT065C, 18 W, 2200 lm, 6500 K

The SmartBright LED Waterproof WT065C range provides maximum performance and durability at great value. As an off-the-shelf LED luminaire solution for all your everyday needs, it can be deployed in a wide variety of locations.

Warnings and Safety

- This product is not suitable for cold, damp storage areas, especially where there are obvious temperature gradients, such as vents, doors, etc.
- Do not install the luminaire where it will be exposed to direct sunlight. UV radiation will damage the material over time, resulting in the loss of the waterproof seal and IP65 rating.

Product data

General Information		Operating and Electrical	
Lamp family code	-	Input Voltage	120 to 277 V
Light source replaceable	No	Line Frequency	50 or 60 Hz
Driver included	Yes	Inrush current	19.2 A
Value ladder	Value	Inrush time	0.13 ms
Light Technical		Power Consumption	18 W
Luminous Flux	2,200 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	6500 K	Connection	Push-in connector 3-pole
Luminous Efficacy (rated) (Nom)	122 lm/W	Cable	-
Color rendering index (CRI)	>80	Protection class IEC	Safety class I
		Surge Protection (Common/Differential)	Surge protection level until 2 kV

SmartBright LED Waterproof WT065C

Controls and Dimming

Dimmable	0-10V
Driver/power unit/transformer	Power supply unit
Constant light output	No

Mechanical and Housing

Housing Material	Polycarbonate
Housing Color	Gray
Mounting device	Mounting bracket adjustable
Overall height	74 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Net Weight (Piece)	0.890 kg

Approval and Application

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	-10%,+5%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data

Order product name	WT065C LED22S/865 1-10V L600 LA
Full product name	WT065C LED22S/865 1-10V L600 LA
Full product code	872016951739499
Order code	911401878985
Material Nr. (12NC)	911401878985
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169517394
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169517516

