



## JRP633 | URBANFLEX LYRE BRACKET, Pole-mounting bracket 1 arm, 0 mm, 0°, Dark gray, Mounting device diameter 60 mm

Today's modern cities are looking to be more attractive, welcoming, convenient and safe. These characteristics help ensure that inhabitants want to live in the city, businesses can maximize their prosperity and visitors can better enjoy their stay. For these reasons, we designed UrbanFlex: a visually coherent and flexible lighting solution to perfectly fit a wide range of urban applications. The signature style is modern and minimal, thereby giving your cityscape a visually coherent, elegant and discrete identity. UrbanFlex is available in two sizes and offers a large diversity of mountings and dedicated brackets and poles. Thanks to the built in Philips Ledgine optimized LED platform, and the wide range of available application-tailored optics, UrbanFlex delivers best in class lighting performance in a broad range of applications. By being System Ready our luminaire offers connectivity and dimming options while it can be paired with lighting management systems such as Interact City or existing and upcoming sensor innovations. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application, making maintenance and programming operations faster and easier, and enabling you to create your digital

library of lighting assets and spare parts. As a company conscious about the impact of light on the environment and biodiversity, we also equipped UrbanFlex with our dedicated light recipe that preserves a dark night sky. UrbanFlex is designed for customers looking for ways to achieve uniformity in design and quality of light with elegant, energy-efficient and sustainable products.

## Light Technical

Effective projected area	0.15 m <sup>2</sup>
--------------------------	---------------------

## Mechanical and Housing

Fixation point length distance (Nom)	30 mm
Fixation diameter	Mounting device diameter 60 mm
Bracket tilt angle	0°
Bracket to luminaire diameter	-
Bracket length	0 mm
Bracket color	Dark gray
Bracket type	Pole-mounting bracket 1 arm
Net Weight (Piece)	4.300 kg

## Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

## Sustainability Data

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

## Product Data

Order product name	JRP633 DGR
Full product name	JRP633 DGR
Full product code	872016903581200
Order code	03581200
Material Nr. (12NC)	912300060240
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169035812
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169035812
Product family code	JRP633 [URBANFLEX LYRE BRACKET]

## Dimensional drawing

