



PL-C 2-PIN

PL-C 13W/830/2P 1CT/5X10BOX

PL-C new shape is an efficient and effective medium wattage fluorescent lamp, used in general downlights for retail, hospitality and office applications. The 2 PIN version is designed for electromagnetic gear and is provided with plug in/pull out lamp base. The 4 PIN version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | | Color rendering index (CRI) | |
|------------------------------------|--------------------|-----------------------------|----------|
| Cap-Base | G24d-1 | | >80 |
| Nominal lifetime | 8,000 hour(s) | Operating and Electrical | |
| Light Technical | | Power Consumption | 13.4 W |
| Color Code | 830 [CCT of 3000K] | Lamp Current (Nom) | 175 mA |
| Luminous Flux | 900 lm | Controls and Dimming | |
| Color Designation | Warm White (WW) | Dimmable | No |
| Chromaticity Coordinate X (Nom) | 440 | Mechanical and Housing | |
| Chromaticity Coordinate Y (Nom) | 403 | Bulb Shape | PL-C |
| Correlated Color Temperature (Nom) | 3000 K | Net Weight (Piece) | 0.040 kg |
| Luminous Efficacy (rated) (Nom) | 67 lm/W | | |

PL-C 2-PIN

Approval and Application


Mercury (Hg) Content (Nom) 1.3

Product Data

Order product name PL-C 13W/830/2P 1CT/5X10BOX
Full product name PL-C 13W/830/2P 1CT/5X10BOX
Full product code 872016922566400
Order code 927812583001

Material Nr. (12NC) 927812583001
Numerator - Quantity Per Pack 1
EAN/UPC - Product/Case 8720169225664
Numerator - Packs per outer box 50
EAN/UPC - Case 8720169225688

Dimensional drawing



| Product | D (max) | D1 (max) | A | B |
|-----------------------------|---------|----------|----------|--------|
| PL-C 13W/830/2P 1CT/5X10BOX | 26 mm | 26 mm | 112.5 mm | 136 mm |

