PHILIPS

Lighting

PL-C 4-PIN

PL-C 26W/830/4P 1CT/5X10BOX

PL-C new shape is an efficient and effective medium wattage fluorescent lamp, used in general downlights for retail, hospitality and office applications.The 2 PIN version is designed for electromagnetic gear and is provided with plug in/pull out lamp base. The 4 PIN version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G24q-3
Nominal lifetime	8,000 hour(s)

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,800 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	440
Chromaticity Coordinate Y (Nom)	403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color rendering index (CRI)	>80

Operating and Electrical	
Power Consumption	26.5 W
Lamp Current (Nom)	325 mA

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	PL-C
Net Weight (Piece)	0.040 kg

Approval and Application	
Mercury (Hg) Content (Nom)	1.3

PL-C 4-PIN

Product Data	
Order product name	PL-C 26W/830/4P 1CT/5X10BOX
Full product name	PL-C 26W/830/4P 1CT/5X10BOX
Full product code	872016922890000
Order code	927813083001
Material Nr. (12NC)	927813083001

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169228900
Numerator - Packs per outer box	50
EAN/UPC - Case	8720169228924

Dimensional drawing



Product	D (max)	D1 (max)	A	B
PL-C 26W/830/4P 1CT/5X10BOX	26 mm	26 mm	146.5 mm	162.5 mm

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.