



# MASTER PL-L 4 Pin

## MASTER PL-L 24W/865/4P 1CT/25\_APR

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	2G11	Power Consumption	24.0 W
Life to 50% Failures (Nom)	15,000 hour(s)	Lamp Current (Nom)	0.345 A
Light Technical		Controls and Dimming	
Color Code	865 [CCT of 6500K]	Dimmable	Yes
Luminous Flux	1,800 lm	Mechanical and Housing	
Color Designation	Cool Daylight	Net Weight (Piece)	82.000 g
Correlated Color Temperature (Nom)	6500 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	73 lm/W	Mercury (Hg) Content (Nom)	2.0 mg
Color rendering index (CRI)	80		

# MASTER PL-L 4 Pin

Energy Consumption kWh/1000 h	26 kWh
<b>Product Data</b>	
Order product name	MASTER PL-L 24W/865/4P 1CT/25_APR
Full product name	MASTER PL-L 24W/865/4P 1CT/25_APR
Full product code	871869965804500
Order code	927903286572


Material Nr. (12NC)	927903286572
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699658045
Numerator - Packs per outer box	25
EAN/UPC - Case	8718699658052

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 24W/865/4P 1CT/ 25_APR	39.0 mm	18.0 mm	289.2 mm	315 mm	321.6 mm

## Photometric data



Spectral Power Distribution Colour - MASTER PL-L 24W/865/4P 1CT/25\_APR

