



# TUV PL-L

## TUV PL-L 36W/4P 1CT/25

TUV PL-L lamps are compact UVC (germicidal) lamps used in residential water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

### Product data


General Information		Lamp Current (Nom)		0.435 A
Cap-Base	2G11	Voltage (Nom)		106 V
Useful Life (Nom)	9,000 hour(s)	Mechanical and Housing		
Light Technical		Net Weight (Piece)		104.000 g
Depreciation at Useful Lifetime	20 %	Approval and Application		
Operating and Electrical		Mercury (Hg) Content (Nom)		4.4 mg
Power Consumption	36 W			

# TUV PL-L

CE mark	Yes
<b>UV</b>	
UV-C Radiation at 100 hr	12.2 W
<b>Product Data</b>	
Order product name	TUV PL-L 36W/4P 1CT/25
Full product name	TUV PL-L 36W/4P 1CT/25
Full product code	871150062878740


Order code	927903404007
Material Nr. (12NC)	927903404007
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500628787
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500628794

## Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 36W/4P 1CT/25	18 mm	38 mm	385 mm	410 mm	415 mm

## Photometric data



Spectral Power Distribution Colour - TUV PL-L 36W/4P 1CT/25

