



# MASTER PL-L 4 Pin

## 36 W 4 Pin Cool daylight Non integrated compact fluorescent

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	2G11
Nominal lifetime	15,000 hour(s)
Life to 50% Failures (Nom)	15,000 hour(s)

Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	2,900 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	80 lm/W

Color rendering index (CRI)	80
-----------------------------	----

Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	0.435 A

Controls and Dimming	
Dimmable	Yes

# MASTER PL-L 4 Pin

## Mechanical and Housing

Net Weight (Piece) 104.000 g

## Approval and Application

Mercury (Hg) Content (Nom) 2.0 mg

Energy Consumption kWh/1000 h 40 kWh

## Product Data

Order product name 36 W 4 Pin Cool daylight Non integrated compact fluorescent

Full product name 36 W 4 Pin Cool daylight Non integrated compact fluorescent

Full product code 871150063520441

Order code 927903486572

Material Nr. (12NC) 927903486572


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8711500635204

Numerator - Packs per outer box 25


EAN/UPC - Case 8711500635211

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
36 W 4 Pin Cool daylight Non integrated compact fluorescent	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

## Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/865/4P 1CT/25

## MASTER PL-L 4 Pin

