



MASTER PL-L 4 Pin

55 W 4 Pin Cool white Non integrated compact fluorescent

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	2G11		82
Nominal lifetime	15,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power Consumption	55.0 W
Luminous Flux	4,800 lm	Lamp Current (Nom)	0.525 A
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	87 lm/W	Dimmable	Yes

MASTER PL-L 4 Pin

Mechanical and Housing

Net Weight (Piece) 134.000 g

Approval and Application

Mercury (Hg) Content (Nom) 2.0 mg

Energy Consumption kWh/1000 h 61 kWh

Product Data

Order product name 55 W 4 Pin Cool white Non integrated compact fluorescent

Full product name 55 W 4 Pin Cool white Non integrated compact fluorescent

Full product code 871150061542841

Order code 927908708472

Material Nr. (12NC) 927908708472


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8711500615428

Numerator - Packs per outer box 25


EAN/UPC - Case 8711500615527

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
55 W 4 Pin Cool white Non integrated compact fluorescent	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 55W/840/4P 1CT/25

MASTER PL-L 4 Pin

