



# MASTER TL5 High Efficiency



## MASTER TL5 HE 14W/830 SLV/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	G5	Power Consumption	14.0 W
Features	na [Not Applicable]	Lamp Current (Nom)	0.165 A
Flux measurement reference	Sphere		
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	1,200 lm		
Color Designation	Warm White (WW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.44	Bulb Shape	T5
Chromaticity Coordinate Y (Nom)	0.403	Net Weight (Piece)	0.052 kg
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	86 lm/W	Approval and Application	
Color rendering index (CRI)	82	Energy Efficiency Class	G
		Mercury (Hg) Content (Nom)	1.2 mg
		Energy Consumption kWh/1000 h	14 kWh

# MASTER TL5 High Efficiency

EPREL Registration Number	423443
<b>Product Data</b>	
Order product name	MASTER TL5 HE 14W/830 SLV/40
Full product name	MASTER TL5 HE 14W/830 SLV/40
Full product code	871150063938755
Order code	927926083055


Material Nr. (12NC)	927926083055
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500639387
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500867469

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 14W/830 SLV/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL5 HE 14W/830 SLV/40

## Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

# MASTER TL5 High Efficiency

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE 14W/830 SLV/40

