



TUV TL Mini

TUV 16W FAM/10X25BOX

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data


General Information		Lamp Current (Nom)		0.4 A
Cap-Base	G5	Voltage (Nom)		43 V
Useful Life (Nom)	9,000 hour(s)	Mechanical and Housing		
Light Technical		Net Weight (Piece)	25.700 g	
Depreciation at Useful Lifetime	15 %	Approval and Application		
Operating and Electrical		Mercury (Hg) Content (Nom)	4.4 mg	
Power Consumption	15 W			

TUV TL Mini

UV	
UV-C Radiation at 100 hr	4.2 W
Product Data	
Order product name	TUV 16W FAM/10X25BOX
Full product name	TUV 16W FAM/10X25BOX
Full product code	871150063869427
Order code	928002004013


Material Nr. (12NC)	928002004013
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500638694
Numerator - Packs per outer box	250
EAN/UPC - Case	8711500638717

Dimensional drawing



Product	D	C
TUV 16W FAM/10X25BOX	16 mm	302.5 mm

Photometric data



Spectral Power Distribution Colour - TUV 16W FAM/10X25BOX

