



MASTERColour CDM-TP

MASTERC CDM-TP 70W/830 PG12-2 1CT/12

Range of protected, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light to be used in open luminaires

Warnings and Safety

- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap base	PG12-2	Power Consumption	73.2 W
Operating position	UNIVERSAL [Any or Universal (U)]	Voltage (nom.)	90 V
Life to 50% failures (nom.)	16,000 h		
Light Technical		Controls and Dimming	
Colour Code	830 [CCT of 3000K]	Dimmable	No
Colour designation	Warm White (WW)		
Chromaticity Coordinate X (Nom)	428	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	401	Lamp Finish	Clear
Correlated Colour Temperature (Nom)	3000 K	Bulb shape	T31
Luminous efficacy (rated) (nom.)	82 lm/W	Net Weight (Piece)	72.000 g
Colour rendering index (CRI)	80		
Arc Length O (Nom)	7 mm	Approval and Application	
		Energy Efficiency Class	G
		Mercury (Hg) content (nom.)	5.2 mg

MASTERC colour CDM-TP

Energy consumption kWh/1,000 hours	81 kWh
Product Data	
Order product name	MASTERC CDM-TP 70W/830 PG12-2 1CT/12
Full product name	MASTERC CDM-TP 70W/830 PG12-2 1CT/12
Full EOC	871150020127015
Order code	928086909230
Material no. (12 NC)	928086909230


Local order code	70CDMTP830
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500201270
Numerator – packs per outer box	12
EAN/UPC – Case	8711500201287

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TP 70W/830 PG12-2 1CT/12	32.00 mm	7 mm	89 mm	93 mm	91 mm	149 mm



Photometric data



Spectral Power Distribution Colour - MASTERC CDM-TP 70W/830 PG12-2 1CT/12

MASTERC colour CDM-TP

Lifetime



LDLE_CDM-TP_0001-Life expectancy diagram

Lumen Maintenance Diagram - MASTERC CDM-TP 70W/830 PG12-2 1CT/12

