MASTERColour CDM-Tm Mini 小型陶瓷複金屬燈

MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12

微型單端陶瓷複金屬燈。PGJ5 型一旋即緊燈座

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- For 20W PGJ5 lamp, use only Philips electronic control gear HID PV mini PGJ5 20W
- For 35W PGJ5 lamp, use only Philips electronic control gear HID PV mini PGJ5 35W
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	PGJ5
操作位置	UNIVERSAL [任何或通用 (U)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	12,000 h

照明技術	
色碼	830 [CCT of 3000K]
光通量	1,600 lm
色彩名稱	暖白光 (WW)

色度坐標 X (標稱)	0.434
色度坐標 Y (Nom)	0.398
相關色溫 (標稱)	3000 K
光效 (額定) (標準)	72 lm/W
演色性指數 (CRI)	87
電弧長 O (標稱)	3 mm

運轉與電力	
耗電量	22.1 W

MASTERColour CDM-Tm Mini 小型陶瓷複金屬燈

電壓 (標稱)	100 V

控制與調光	
可調光	否

機械與外罩	
燈泡表層	透明
燈泡形狀	T13.3
淨重 (個)	0.005 kg

認證與應用	
節能等級	G
汞 (Hg) 含量 (最大)	2.4 mg
汞 (Hg) 含量 (標稱)	2.4 mg
能源消耗 kWh/1000 h	23 kWh

EPREL 註冊碼	473347
CE 標誌	是

產品資料	
下訂產品名稱	MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12
完整產品名稱	MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12
完整產品代碼	871150020751715
訂單代碼	928087905130
材質 Nr. (12NC)	928087905130
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500207517
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8711500207524

二维绘图



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12	13.2 mm	0.44 in	3 mm	22.3 mm	22.9 mm	22.6 mm	52 mm

光度数据



Light Distribution Diagram - MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12



Spectral Power Distribution Colour - MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12

MASTERColour CDM-Tm Mini 小型陶瓷複金屬燈

壽命



LDLE_CDM-Tm_20W_830_PGJ5-Life expectancy diagram



Lumen Maintenance Diagram - MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12

© 2023 Signify Holding 保留一切權利。 Signify 不對本協議所含括資訊之準確性及完整性提供任何聲明或保證，對以此訊息為依據採取的任何行動亦概不負責。 除非 Signify 同意，本文件提及之資訊並非任何商業合約，亦不構成任何報價或合約任一部分。 Philips 與 Philips Shield Emblem 均屬 Koninklijke Philips N.V 註冊商標。