



MASTERCoulour CDM-TC

MASTERC CDM-TC 70W/842 G8.5 1CT/12

Range of single-ended, very compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color rendering index (CRI)	
Cap-Base	G8.5		89
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	5 mm
Flux measurement reference	Sphere	Operating and Electrical	
Life to 50% Failures (Nom)	12,000 hour(s)	Power Consumption	73.2 W
		Voltage (Nom)	88 V
Light Technical		Controls and Dimming	
Color Code	842 [CCT of 4200K]	Dimmable	No
Luminous Flux	5,800 lm	Mechanical and Housing	
Color Designation	Cool White (CW)	Bulb Finish	Clear
Chromaticity Coordinate X (Nom)	0.371	Bulb Material	UV-Block Quartz
Chromaticity Coordinate Y (Nom)	0.366	Bulb Shape	T14
Correlated Color Temperature (Nom)	4200 K		
Luminous Efficacy (rated) (Nom)	79 lm/W		

MASTERC colour CDM-TC


Net Weight (Piece)	0.010 kg
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	7 mg
Mercury (Hg) Content (Nom)	7 mg
Energy Consumption kWh/1000 h	74 kWh
EPREL Registration Number	473356
CE mark	Yes

Product Data

Order product name	MASTERC CDM-TC 70W/842 G8.5 1CT/12
--------------------	------------------------------------


Full product name	MASTERC CDM-TC 70W/842 G8.5 1CT/12
Full product code	871150021275715
Order code	928094605131
Material Nr. (12NC)	928094605131
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500212757
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500212764

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 70W/842 G8.5 1CT/12	15 mm	5 mm	51 mm	53 mm	52 mm	85 mm


Photometric data



Spectral Power Distribution Colour - MASTERC CDM-TC 70W/842 G8.5 1CT/12

MASTERCcolour CDM-TC

Lifetime



LDLE_CDM-TC_0001-Life expectancy diagram

