



MASTER CityWhite CDO-ET

MASTER CityWh CDO-ET Plus 150W/828 E40

Ceramic metal halide lamp, with opalized ovoid outer bulb shape, used in outdoor offering pleasant white light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)

Product data

General Information	
Cap base	E40
Operating position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	27,000 h

Light Technical	
Colour Code	828 [CCT of 2800K]
Luminous Flux	15,400 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.447
Chromaticity Coordinate Y (Nom)	0.4
Correlated Colour Temperature (Nom)	2800 K
Luminous efficacy (rated) (nom.)	108 lm/W
Colour rendering index (CRI)	85

Operating and Electrical	
Power Consumption	143.0 W
Voltage (nom.)	89 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Coated glass
Bulb shape	BD90
Net Weight (Piece)	0.157 kg


Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) content (max.)	15.8 mg
Mercury (Hg) content (nom.)	15.8 mg
Energy consumption kWh/1,000 hours	143 kWh

MASTER CityWhite CDO-ET

EPREL Registration Number	473400
CE mark	Yes
Product Data	
Order product name	MASTER CityWh CDO-ET Plus 150W/828 E40
Full product name	MASTER CityWh CDO-ET Plus 150W/828 E40
Full EOC	871829115881300
Order code	928154908835


Material no. (12 NC)	928154908835
Local order code	150CDOETPLUS828
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291158813
Numerator – packs per outer box	12
EAN/UPC - Case	8718291158820

Dimensional drawing




Product	D (max)	C (max)
MASTER CityWh CDO-ET Plus 150W/828 E40	91 mm	227 mm

Photometric data





Light Distribution Diagram - MASTER CityWh CDO-ET Plus 150W/828 E40



Spectral Power Distribution Colour - MASTER CityWh CDO-ET Plus 150W/828 E40

MASTER CityWhite CDO-ET

Lifetime



LDLE_CDO-ET_0002-Life expectancy diagram

Lumen Maintenance Diagram - MASTER CityWh CDO-ET Plus 150W/828 E40

