



# MASTERColour CDM-R111 Elite

## MASTERC CDM-R111 Elite 70W/930 GX8.5 10D

MASTERColour CDM-R111 Elite combines the trendy look of 111 mm aluminium-reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

### Warnings and Safety

- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/930 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	GX8.5
Operating Position	UNIVERSAL [Any or Universal (U)]
Switching Cycle	1,050
Flux measurement reference	Narrow Cone
Life to 50% Failures (Nom)	12,000 hour(s)

Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	10 degree(s)
Luminous Flux	2,805 lm
Luminous Intensity (Nom)	45,000 cd
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.434
Chromaticity Coordinate Y (Nom)	0.398

Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	40 lm/W
Color rendering index (CRI)	92
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	2,805 lm

Operating and Electrical	
Power Consumption	73.2 W
Warm-up time to 60% light	120 s
Voltage (Nom)	89 V

Controls and Dimming	
Dimmable	No

# MASTERC colour CDM-R111 Elite

## Mechanical and Housing

Bulb Finish	Reflector
Bulb Shape	R111
Net Weight (Piece)	96.000 g


## Approval and Application

Energy Efficiency Class	G
Mercury (Hg) Content (Max)	6.6 mg
Mercury (Hg) Content (Nom)	6.6 mg
Energy Consumption kWh/1000 h	74 kWh
EPREL Registration Number	473282

## Product Data



Order product name	MASTERC CDM-R111 Elite 70W/930 GX8.5 10D
Full product name	MASTERC CDM-R111 Elite 70W/930 GX8.5 10D
Full product code	871829168962100
Order code	928195605330
Material Nr. (12NC)	928195605330
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291689621
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291689638

## Dimensional drawing



Product	D (max)	C (max)
MASTERC CDM-R111 Elite 70W/930 GX8.5 10D	111 mm	95 mm

## Photometric data



Spectral Power Distribution Colour - MASTERC CDM-R111 Elite 70W/930 GX8.5 10D

Light Distribution Diagram - MASTERC CDM-R111 Elite 70W/930 GX8.5 10D

## MASTERCcolour CDM-R111 Elite

