



# CorePro Plastic LED bulbs



## CorePro LEDbulb ND 8-60W A60 B22 827

CorePro, LEDbulb, A60, 60 W, B22, 2700 K, 806 lm, CRI 80, 15000 h

The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides beautiful light and dependable performance you expect from LED at an affordable price. CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings of 80% and provides excellent quality of light. By offering a lifetime of 15,000 hours, it reduces maintenance costs.

### Product data


General Information		Operating and Electrical	
Cap base	B22	Colour consistency	<6
Nominal lifetime	15,000 h	Colour rendering index (CRI)	80
Switching Cycle	50,000	LLMF at end of nominal lifetime (nom.)	70 %
Lighting Technology	LEDbulb	Line Frequency	50 to 60 Hz
Flux measurement reference	Sphere	Input frequency	50 to 60 Hz
Warranty period	2 years	Power Consumption	8 W
Colour Code	827 [CCT of 2700K]	Lamp current (nom.)	75 mA
Beam angle (nom.)	200 degree(s)	Wattage equivalent	60 W
Luminous Flux	806 lm	Starting time (nom.)	0.5 s
Colour designation	Warm White (WW)	Warm-up time to 60% light	0.5 s
Correlated Colour Temperature (Nom)	2700 K	Power Factor (Fraction)	0.5
Luminous efficacy (rated) (nom.)	100.00 lm/W	Voltage (nom.)	220-240 V

# CorePro Plastic LED bulbs

Temperature	
T-Case maximum (nom.)	85 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	A60
Net Weight (Piece)	0.080 kg
Approval and Application	
Energy Efficiency Class	F
Energy consumption kWh/1,000 hours	8 kWh
EPREL Registration Number	397622
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4



Ambient temperature range	-20°C to 45°C
Application Conditions	
Can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	CorePro LEDbulb ND 8-60W A60 B22 827
Full product name	CorePro LEDbulb ND 8-60W A60 B22 827
Full EOC	871869657763900
Order code	929001233902
Material no. (12 NC)	929001233902
Local order code	CPB9W827B22NDF
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696577639
Numerator – packs per outer box	10
EAN/UPC - Case	8718696577646

## Dimensional drawing



Product	D	C
CorePro LEDbulb ND 8-60W A60 B22 827	60 mm	110 mm

## Photometric data




General uniform lighting - CorePro LEDbulb ND 8-60W A60 B22 827

Light Distribution Diagram - CorePro LEDbulb ND 8-60W A60 B22 827


# CorePro Plastic LED bulbs

## Photometric data




Spectral Power Distribution Colour - CorePro LEDbulb ND 8-60W A60 B22 827

## Lifetime



LEDbulb 40W E27 830 FR A60



Lumen Maintenance Diagram - CorePro LEDbulb ND 8-60W A60 B22 827

