



CorePro LED tube Mains T5

CorePro LEDtube 600mm 8W830 G5 I MX

CorePro, LEDtube, T5, Mains only, 600 mm, 100-240 V, 8 W, 14W TL5 HE, 3000 K, 1000 lm, 30000 hour(s)

The professional LEDtube MainsFit is a better LED solution suitable for replacing T5 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information	
Cap-Base	G5
Nominal lifetime	30,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Warranty period	3 years

Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,000 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	112.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	70 %
---------------------------------------	------


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8 W
Lamp Current (Max)	75 mA
Lamp Current (Min)	30 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.92
Voltage (Nom)	100-240 V
LED alternative to fluorescent lamp power	14W TL5 HE
Ballast Compatibility	Mains only

CorePro LED tube Mains T5

Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Glass
Product Length	600 mm
Bulb Shape	T5
Net Weight (Piece)	0.070 kg
Approval and Application	
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur certificate



EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C
Product Data	
Order product name	CorePro LEDtube 600mm 8W830 G5 I MX
Full product name	CorePro LEDtube 600mm 8W830 G5 I MX
Full product code	871869673414800
Order code	929001380612
Material Nr. (12NC)	929001380612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696734148
Numerator - Packs per outer box	20
EAN/UPC - Case	8718696734155

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm 8W830 G5 I MX	15.8 mm	19 mm	549 mm	556.1 mm	563.2 mm

Photometric data




Spectral Power Distribution Colour - CorePro LEDtube 600mm 8W830 G5 I MX

General uniform lighting - CorePro LEDtube 600mm 8W830 G5 I MX


CorePro LED tube Mains T5

Photometric data




Light Distribution Diagram - CorePro LEDtube 600mm 8W830 G5 I MX


Lifetime




ESSENTIAL LEDtube 8-16W G5 830-865 APR



ESSENTIAL LEDtube 8-16W G5 830-865 APR




ESSENTIAL LEDtube 8-16W G5 830-865 APR



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W830 G5 I MX

CorePro LED tube Mains T5

Lifetime



Lumen Maintenance Diagram - CorePro LEDtube 600mm 8W830 G5 I MX

