



Specialty Lamps

8W (60W) E26 Blue Bulb

LEDbulb, A19, 40 W, E26, 10950 hour(s), Plastic

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data

General Information	
Cap-Base	E26
Nominal lifetime	10,950 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	10,950 hour(s)
Lighting Technology	LEDbulb

Light Technical	
Beam Angle (Nom)	120 degree(s)
Color Consistency	-
Color rendering index (CRI)	-
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8 W
Lamp Current (Nom)	115 mA

Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	80 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	107 mm
Overall width	60 mm
Overall height	107 mm

Specialty Lamps

Dimensions (Height x Width x Depth)	107 x 60 x 107 mm
Bulb Shape	A19
Net Weight (Piece)	0.060 kg

Approval and Application

EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	8W (60W) E26 Blue Bulb
Full product name	8W (60W) E26 Blue Bulb
Order code	929001998005
Material Nr. (12NC)	929001998005
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463243
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677463248

Dimensional drawing



Product	D	C
8W (60W) E26 Blue Bulb	60 mm	107 mm

Photometric data




© 2020 Philips Lighting B.V. Page 11 of 11

Spectral Power Distribution Colour - 8A19/LED/BLUE/P/ND 120V 4/1FB

General uniform lighting - 8A19/LED/BLUE/P/ND 120V 4/1FB


Specialty Lamps

Photometric data




Light Distribution Diagram - 8A19/LED/BLUE/P/ND 120V 4/1FB

Lifetime



Lumen Maintenance Diagram - 8A19/LED/BLUE/P/ND 120V 4/1FB



Life Expectancy Diagram

